

## CRC HANDCLEANER

Ref. : 10535

### 1. GENERAL DESCRIPTION

---

Waterless handcleaner containing lanolin.

CRC Handcleaner is formulated to meet the tough needs of the industrial professional, with hand care as the primary objective. It is based on mild hydrocarbon solvents and biodegradable surfactants. CRC Handcleaner can be used without water and is ideal when working inside or outside where there is no easy access to wash facilities.

### 2. FEATURES

---

- Removes the most stubborn dirt and grime.
- Super effective on grease, common paints, ink, glue cements, bitumen, carbon and many other chemical compounds.
- Can be used with or without water.
- Quick cleaning capacity.
- Contains lanolin to condition the skin.
- Pleasant perfume odour.
- Contains no abrasives.
- Leaves the hands with a smooth soft feel.
- No disposal problems.

### 3. APPLICATIONS

---

To clean hands soiled with:

- oils and greases
- stains and grime
- cement and adhesives
- bitumen and tar
- common paints and inks

Out-cleans soaps:

- in industrial plants
- in mines
- at farms
- at construction sites
- at home

### 4. DIRECTIONS


---

- Before use, do not wet hands.
- Apply sufficient cleaner (about a teaspoonful) onto dry, soiled hands.
- Rub well until completely liquefied and all soiling is loosened.



Manufactured by :  
CRC Industries Europe NV  
Touwslagerstraat 1 – 9240 Zele – Belgium  
Tel (32) (0) 52/45.60.11 Fax (32) (0) 52/45.00.34  
[www.crcind.com](http://www.crcind.com)





## TECHNICAL DATA SHEET 2/2

### CRC HANDCLEANER

Ref. : 10535

- Just wipe off with paper towel or cloth, or rinse off with water.
- Dry hands properly.
- Avoid eye contact. Keep out of reach of children.
- A safety data sheet according EU directive 93/112 is available for all CRC products.

#### 5. TYPICAL PRODUCT DATA (without propellant)

---

Appearance	: semi solid cream
Colour	: white
Odour	: characteristic perfume odour
Clarity	: opaque
Specific gravity (@ 20°C)	: 1 ± 0,1
pH (5% in water)	: 6,25 – 6,75
Viscosity	: 8.000 – 9.000 cp
Solids content (6 hrs. @ 100°C)	: 12,0 %
Thermal stability	
48 hrs. @ 45°C	: pass
48 hrs. @ 0°C	: pass
Properties of the hydrocarbon solvent	
Distillation range	: 195 – 245 °C
Flash point (closed cup)	: 73 °C
Aromatics content	: < 0,1% wt

#### 6. PACKAGING

---

tubes :	12 x 150 ml
bulk :	6 x 2500 ml
	a dispenser for the 2.500 ml bulk pack is available

All statements in this publication are based on service experience and/or laboratory testing. Because of the wide variety of equipment and conditions and the unpredictable human factors involved, we recommend that our products be tested on-the-job prior to use. All information is given in good faith but without warranty neither expressed nor implied.

This Technical Data Sheet may already have been revised at this moment for reason such as legislation, availability of components and newly acquired experiences. The latest and only valid version of this Technical Data Sheet will be sent to you upon simple request or can be found on our website: [www.crcind.com](http://www.crcind.com).

We recommend you to register on this website for this product so you will be able to receive any future updated version automatically.

Version : 10535 03 0300 01  
Date : 25 september 2003



Manufactured by :  
CRC Industries Europe NV  
Touwslagerstraat 1 – 9240 Zele – Belgium  
Tel (32) (0) 52/45.60.11 Fax (32) (0) 52/45.00.34  
[www.crcind.com](http://www.crcind.com)

