

DIMENSIONS ARE IN INCHES		UNLESS OTHERWISE NOTED	TOLERANCES AND ANGLES	TITLE	DWG NO.
ONE PLACE DECIMALS: $\pm .1$ [2.5]	THREE PLACE DECIMALS: $\pm .005$ [.127]		ANGLES $\pm 2^\circ$	LOW PROFILE SOCKET STRIP	CLH-1XX-XX-X-XX-XX
TWO PLACE DECIMALS: $\pm .01$ [.25]	FOUR PLACE DECIMALS: $\pm .0020$ [.0508]				SHEET 1 OF 2











TABLE 1		
ENTRY SPEC	CONTACT	INSULATOR
-DE (SEE FIG. 1)	C-73-03-X-X	CLH-XX-D
-DV (SEE FIG. 2)	C-73-01-X-X	CLH-XX-D
-TE (SEE FIG. 3)	C-73-02-X-X	CLH-XX-D
-PE (SEE FIG. 4)	C-73-04-X-X	CLH-XX-D
-BE (SEE FIG. 5)	C-73-01-X-X	CLH-XX-DBE



"Q" = (# OF POS x .100) $\pm .005$
"P" = ("Q" - .225/2) $\pm .020$



AVAILABLE ON POSITIONS 03 THRU 50 ONLY

IMPORTANT NOTE
THE DIMENSIONS SHOWN ON THIS DRAWING ARE FOR INFORMATION ONLY. THE DIMENSIONS SHOWN ON THE PARTS DRAWING ARE THE DIMENSIONS TO BE USED FOR MANUFACTURING. THE DIMENSIONS SHOWN ON THE PARTS DRAWING ARE THE DIMENSIONS TO BE USED FOR MANUFACTURING.

MATERIAL:		DISPROD/ASSEMBLY/100
BODY:		CLH-ARM
VECTRA E130		
CONTACT:		
521 PHOSPHOR BRONZE		
FULL HARD		
MADE BY:		PURVIS 10-4-94
CLH-1XX-XX-X-XX-XX		
SHEET 1 OF 2		