

CN-TVA-001

The drawing consists of two views of a mechanical assembly. The top view is a cross-section showing a central cylindrical component with a cross-hatched pattern, labeled 'A'. This component is seated within a larger housing. The housing has a central bore with a diameter of $\varnothing 8.7 \pm 0.1$ and an outer diameter of $\varnothing 9.5^{+0.02}_{-0.05}$. The total length of the housing is 24 ± 0.1 , with two sections of 8.5 ± 0.1 on either side of the central bore. A dimension of 0.5 ± 0.1 is shown for the thickness of the housing wall. The bottom view is a side view of a cylindrical component, labeled 'B', with a diameter of $\varnothing 1.8 \pm 0.1$. It has a total length of 23 ± 0.1 and a central section with a diameter of $\varnothing 2.4 \pm 0.05$ and a length of 2.0 ± 0.1 . A label 'C' points to a feature on the side of the housing in the top view.

	Approved	
	Check	

