

REVISIONS				DOC. NO. SPC-F004 * Effective: 7/8/02 * DCP No: 1398						
DCP #	REV	DESCRIPTION			DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
	B	Marking removed, spec revised			JAP	2/19/92	JC	2/19/92	JC	2/19/92
1199	C	Renamed -was PHS-0**-***-BLK			JWM	9/24/01	JC	10/16/01	JC	10/16/01

The **PHS** series is a flexible, adhesive-lined, flame retardant, thin wall polyolefin with an integral internal layer of special thermoplastic adhesive that bonds with a wide variety of rubber, plastics and metals, forming a permanent, non-drying, flexible and water proof barrier.

Shrink Ratio: 3:1 Shrink Temp: 121°C (259°F) Operating Temp: -55°C ~ 110°C (-67°F~230°F)

Dimensions				Standard Packages (Color: Black)					
Size	Expanded I.D. (Min)	Recovered I.D. (Max)	Recovered Nominal Wall Thickness	4 Foot Lengths (+1", -0")			6 Inch Lengths (±.125")		
				Type No.	Pcs	Total Footage	Type No.	Pcs	Total Footage
1/8"	.125"	.040"	.040"	PHS-008-4025-BLK	25	100FT	PHS-008-6028-BLK	28	14FT
3/16"	.187"	.062"	.040"	PHS-012-4025-BLK	25	100 FT	PHS-012-6024-BLK	24	12 FT
1/4"	.250"	.080"	.040"	PHS-016-4025-BLK	25	100 FT	PHS-016-6020-BLK	20	10 FT
3/8"	.375"	.120"	.055"	PHS-024-4025-BLK	25	100 FT	PHS-024-6016-BLK	16	8 FT
1/2"	.500"	.160"	.070"	PHS-032-4005-BLK	5	20 FT	PHS-032-6014-BLK	14	7 FT
3/4"	.750"	.250"	.085"	PHS-048-4005-BLK	5	20 FT	PHS-048-6012-BLK	12	6 FT
1"	1.000"	.320"	.100"	PHS-064-4005-BLK	5	20 FT	PHS-064-6008-BLK	8	4 FT
1 1/2"	1.500"	.510"	.100"	PHS-096-4005-BLK	5	20 FT	PHS-096-6005-BLK	5	2.5 FT

TYPICAL PROPERTIES

Physical

Tensile Strength	2100 PSI
Ultimate Elongation	450%
Longitudinal Change	+1%, -15%
Secant Modulus (2%)	17,000 PSI
*Heat Aging (168 hrs @ 175°C)	Elongation 175%
*Heat Shock (4 hrs @ 225°C)	No dripping, cracking, or flowing
*Low Temp Flexibility (4 hrs @ -55°C)	No cracking

**Flexibility: 3

Flammability: Self-extinguishing, meets UL 224
All-Tubing Flame Test (jacket)

Electrical

Dielectric Strength	700 V/mil
Volume Resistivity	10^{14} ohm-cm

Chemical

Corrosive Effect	Non-corrosive
Water Absorption	0.3%
Fungus Resistance	Non-nutrient
Fluid Resistance	Excellent
Applicable Specifications: MIL-DTL-23053/4	Class 3

Adhesive

Peel Strength, pli	
Polyethylene	30
PVC	10
Lead	15
Aluminum	40

Corrosive Effect Non-corrosive



*Outer wall only.

**Flexibility: The materials are rated on a scale of 1~10. (1=most flexible and 10=most rigid)

*The technical information provided consists of typical product data and should not be used for specification purposes.
Unless otherwise noted, all tests are performed at room temperature.*

SPC-F004.DWG

TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY:	DATE:	DRAWING TITLE: High Shrink-Adhesive Lined, Polyolefin Tubing				
			SIZE	DWG. NO.	ELECTRONIC FILE	REV	
JAP		2/19/92	A		TA-409		
CHECKED BY:		DATE:			TA-409.dwg		
JC		2/19/92			C		
APPROVED BY:		DATE:	SCALE: NTS		U.O.M.: INCHES [mm]		
JC		2/19/92			SHEET: 1 OF 1		

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY. DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.