

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

©

COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	ECR-15-004309	18MAR2015	DW	CW
	A3	ECR-15-007632	25MAY2015	DW	CW
	B	ECR-15-014907	14OCT2015	DL	CW
	B1	ECR-16-011987	08NOV2016	QY	CW

NOTES:

- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 500 V
RATED CURRENT: 16 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6 KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
OPERATION TEMPERATURE: $-40-+125^{\circ}C$
WIRE RANGE: 0.14-4 mm² (26-12 AWG)
CONTACT TYPE: CRIMP CONTACT
- CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING:T20300X20XX000)


注释:

- 技术参数:
绝缘材料: PC
额定电压: 500V
额定电流: 16A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 6 KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
工作温度: $-40-+125^{\circ}C$
接线范围: 0.14-4 mm² (26-12 AWG)
接线类型: 冷压接
- 端子需要单独订购.
(订货号参考图面: T20300X20XX000)




M4 SCREW, RECOMMENDED
TIGHTENING TORQUE 1.2Nm
M4螺丝, 推荐锁紧力矩 1.2Nm

4X M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3螺丝, 推荐锁紧力矩 0.5Nm



PANEL CUT FOR INSERTS FOR USE
WITHOUT HOODS/ HOUSINGS
不使用防护外壳时芯件的安装开孔图




TYPE 1, T2050462201-000, WITH TE LOGO
类型 1, T2050462201-000, TE LOGO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

FINISH

DWN 11JUN2014

David Wang

CHK 11JUN2014

Chris Wang

APVD 11JUN2014

Xiang Xu

PRODUCT SPEC

108-106137

APPLICATION SPEC

114-106137

WEIGHT

-

Customer Drawing

TE

TE Connectivity

NAME

HEE-046-F

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

T2050462201000

SCALE

1:1





SHEET

1 OF 2

REV

B1


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




NOTE:
ALL SPEC REFER TO TYPE I

注释:
所有产品规范参照 TYPE I

TYPE-2,T2050462201-002,WITH STAINLESS STEEL SCREW,WITHOUT LOGO
类型-2,T2050462201-002,带不锈钢螺丝,无LOGO



T2050462201-002	HEE-046-F	HEE-046 FEMALE INSERT, WITH STAINLESS STEEL SCREW,WITHOUT LOGO HEE-046 母插,带不锈钢螺丝,无LOGO	TYPE-2 类型-2
T2050462201-000	HEE-046-F	HEE-046 FEMALE INSERT HEE-046 母插	TYPE-1 类型-1
PART NUMBER 料号	PART DESCRIPTION 描述		TYPE 类型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN David Wang 11JUN2014	 TE Connectivity					
		CHK Chris Wang 11JUN2014						
DIMENSIONS: mm		APVD Xiang Xu 11JUN2014	NAME HEE-046-F					
		PRODUCT SPEC 108-106137	SIZE A3					
		APPLICATION SPEC 114-106137					CAGE CODE 00779	
		DRAWING NO C-T2050462201000						
MATERIAL - -		FINISH - -	RESTRICTED TO -		SCALE 1:1			
Customer Drawing			SHEET 2 OF 2		REV B1			