

HHR200A Cylindrical 4/5A size (HR 17/43)

Dimensions (with Tube) (mm)




Specifications

Diameter	17.0 +0 / -0.7 mm
Height	43.0 +0 / -1.5mm
Approximate Weight	32g

Nominal Voltage		1.2V	
Discharge Capacity*	Average**	2040mAh	
	Rated (Min.)	2000mAh	
Approx. Internal impedance at 1000Hz at charged state.		20mΩ	
Charge		Standard	200mA x 16hrs.
		Rapid	1700mA x 1.4hrs.
Ambient Temperature	Charge	Standard	0°C to 45°C
		Rapid	0°C to 40°C
	Discharge		-10°C to 65°C
	Storage	< 1 year	-20°C to 35°C
		< 3 months	-20°C to 45°C
		< 1 month	-20°C to 55°C

* After charging at 0.1CmA for 16 hours, discharging at 0.2CmA.
** For reference only.
Battery performance and cycle life are strongly affected by how they are used. In order to maximize battery safety, please consult Panasonic when determining charge / discharge specs, warning label contents and unit design.

Typical Charge Characteristics



Typical Discharge Characteristics

