

HCMOS SMD Crystal Oscillator

ASD SERIES



ESD Sensitive



RoHS/RoHS II compliant



2.5 X 2.0 X 1.0 mm

Moisture Sensitivity Level (MSL) – This product is Hermetically Sealed and not Moisture Sensitive - MSL = N/A: Not Applicable

For Vdd=3.3V & 2.5V and custom frequencies between 8.00MHz & 200.000MHz, or carrier frequency > 60.0MHz, please consider Abracon's [ASG2-C series](#) of XO and VCXO's

FEATURES:

- Low height 1.0mm max
- Low current consumption
- Tri-state function
- Suitable for RoHS compliant reflow
- Tight stability option
- Seam sealed package assures high reliability

APPLICATIONS:

- CCD clock for VTR Camera
- Equipment connected to PC or PC cards
- Thin equipment

STANDARD SPECIFICATIONS:

Parameters		Minimum	Typical	Maximum	Units	Notes
Frequency Range		0.750		60	MHz	
Operating Temperature		-20		+70	°C	STD temp. Option code E (See options)
Storage Temperature		-55		+100	°C	
Overall Frequency Stability		-100		+100	ppm	See options
Supply Voltage (Vdd)		+3.135	+3.3	+3.465	V	ASD (Standard)
		+2.85	+3.0	+3.15		ASD1
		+2.375	+2.5	+2.625		ASD2
		+1.71	+1.8	+1.89		ASD3
		+0.95	+1.0	+1.05		ASD6
Input Current (Idd)	ASD (3.3V)		2.5	5	mA	0.750~15.999 MHz
			4	7		16.000~39.999 MHz
			9	13		40.000~60.000 MHz
	ASD1 (3.0V)		2.5	4	mA	0.750~15.999 MHz
			3.5	6		16.000~39.999 MHz
			8	12		40.000~60.000 MHz
	ASD2 (2.5V)		2	3.5	mA	0.750~15.999 MHz
			3	5		16.000~39.999 MHz
			7	10		40.000~60.000 MHz
	ASD3 (1.8V)		1	2.5	mA	0.750~15.999 MHz
			2	4		16.000~39.999 MHz
			4	7		40.000~60.000 MHz
	ASD6 (1.0V)		1.0	2.5	mA	25.000 MHz
Symmetry @ 1/2Vdd		40		60	%	STD (See option)
Output Load:				15	pF	CMOS
Output Voltage (VOH):		0.9* Vdd			V	
Output Voltage (VOL):				0.1* Vdd	V	



HCMOS SMD Crystal Oscillator

ASD SERIES

(Continued)



RoHS/RoHS II compliant



2.5 X 2.0 X 1.0 mm

Parameters		Minimum	Typical	Maximum	Units	Notes
Rise and Fall Time (Tr/Tf):	ASD (3.3V)		3	7	ns	0.750~15.999 MHz
			2.5	6		16.000~39.999 MHz
			2	4		40.000~60.000 MHz
	ASD1 (3.0V)		3	7	ns	0.750~15.999 MHz
			2.5	6		16.000~39.999 MHz
			2	4		40.000~60.000 MHz
	ASD2 (2.5V)		4	8	ns	0.750~15.999 MHz
			3	7		16.000~39.999 MHz
			2.5	5		40.000~60.000 MHz
	ASD3 (1.8V)		5	10	ns	0.750~15.999 MHz
			3.5	8		16.000~39.999 MHz
			3	6		40.000~60.000 MHz
	ASD6 (1.0V)		1.9	6.0	ns	25.000 MHz
Start-up Time:	ASD (3.3V)		6	10	ms	0.750~15.999 MHz
			6	10		16.000~39.999 MHz
			5	10		40.000~60.000 MHz
	ASD1 (3.0V)		6	10	ms	0.750~15.999 MHz
			6	10		16.000~39.999 MHz
			5	10		40.000~60.000 MHz
	ASD2 (2.5V)		6	10	ms	0.750~15.999 MHz
			6	10		16.000~39.999 MHz
			5	10		40.000~60.000 MHz
	ASD3 (1.8V)		6	10	ms	0.750~15.999 MHz
			6	10		16.000~39.999 MHz
			5	10		40.000~60.000 MHz
	ASD6 (1.0V)		2.0	10	ms	25.000 MHz
Tri-state function (Stand-by) :		"1" (VIH≥0.7*Vdd) or Open: Oscillation; "0" (VIH<0.3*Vdd) : No oscillation/Hi Z				
Phase Jitter (12kHz to 20MHz)	ASD (3.3V)		0.4	1.0	ps	0.750~15.999 MHz
			0.4	1.0		16.000~39.999 MHz
			0.3	1.0		40.000~60.000 MHz
	ASD1 (3.0V)		0.4	1.0	ps	0.750~15.999 MHz
			0.4	1.0		16.000~39.999 MHz
			0.3	1.0		40.000~60.000 MHz
	ASD2 (2.5V)		0.5	1.0	ps	0.750~15.999 MHz
			0.5	1.0		16.000~39.999 MHz
			0.5	1.0		40.000~60.000 MHz
	ASD3 (1.8V)		0.5	1.0	ps	0.750~15.999 MHz
			0.5	1.0		16.000~39.999 MHz
			0.5	1.0		40.000~60.000 MHz
	ASD6 (1.0V)		0.3	1.0	ps	25.000 MHz
Period Jitter RMS	ASD (3.3V)		3.0	5.0	ps	0.750~15.999 MHz
			3.0	5.0		16.000~39.999 MHz
			3.0	5.0		40.000~60.000 MHz
	ASD1 (3.0V)		3.0	5.0	ps	0.750~15.999 MHz
			3.0	5.0		16.000~39.999 MHz
			3.0	5.0		40.000~60.000 MHz
	ASD2 (2.5V)		3.0	5.0	ps	0.750~15.999 MHz
			3.0	5.0		16.000~39.999 MHz
			3.0	5.0		40.000~60.000 MHz
	ASD3 (1.8V)		3.0	5.0	ps	0.750~15.999 MHz
			3.0	5.0		16.000~39.999 MHz
			3.0	5.0		40.000~60.000 MHz
	ASD6 (1.0V)		4.8	6.0	ps	25.000 MHz
Aging at 25°C/year		-5		+5	ppm	
Disable Current:				20	µA	



HCMOS SMD Crystal Oscillator

ASD SERIES





2.5 X 2.0 X 1.0 mm

OPTIONS AND PART IDENTIFICATION:




OUTLINE DRAWING:



Bottom view

Recommended land pattern




Pin	Function
1	Tri-State
2	GND/Case
3	Output
4	Vdd

Note1: Recommend using an approximately 0.01uF bypass capacitor between PIN 2 and 4.

Dimensions: inches (mm)

ASD SERIES

T: 1000pcs/reel
T2: 250pcs/reel
T3: 3000pcs/reel



Dimensions: mm

The graph illustrates the temperature profile for a reflow soldering process. The Y-axis represents Temperature (°C) and the X-axis represents Time (seconds). The profile is divided into three main phases: Pre-Heat, Reflow, and Cool.

- Pre-Heat:** The temperature rises from 25°C to 150°C. This phase is labeled with a time interval of 60~120s.
- Reflow:** The temperature rises from 150°C to 260°C, remains at 260°C for a short duration, and then falls back to 150°C. This phase is labeled with a time interval of 30~40s. A note above the peak indicates "10s max. 1 time at +260°C±5°C".
- Cool:** The temperature falls from 150°C to 25°C. This phase is labeled with a time interval of 60~90s.



Need a test socket for the ASD Series? To view compatible **PRECISION TEST & BURN-IN SOCKETS** for these parts, [**click here. P/N AXS-2520-04-01**](#)

ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[ASD1-4.000MHz-ECT](#) [ASD1-33.333MHz-ECT](#) [ASD1-14.7456MHz-ECT](#) [ASD1-60.000MHz-ECT](#) [ASD3-24.000MHz-ECT](#) [ASD1-8.000MHz-ECT](#) [ASD3-27.000MHz-ECT](#) [ASD1-50.000MHz-ECT](#) [ASD3-20.000MHz-ECT](#) [ASD1-14.31818MHz-ECT](#) [ASD3-24.576MHz-ECT](#) [ASD1-32.000MHz-ECT](#) [ASD1-40.000MHz-ECT](#) [ASD3-25.000MHz-ECT](#) [ASD1-3.6864MHz-ECT](#) [ASD1-24.576MHz-ECT](#) [ASD1-30.000MHz-ECT](#) [ASD1-48.000MHz-ECT](#) [ASD1-11.0592MHz-ECT](#) [ASD1-12.000MHz-ECT](#) [ASD1-10.000MHz-ECT](#) [ASD3-50.000MHz-ECT](#) [ASD1-33.000MHz-ECT](#) [ASD3-14.31818MHz-ECT](#) [ASD1-25.000MHz-ECT](#) [ASD3-29.4912MHz-ECT](#) [ASD1-7.3728MHz-ECT](#) [ASD3-40.000MHz-ECT](#) [ASD1-20.000MHz-ECT](#) [ASD1-27.000MHz-ECT](#) [ASD1-1.544MHz-ECT](#) [ASD1-18.432MHz-ECT](#) [ASD1-24.000MHz-ECT](#) [ASD-25.000MHz-LKST](#) [ASD3-1.544MHz-LR-T](#) [ASD3-1.8432MHz-LR-T](#) [ASD3-3.6864MHz-LR-T](#) [ASD3-4.000MHz-LR-T](#) [ASD3-7.3728MHz-LR-T](#) [ASD3-8.000MHz-LR-T](#) [ASD3-10.000MHz-LR-T](#) [ASD3-11.0592MHz-LR-T](#) [ASD3-12.000MHz-LR-T](#) [ASD3-14.31818MHz-LR-T](#) [ASD3-14.7456MHz-LR-T](#) [ASD3-18.432MHz-LR-T](#) [ASD3-19.200MHz-LR-T](#) [ASD3-20.000MHz-LR-T](#) [ASD3-24.000MHz-LR-T](#) [ASD3-24.576MHz-LR-T](#) [ASD3-25.000MHz-LR-T](#) [ASD3-26.000MHz-LR-T](#) [ASD3-27.000MHz-LR-T](#) [ASD3-29.4912MHz-LR-T](#) [ASD3-30.000MHz-LR-T](#) [ASD3-32.000MHz-LR-T](#) [ASD3-33.000MHz-LR-T](#) [ASD3-33.333MHz-LR-T](#) [ASD3-44.000MHz-LR-T](#) [ASD3-48.000MHz-LR-T](#) [ASD3-50.000MHz-LR-T](#) [ASD3-60.000MHz-LR-T](#) [ASD3-64.000MHz-LR-T](#) [ASD3-66.000MHz-LR-T](#) [ASD3-66.666MHz-LR-T](#) [ASD3-70.000MHz-LR-T](#) [ASD3-75.000MHz-LR-T](#) [ASD1-1.544MHz-LR-T](#) [ASD1-1.8432MHz-LR-T](#) [ASD1-3.6864MHz-LR-T](#) [ASD1-4.000MHz-LR-T](#) [ASD1-7.3728MHz-LR-T](#) [ASD1-8.000MHz-LR-T](#) [ASD1-10.000MHz-LR-T](#) [ASD1-11.0592MHz-LR-T](#) [ASD1-12.000MHz-LR-T](#) [ASD1-14.31818MHz-LR-T](#) [ASD1-14.7456MHz-LR-T](#) [ASD1-18.432MHz-LR-T](#) [ASD1-19.200MHz-LR-T](#) [ASD1-20.000MHz-LR-T](#) [ASD1-24.000MHz-LR-T](#) [ASD1-24.576MHz-LR-T](#) [ASD1-25.000MHz-LR-T](#) [ASD1-26.000MHz-LR-T](#) [ASD1-27.000MHz-LR-T](#) [ASD1-29.4912MHz-LR-T](#) [ASD1-30.000MHz-LR-T](#) [ASD1-32.000MHz-LR-T](#) [ASD1-33.000MHz-LR-T](#) [ASD1-33.333MHz-LR-T](#) [ASD1-44.000MHz-LR-T](#) [ASD1-48.000MHz-LR-T](#) [ASD1-50.000MHz-LR-T](#) [ASD1-60.000MHz-LR-T](#) [ASD1-64.000MHz-LR-T](#) [ASD1-66.000MHz-LR-T](#) [ASD1-66.666MHz-LR-T](#) [ASD1-70.000MHz-LR-T](#) [ASD1-75.000MHz-LR-T](#)