



ELECTRICAL:

746ET SERIES MAGNETIC CIRCUIT




C1 = 1000pF, 2 kV CAPACITOR

R1-R4 = 75 OHMS, 1/16W RESISTORS



PIN DESIGNATIONS

SUGGESTED PCB LAYOUT
(Component Side)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DRN G. ATTADIA - DOCK5 16MAR2005	TRP connector Dongguan China	
DIMENSIONS: INCHES		CHK D. FAROLE 16MAR2005	PRODUCT SPEC 108-2100	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPRO D. FAROLE 16MAR2005	APPLICATION SPEC —	
MATERIAL —		FINISH —	WEIGHT —	
0 PLC ± — 2 PLC ± — 3 PLC ± .010 4 PLC ± .005 ANGLES ± —		SIZE A100779C-6610165		RESTRICTED TO —
CUSTOMER DRAWING		SCALE 4:1		SHEET 2 OF 2 REV E