

THIS DRAWING IS UNPUBLISHED. DIFFUSION RESTREINTE. RELEASED FOR PUBLICATION LIBRE A LA DIFFUSION. ALL RIGHTS RESERVED. TOUS DROITS RESERVES.

FILS ADMISSIBLES (ACCEPTABLES WIRES)

LOC F DIST 7

REVISIONS

P	LTR	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
D1		REVISED PER ECO-11-005150	27APR11	RK	HMR

JAUGE (AWG) SECTION / 7 BRINS (7 STRANDS) 24 0.22mm²

ISOLANT: Ø MAX / MATIERE (INSUL.: Ø MAX / MAT'L) Ø 1.2 / PVC

2.54

DIM A

VOIE N°1 (FIRST POSITION)

14.5⁰_{-0.4}

5

REPERE VOIE N°1 (MARK POSITION NUMBER 1)

"B" +0.12₀

"C" 0_{-0.8}

8⁰_{-0.5}

1.8±0.2

10.3

8.9 MIN

3.4⁰_{-0.1}

4.5⁰_{-0.1}

COUPE C-C

OBSOLETE

OBSOLETE	9	64.38	60.96	25	2-201708-5	2-144270-5
OBSOLETE	9	61.76	58.42	24	2-201708-4	2-144270-4
OBSOLETE	10	59.22	55.88	23	2-201708-3	2-144270-3
OBSOLETE	10	56.68	53.34	22	2-201708-2	2-144270-2
OBSOLETE	10	54.14	50.80	21	2-201708-1	2-144270-1
OBSOLETE	11	51.60	48.26	20	2-201708-0	2-144270-0
OBSOLETE	12	49.06	45.72	19	1-201708-9	1-144270-9
	12	46.52	43.18	18	1-281708-8 *	1-144270-8 *
OBSOLETE	13	43.98	40.64	17	1-201708-7	1-144270-7
OBSOLETE	14	41.44	38.18	16	1-201708-6	1-144270-6
	15	38.90	35.56	15	1-281708-5 *	1-144270-5 *
OBSOLETE	16	36.36	33.02	14	1-201708-4	1-144270-4
OBSOLETE	17	33.82	30.48	13	1-201708-3	1-144270-3
	18	31.28	27.94	12	1-281708-2 *	1-144270-2 *
OBSOLETE	20	28.74	25.40	11	1-201708-1	1-144270-1
	20	26.20	22.86	10	1-281708-0 *	1-144270-0 *
OBSOLETE	25	23.66	20.32	9	0-201708-9	0-144270-9
	25	21.12	17.78	8	0-281708-8 *	0-144270-8 *
	30	18.58	15.24	7	0-281708-7	0-144270-7
	35	16.04	12.70	6	0-281708-6 *	0-144270-6 *
	40	13.50	10.16	5	0-281708-5 *	0-144270-5 *
	50	10.96	7.62	4	0-281708-4 *	0-144270-4 *
	70	8.42	5.08	3	0-281708-3 *	0-144270-3 *
	100	5.88	2.54	2	0-281708-2	0-144270-2

QUANT / TUBE C A, B Nb DE POS 4 VRAC (L.P.)

DIMENSIONS

REFERENCES (PART No)

1 CES CONNECTEURS SONT PREVUS POUR ETRE ACCOUPLES AVEC LES EMBASES 'HE1402' SIMPLE RANGEE (THESE CONNECTEURS ARE DESIGNED TO BE MATED WITH 'HE1402' HEADERS SINGLE ROW)

2 LES REFERENCES SUIVIES D'UN ' * ' SONT LES VERSIONS NORMALISEES SELON LA 'CEI 603-8' (THE PART-NO FOLLOWED BY ' * ' ARE COVERED BY THE INTERNATIONAL STANDARD 'IEC603-8')

3 REVETEMENT DES CONTACTS: ETAME (THE CONTACTS ARE TIN PLATED)

4 CONNECTEURS CONDITIONNES SOUS TUBE PVC (THESE CONNECTEURS ARE PACKAGED IN TUBE)

5 ' X ' EST REMPLACÉ PAR LE DEUXIEME CHIFFRE DES JAUGES AWG (' X ' REPLACED BY THE SECOND DIGIT OF AWG AS DEFINED IN TABLE)

6 MATIERES - BOITIER: PBT UL94V0 - CONTACTS: BRONZE PHOSPHOREUX. (MATERIALS - CASE: PBT UL94V0 - CONTACTS: PHOSPHOR BRONZE)

DWN/DESSINE 17NOV2000 C. COMBEDOUZON

CHK/VERIFIE 17NOV2000 T. CORRIOU

APVD/APPROUVE 17NOV2000 Y. PETRONIN

PRODUCT SPEC 108-15053

SPEC, PRODUIT

APPLICATION SPEC 114-15030

SPEC, APPLICATION

WEIGHT MASSE APPROX. -

SIZE FORMAT A2

CAGE CODE 00779

DRAWING NO No PLAN C=281708

RESTRICTED TO RESERVE A -

CUSTOMER DRAWING /PLAN CLIENT

UNIQUEMENT POUR REFERENCE

SCALE ECHELLE 4

SHEET FEUILLE

OF DE

REV D1