

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD


A

REV PER 0G3A-0002-04

05MAR04

JR

TM

AMP
WIRE RANGE22-16 AWG
SOLID OR STRANDED

- 1 STAMP AMP 22-18, LOCATED APPROX AS SHOWN. STAMPING MAY BE ON TOP OR BOTTOM.
- 2 WIRE INSULATION DIA: 2.67-3.56
- 3 TONGUE MATERIAL THK: 0.84 MAX
- 4 FROM THE EDGE OF METAL WIRE BBL TO CENTER OF STUD HOLE.
- 5 105°C [221°F] MAX OPERATING TEMP.
- 6 VOLTAGE RATING, 300V MAX
- 7 MATERIAL: BODY- COPPER ASTM B-152
SLEEVE: NYLON, RED
- 8 FINISH: BODY- TIN PLATE PER ASTM B545

LOOSE PIECE

151730-0

PACKAGE TYPE

PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN JR RUTH 05MAR2004

CHK T MICHIELUTTI 05MAR04

APVD T MICHIELUTTI 05MAR04

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

tyco
ElectronicsTyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME

TERMINAL, RING TONGUE, P.I.D.G.,
WIRE SIZE 22-16 AWG

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3


00779

C-151730

SCALE 5:1

SHEET 1 OF 1

REV A

DIMENSIONS:
mmTOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± -
2 PLC ± .02
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL

FINISH

