


1.27mm Female Header

1.27mm x 2.54mm Female Header

- single row -


- dual row -



SPECIFICATIONS

Current rating	1 A
Insulator resistance	5000 MΩ min.
Contact resistance	20 mΩ max.
Dielectric withstanding voltage	500 V AC
Operating temperature	- 40°C to +105°C
Contact material	Phosphor Bronze
Insulator material	Nylon-6T , UL 94 V-0

PCB Hole Layout



APPLICATION AND FEATURES

- Standard & low profile types
- Hi-rel fork contact design
- Mates with 0.46mm square or round Pin Header

How to order

BL x - xxx - S xxx - 11 /1

Rows	Nbr of contacts	Connector style (height above board)	Plating
1 = single row 2 = dual row	<u>connector style 460</u> single row = 003 to 040 dual row = 006 to 100 <u>connector style 850</u> single row = 003 to 036 dual row = 006 to 100	460 = 4.60mm 850 = 8.50mm	11 = gold Others on request