



### Main

Commercial Status	Commercialised
Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch lever
Device short name	ZC2J
Product compatibility	XC2J
Associated head	ZC2JE09
Movement of operating head	Rotary
Type of operator	Stay put forked arm with rollers stay put thermoplastic (1 track)
Type of approach	Lateral approach

### Complementary

Switch actuation	By specific cam
Positive opening	Without

### Environment

Ambient air temperature for operation	-40...158 °F (-40...70 °C) for low temperature -13...158 °F (-25...70 °C) for standard environment
Ambient air temperature for storage	-40...158 °F (-40...70 °C) for low temperature -40...158 °F (-40...70 °C) for standard environment
Environmental characteristic	Low temperature Standard environment

### Ordering and shipping details

Category	22449 - LIMIT SWITCHES,ACCESSORIES
Discount Schedule	T
GTIN	00785901324751
Nbr. of units in pkg.	1
Package weight(Lbs)	0.80
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	N
Country of origin	FR

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will be Compliant on 3Q2013
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available <a href="#">Download Product Environmental</a>
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Period	18 months
--------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZC2JY71](#)