






PRODUCT NO.	FINISH	DIRECTION	PRODUCT NO.	FINISH	DIRECTION
77138-001	②	FIG. 1	△ 77138-001LF	②	FIG. 1
77138-101	⑥	FIG. 1	△ 77138-101LF	⑥	FIG. 1
77138-201	⑤	FIG. 1	△ 77138-201LF	⑤	FIG. 1
77138-001RE	②	FIG. 2	△ 77138-001RELF	②	FIG. 2




⑦ FIG.1



⑦ FIG.2



SECT. A-A



SECT. B-B

NOTES :

- 1 MATERIAL : PHOSPHOR BRONZE
- ② FINISH : SELECTIVE GOLD PLATING $0.2 \mu\text{m}$ MIN. (CONTACT AREA) OVER NICKEL
- 3 WIRE RANGE : AWG #26-#30
INS.DIA. : $\frac{1.4}{.055}$ DIA.MAX.
- 4 GENERAL TOLERANCE : $\pm \frac{0.25}{.010}$
- ⑤ FINISH : SELECTIVE GOLD PLATING $0.5 \mu\text{m}$ MIN. (CONTACT AREA) OVER NICKEL
- ⑥ FINISH : SELECTIVE GOLD PLATING $0.76 \mu\text{m}$ MIN. (CONTACT AREA) OVER NICKEL
- ⑦ SEE FIG. 1, 2 FOR UNREELING DIRECTION AFTER PLATING.
8. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- △ 9. CRIMP SPECIFICATION OF THIS PRODUCT : 100-006

mat'l. code					surface	tolerance	projection	product family	CODE
---					ISO 1302 ✓	ISO 406 ISO 1101		5MTs - MINITEK COMM COMP HPL577	JP
ltr	description	ecn no	dr	date	tolerances unless otherwise specified			title	
C	REVISED PER ECR J8424			5/26/'87	angles	linear			
D	REVISED	J10082	N.Y	8/13/'91					
E	REVISED	J70124	Y.K	5/27/'97					
F	REVISED	J80320	H.T	8/11/'98	dr		mm	MINITEK TERMINAL (AWG#26-#30)	
G	REVISED	J05-0550	R.S	8/31/'05	enr		scale 10:1		
H	REVISED	J06-0352	R.S	8/29/'06	chr				
J	ADD_NOTE9	J07-0092	R.S	2/7/'07	appd				
sheet	revision	J						dwg no	sheet 1 of 1 size
index	sheet	1						77138	A3
								type	Product Customer Drawing
								Rev.	J