


SPECIFICATIONS



Model Number: MX2B2
Part Number: 030519

November 16, 2006

Mechanical Drawing:



Motor:

Nominal Voltage	= 115 VAC
Frequency	= 50 / 60 Hz
Nominal Running Current	= 0.200 / 0.180 Amps
Locked Rotor Current	= 0.280 / 0.270 Amps
Running Power	= 17 / 15 Watts
Average Speed	= 2700 / 3100 RPM
Bearings	= Ball
Air Flow	= 92 / 108 CFM
Acoustic:	= 44.8 / 48.7 dBA

Construction:

Venturi: Zinc Alloy, Black
Propeller: Plastic, Black, UL 94V-0

Life Expectancy:

This fan is designed for continuous duty life of 83,000 hours at 40°C.

Additional Features:

Shaded Pole Induction Motor
Impedance Protected
Feathered Edge Propeller
Operating Temperature:
Storage Temperature:

Termination:

12" Lead wires

Agency Approvals:

UL, CSA, VDE