





PCB THICKNESS: 1.6±0.1

	NIL	NIL	14	7	16	16	5-		-3
	NIL	NIL	38	19	40	40	5-		-2
	5, 16		14	7	16	16	5-		-1
	3, 16		14	7	16	16	5-		-0
	1, 8		6	3	8	8	4-		-9
	NIL		48	24	50	50	4-		-8
			46	23	48	48	4-		-7
			44	22	46	46	4-		-6
			40	20	42	42	4-		-4
			36	18	38	38	4-		-2
			34	17	36	36	4-		-1
			32	16	34	34	4-		-0
			30	15	32	32	3-		-9
			26	13	28	28	3-		-7
			20	10	22	22	3-		-4
			18	9	20	20	3-		-3
			16	8	18	18	3-		-2
			12	6	14	14	3-		-0
			4	2	6	6	2-		-6
		0, 76 μm	2	1	4	4	2-		-5
			48	24	50	50	2-		-4
			46	23	48	48	2-		-3
			44	22	46	46	2-		-2
			42	21	44	44	2-		-1
			40	20	42	42	2-		-0
			38	19	40	40	1-		-9
			36	18	38	38	1-		-8
			30	15	32	32	1-		-5
			28	14	30	30	1-		-4
			24	12	26	26	1-		-2
			16	8	18	18			-8
			14	7	16	16			-7
			12	6	14	14			-6
			10	5	12	12			-5
			8	4	10	10			-4
			6	3	8	8			-3
		0, 2 μm	2	1	4	4	5176837-1		

DIMENSIONS: mm 		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.25 1 PLC ±0.2 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ±		DWN 07MAR2005		 TE Connectivity				
				CHK WYLEE						
GENERAL TOLERANCE 0<* : 10 : ±0.2 10<* : 30 : ±0.25 30<* : 100 : ±0.3 ANGLES : ±3°		MATERIAL 		VINCENT TAN		NAME AMPMODU 2mm PITCH POST HDR, HORIZONTAL TYPE, L=2.6				
				APVD SE L'ONG						
				PRODUCT SPEC						
				APPLICATION SPEC						
FINISH 		WEIGHT		SIZE		CAGE CODE	DRAWING NO			
		-		A2		00779	 5176837			
CUSTOMER DRAWING						SCALE		SHEET	OF	REV
						-			1	