

TIP115 TIP116 TIP117

PNP Epitaxial Silicon Darlington Transistors

Features

- Halogen free available upon request by adding suffix "-HF"
- High DC Current Gain : $h_{FE}=1000$ @ $V_{CE}=4.0V$, $I_C=1.0A$ (Min.)
- Low Collector-Emitter Saturation Voltage
- Complementary to TIP110/111/112
- Lead Free Finish/RoHS Compliant (Note1) ("P" Suffix designates RoHS Compliant. See ordering information)
- Epoxy meets UL 94 V-0 flammability rating

Moisture Sensitivity Level 1

Maximum Ratings

- Mounting Torque: 5 in-lbs Maximum

Symbol	Rating	Rating	Unit
V _{CEO}	Collector-Emitter Voltage TIP115 TIP116 TIP117	60 80 100	V
V _{CBO}	Collector-Base Voltage TIP115 TIP116 TIP117	60 80 100	V
V _{EBO}	Emitter-Base Voltage	5.0	V
I _C	Collector Current (DC)	2.0	A
I _{CP}	Collector Current (Pulse)	4.0	A
I _B	Base Current (DC)	50	mA
P _C	Collector Dissipation @T _A =25°C	2.0	W
	Collector Dissipation @T _C =25°C	50	W
T _{J1}	Junction Temperature	-55 to +150	°C
T _{STG}	Storage Temperature	-55 to +150	°C

Electrical Characteristics @ 25°C Unless Otherwise Specified

Symbol	Parameter	Min	Max	Units
--------	-----------	-----	-----	-------

OFF CHARACTERISTICS


$V_{CEO(SUS)}$	Collector-Emitter Sustaining Voltage ($I_C=30mA$, $I_B=0$)	TIP115 TIP116 TIP117	60 80 100	---	Vdc
I_{CEO}	Collector Cut-off Current ($V_{CE}=30Vdc$, $I_B=0$) ($V_{CE}=40Vdc$, $I_B=0$) ($V_{CE}=50Vdc$, $I_B=0$)	TIP115 TIP116 TIP117	---	2.0 2.0 2.0	mAdc
I_{CBO}	Collector Cut-off Current ($V_{CB}=60Vdc$, $I_E=0$) ($V_{CB}=80Vdc$, $I_E=0$) ($V_{CB}=100Vdc$, $I_E=0$)	TIP115 TIP116 TIP117	---	1.0 1.0 1.0	mAdc
I_{EBO}	Emitter Cut-off Current ($V_{BE}=5.0Vdc$, $I_C=0$)		---	2.0	mAdc

ON CHARACTERISTICS

$h_{FE(1)}$	DC Current Gain ($I_C=1.0A$, $V_{CE}=4.0Vdc$) ($I_C=2.0A$, $V_{CE}=4.0Vdc$)	1000 500	---	---	----
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage ($I_C=2.0A$, $I_B=8.0mA$)	---	2.5		Vdc
$V_{BE(ON)}$	Base-Emitter On Voltage ($I_C=2.0A$, $V_{CE}=4.0Vdc$)	---	2.8		Vdc
C_{ob}	Output Capacitance ($V_{CB}=10V$, $I_E=0$, $f=0.1MHz$)	---	200		pF

Notes:1.High Temperature Solder Exemption Applied, see EU Directive Annex 7.

TO-220



- 1.Base
- 2.Collector
- 3.Emitter

$R1 \approx 10 k\Omega$
 $R2 \approx 0.6 k\Omega$

DIMENSIONS

DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	.560	.625	14.22	15.88	
B	.380	.420	9.65	10.67	
C	.140	.190	3.56	4.82	
D	.020	.045	0.51	1.14	
F	.139	.161	3.53	4.09	Ø
G	.190	.110	2.29	2.79	
H	---	.250	---	6.35	
J	.012	.025	0.30	0.64	
K	.500	.580	12.70	14.73	
L	.045	.060	1.14	1.52	
N	.190	.210	4.83	5.33	
Q	.100	.135	2.54	3.43	
R	.080	.115	2.04	2.92	
S	.045	.055	1.14	1.39	
T	.230	.270	5.84	6.86	
U	---	.050	---	1.27	
V	.045	---	1.15	---	

Ordering Information :

Device	Packing
Part Number-BP	Bulk; 1Kpcs/Box

Note : Adding "-HF" suffix for halogen free, eg. Part Number-BP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.