

Absorbent Specification Guide

www.BradyID.com/SPC

Absorbent Specification Guide

Part Numbers	Type	Size	Perforated	Absorbency Factor (gl/g)	Absorbency Capacity (gal)	Shipping Wt. (lbs)	Pallet Qty.*	Quantity
96229	Spill Magnet	12" dia.	n/a	n/a	n/a	1	100	1/each
AW99	Pillow	9"x9"	n/a	12.5	14	10	40	32/case
AW124	SOC	3"x12'	n/a	9	12	12	40	4/case
AW412	SOC	3"x4'	n/a	9	12	12	40	12/case
AW430	SOC	3"x4'	n/a	9	30	26	20	30/case
AW806	SOC	3"x8'	n/a	9	12	12	40	6/case
AW1818	Pillow	18"x18"	n/a	12.5	28	19	20	16/case
AW1818-2	Pillow	18"x18"	n/a	12.5	14	9.5	40	8/case
BM15	Heavy Wt. Roll	15"x150'	Yes, 7.5" and 12" across	12.5	25	17	30	1/case
BM30	Heavy Wt. Roll	30"x150'	Yes, 15" and every 15"	12.5	52	34.5	12	1/case
BM30X	Heavy Wt. Roll	30"x150'	No	12.5	52	34.5	12	1/case
BM100	Heavy Wt. Pad	15"x19"	Yes, 7.5"	12.5	27.5	16.5	40	100/bale
BPO100	Heavy Wt. Pad	15"x17"	Yes, 7.5"	18	20.5	8.5	30	100/bale
BPO200	Light Wt. Pad	15"x17"	Yes, 7.5"	18	34	13.7	18	200/bale
BPO500	Light Wt. Pad	15"x17"	Yes, 7.5"	18	17	7	30	100/bale
BPU100	Heavy Wt. Pad	15"x17"	Yes, 7.5"	18	20.5	8.5	30	100/bale
BPU200	Light Wt. Pad	15"x17"	Yes, 7.5"	18	34	13.7	18	200/bale
BPU500	Light Wt. Pad	15"x17"	Yes, 7.5"	18	17	7	30	100/bale
BRO150	Heavy Wt. Roll	30"x150"	Yes, every 30"	14.5	38	19.5	18	1/bale
BRU150	Heavy Wt. Roll	30"x150"	Yes, every 30"	14.5	38	19.5	18	1/bale
BSC20	SOC	3"x42"	n/a	15	84	24	20	20/case
BSC40	SOC	3"x42"	n/a	15	81	47.5	16	40/case
BSCSK-CB	BASIC Vehicle Spill Kit	n/a	n/a	n/a	7.75	7	50	1/each
BSM100	Medium Wt. Rug	36"x100'	No	8	25	24	40	1/bale
BSM300	Medium Wt. Rug	36"x300'	No	8	74	67	12	1/bale
BSM3650	Medium Wt. Rug	36"x50'	No	8	12	12	40	1/case
CB305	Boom	3" Float, 4.5" Skirt, 25' Sections	n/a	n/a	n/a	22.5	11	1/case
CB612	Boom	6" Float, 12" Skirt, 100' Sections	n/a	n/a	n/a	200	3	1/case
CC400	SOC	3"x4'	n/a	8.5	8.5	29	32	12/case
CC440V	SOC	3"x4'	n/a	8.5	56	30	16	40/case
CH15P	Medium Wt. Roll	15"x150'	Yes, every 18"	12.5	30	14	30	1/bale
CH30DP	Medium Wt. Roll	30"x150'	Yes, every 15" and up center	12.5	40	25	12	1/case
CH100	Medium Wt. Pad	15"x19"	Yes, 7.5"	18	30	16	30	100/case
CH1212	Medium Wt. Pad	12"x12"	No	18	30	14.5	30	200/case
CH1212-50	Medium Wt. Pad	12"x12"	No	12.5	7.5	4	120	50/case
CS-CB18	Oil Only Granular	18 lbs	n/a	8	18	1000	50	1 pallet
CS-LFB10	Oil Only Granular	10 lbs	n/a	8	10	640	64	1 pallet
DGUARD9	Drain Guard	36" X 48" X 18"	n/a	n/a	0.9	1	36	1/case
DGUARD14	Drain Guard	36" X 48" X 18"	n/a	n/a	1.4	2	36	1/case
DGUARD910	Drain Guard	36" X 48" X 18"	n/a	n/a	9	10	20	10/case
DGUARD1410	Drain Guard	36" X 48" X 18"	n/a	n/a	14	20	20	10/case
DPA24	Drip Pan	10"x10"	n/a	n/a	n/a	6	20	24/case
DTA25	Medium Wt. Drum Cover	22" dia.	n/a	12.5	6	6	48	25/case
DTO25	Medium Wt. Drum Cover	22" dia.	n/a	12.5	6	6	48	25/case
DZ-100	Universal Granular	40 lbs	n/a	1.5	8.5	1600	40	1 pallet
ENV50	Medium Wt. Pad	30"x30"	No	20	50	19	7	50/bale
ENV100	Heavy Wt. Pad	15"x19"	No	20	33	12.5	24	100/bale
ENV150	Medium Wt. Roll	30"x150'	No	15	44	22	18	1/bale
ENV200	Light Wt. Pad	15"x19"	No	23	51	16	18	200/bale
ENV300	Medium Wt. Pad	15"x19"	No	20	28	10	24	100/bale
ENV500	Light Wt. Pad	15"x19"	No	23	24.5	8	30	100/bale
ENV510	ENV Boom	5"x10'	n/a	12.6	32	19	20	4/bale
ENV810	ENV Boom	8"x10'	n/a	13	65	38	10	4/bale

* In an effort to reduce shipping costs for our customers, pallet quantities may vary.

DISCLAIMER: The above properties are "nominal" values used for PROCESS CONTROL when the product is produced and/or inspected. Performance "nominals" may vary depending upon the specific application, and/or the environment being applied, stored, or shipped. The "Absorbency" Spec and "SPCTM004" test method is based on the protocol of ASTM F726, using SAE20 non-detergent as the Oil Type, medium viscosity.