





TAPING SPECIFICATIONS
(rear side of tape)



PART NO.*

COLOR

597-7701-2xx Red/Green

597-7721-2xx Yellow/Green

Features

- Compatible with automatic placement equipment
- Compatible with infrared reflow processes
- Packaged on 8mm tape, 7" reels (meets EIA-481-1 standard)
- Helps to eliminate mixed technology PC board processing
- Compatible with Dialight's Optopipe™ Series light pipes

***ORDERING INFORMATION**

597-77x1-2xx

packaging option →

02	20 pieces on tape
07	7" reel, 1500 pcs/reel

ABSOLUTE MAXIMUM RATINGS ($T_A=25^\circ\text{C}$)


	Red/Green -7701	Yellow/Green -7721
Power Dissipation (mW)	100/100	60/100
Forward Current (mA)	30/30	20/30
Derating (mA/°C) From 50°C	.6/.6	.4/.6
Peak Current (mA)	120/120	80/100
Pulse width 10 μs		
Operating Temperature (°C)	-55/+100	-55/+100
Storage Temperature (°C)	-55/+100	-55/+100
Soldering Profile	235°C peak 15 seconds, 185° for 90 seconds	

Solder Adherence per MIL-STD-202E, Method 208C


OPERATING CHARACTERISTICS ($T_A=25^\circ\text{C}$)

		Red/Green -7701	Yellow/Green -7721
Luminous Intensity (mcd)	Min.	8/8	8/8
	Typical	16/16	16/16
Peak Wavelength (nm)	Typical	630/565	585/565
λ_{Peak}			
Viewing Angle ($2\theta_{1/2}$)	Typical	120°	120°
Forward Voltage (V)	Typical	2/2.1	1.8/2.1
	Max.	2.6/2.6	2.7/2.6

$\theta_{1/2}$ is the off axis angle at which the luminous intensity is half the axial luminous intensity



TAPING SPECIFICATIONS
(rear side of tape)



Features

- Compatible with automatic placement equipment
- Compatible with infrared reflow processes
- Packaged on 8mm tape, 7" reels (meets EIA-RS-481-1 standard)
- Helps to eliminate mixed technology PC board processing
- Compatible with Dialight's Optopipe™ Series light pipes

PART NO.*

597-7731-2xx
597-7741-2xx
597-7761-2xx

COLOR

Red/Yellow
Orange/Green
Orange/
Pure Green

NEW

NEW

***ORDERING INFORMATION**

597-77x1-2xx

packaging option

02	20 pieces on tape
07	7" reel, 2000 pcs/reel

ABSOLUTE MAXIMUM RATINGS ($T_A=25^\circ\text{C}$)

	Red/Yellow -7731	Orange/Green -7741	Orange/Pure Green -7761
Power Dissipation (mW)	100/100	100/100	100/100
Forward Current (mA)	30/30	30/30	30/30
Derating (mA/°C) From 55°C	.66/.66	.66/.66	.66/.66
Peak Current (mA)	500	500	500
Pulse width 10 μs			
Operating Temperature (°C)	-55/+100	-55/+100	-55/+100
Storage Temperature (°C)	-55/+100	-55/+100	-55/+100
Soldering Profile	235°C peak 15 seconds, 185° for 90 seconds		

Solder Adherence per MIL-STD-202E, Method 208C

OPERATING CHARACTERISTICS ($T_A=25^\circ\text{C}$)

		Red/Yellow -7731	Orange/Green -7741	Orange/Pure Green -7761
Luminous Intensity (mcd)	Min.	2.5/2.5	4/4	2.5/2.5
	Typical	7.3/6.8	8/8	5/5
Peak Wavelength (nm)	Typical	635/586	610/565	610/557
λ_{Peak}				
Viewing Angle ($2\theta_{1/2}$)	Typical	120°	120°	120°
Forward Voltage (V)	Typical	2/2	2/2	2/2
	Max.	2.6/2.6	2.6/2.6	2.6/2.6
Reverse Voltage (V), $I_R=10\mu\text{A}$	Min.	5	5	5

$\theta_{1/2}$ is the off axis angle at which the luminous intensity is half the axial luminous intensity