

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20




© COPYRIGHT 20

BY -



ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	J	REV. BY ECO 17-008400	23JUN2017	HC	WLS



- 1 -PEÇA SOLTA - VER DESENHO 444201.
LOOSE PIECE - SEE DRAWING 444201.
- 2 -LOCALIZAÇÃO DO DIMPLE - 3,0mm PARA O PN 1-881623-0
DIMPLE LOCATION 3,0mm. FOR PN 1-881623-0.
- 3 -OBSOLETE PARTS:OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 4 -HEAT TREATMENT.



OBSOLETE

OBSOLETE




0,5	—	LATÃO/BRASS	4 1-881623-1
0,8	—	LATÃO/BRASS	2 1-881623-0
0,5	ESTANHADO/TIN PLATED	LATÃO/BRASS	1 881623-9
0,5	—	LATÃO/BRASS	1 881623-8
OBSOLETE	ESTANHADO/TIN PLATED	LATÃO/BRASS	881623-7
OBSOLETE	—	LATÃO/BRASS	881623-6
0,8	NIQUELADO/NICKEL PLATED	AÇO/STEEL	881623-5
0,8	—	AÇO/STEEL	881623-4
0,8	ESTANHADO/TIN PLATED	BRONZE/PH.BRONZE	881623-3
0,8	ESTANHADO/TIN PLATED	LATÃO/BRASS	1 881623-2
0,8	—	LATÃO/BRASS	1 881623-1
5 FOR TAB THICKNESS		FINISH	MATERIAL
			PART NUMBER

INSERTION AND EXTRACTION REQUIREMENTS	1st ON (N)MAX	1st OFF (N)MIN	6th ON (N)MIN
	46	28	15

Ø 2,0-3,3mm.	0,5-1,0mm2
INS. RANGE	WIRE RANGE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±0,3
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±1°

MATERIAL
SEE TABLE

FINISH
SEE TABLE

DWN 20JUN2017

H.C.CANTER

CHK 26JUN2017

W.L.STEFANI

APVD -

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME
.187 SERIES FASTON REC.

-

-

SIZE

A3

CAGE CODE

-

DRAWING NO

©-881623

RESTRICTED TO

-

SCALE 5/1

SHEET 1 OF 1

REV J