










Walzrichtung
direction of rolling



Merkmal feature	FCI Nr. FCI no.
① FCI-Firmenzeichen / FCI-Supplier code	-
② Teile Code / Part code	9 909 12 90
③ Oberflaechenangabe / Surface finish Sn = Zinn / Tin; Ag = Silber / silver oder/lor Woche und Jahr der Herstellung / Week and year of production Jahr / Year: 2012=0; 2013=P; 2014=R; 2015=S...	9 909 12 90
④ Masz fuer Vereinzelung - nur gueltig fuer Kabelkonfektionierer Dimension for separating - only valid for the Harnessmaker	-
⑤ Laserschweisspunkte / Laser welding points	-
Material	-
6 Grundkoerper / Contact Body: CuCrSiTi (K75)	-
7 Ueberfeder / Hood X10 CrNi I8 8 Oberflaeche blank / surface blanc	-
Querverweise / Cross references	-
8 Ausfuehrungsvorschrift fuer Flachstecker design order for male contact 1.2-0.06 x 9.5±0.1	9 019 00 09
9 zugehoerige Kammer / associated cavity - Ø 12.1±0.1	9 007 01 00 9 007 02 00
10 Crimpspezifikation / Crimpspecification	9 084 16 00
11 Produktspezifikation / product specification	9 901 11 40
Der Kontakt ist geeignet fuer nicht wasserdichte und wasserdichte (EAA) Anwendung. EAA gemass FCI Zeichnung verwenden. (siehe Tabelle) The terminal is suitable for non waterproof and waterproof application (SWS). Use SWS according FCI-drawing. (see table)	6 099 33 01
Toleranzen / Tolerances:	-
13 DIN ISO 2768-fH; Masze / Dimensions <0.5 = ±0.05	-
14 DIN EN ISO 1101	-
15 Haltestreifen unten. / Reels transported and stored horizontally! Retaining strip down.	-
16 Unterbrechungen am Band zulassig! 2 separations at strip allowed! Separations are maked	-
①7 Teilernr. nicht fuer Neuanwendungen erlaubt Part no. not allowed for new applications	-
①8 Die Verwendung der Einzeldichtungen ist abhaengig vom Isolations-Ø der Leitung und nicht vom Leitungsquerschnitt The application of single wire seals is depends on the insulation-Ø of the wire only not from the wire section	-
Abweichungen von der bildlichen Darstellung im Bereich der Ueberfeder sind zulassig. Deviations from the pictorial representation in the area of spring are allowed	-
19 Aenderungen die dem technischen Fortschritt dienen, behalten wir uns vor. changes reference to the technical progress, we reserve the right.	-
20 Massgebend ist nur der deutsche Text Only the german language shall be binding	-

F292210	A	1.2-3.5µm Ag		3B	7.0	4.0	7.2	10.6	6.4	10.3	26.5	6 099 33 03	rot/red	5.8- 6.5
F682210	A	1-3µm Sn		3A	7.0	4.0	7.2	10.6	6.4	10.3	26.5	6 099 33 04	gelb/yellow	5.4- 6.6
6 007 04 72 ①7	C	1.2-3.5µm Ag	>6.0-10.0	□□	7.0	4.0	7.2	10.6	6.4	10.3	26.0	6 099 33 01	schwarz/black	3.5- 5.5
6 007 04 71 ①7	C	1-3 µm Sn		□□	7.0	4.0	7.2	10.6	6.4	10.3	26.0			
F192210	A	1.2-3.5µm Ag		2B	5.4	2.8	5.8	8.0	4.2	8.4	26.5	6 099 33 01	schwarz/black	3.5-5.5
F582210	A	1-3 µm Sn	4.0-6.0	2A	5.4	2.8	5.8	8.0	4.2	8.4	26.5	6 099 33 08	gruen/green	3.4-4.4
6 007 04 62 ①7	C	1.2-3.5µm Ag		□	5.4	2.8	5.8	8.0	4.2	8.4	26.0	6 099 33 08	gruen/green	3.4-4.4
6 007 04 61 ①7	C	1-3 µm Sn		□	5.4	2.8	5.8	8.0	4.2	8.4	26.0			
6 007 04 52	C	1.2-3.5µm Ag	>2.5-4.0	□	5.0	2.3	5.6	7.0	3.8	7.0	26.0	6 099 33 01	schwarz/black	3.5-5.5
6 007 04 51	C	1-3µm Sn		□	5.0	2.3	5.6	7.0	3.8	7.0	26.0	6 099 33 08	gruen/green	3.4-4.4
6 007 10 42	C	1.2-3.5µm Ag	>1.5- 2.5	△	4.3	2.0	4.4	7.0	3.8	7.0	26.0	6 099 33 05	Blau/Blue	2.7-3.0
6 007 10 41	C	1-3µm Sn		△	4.3	2.0	4.4	7.0	3.8	7.0	26.0			
Teile Nr. Part no.	Rev.	Oberflaeche Surface finish	Crimp- bereich Crimp area (mm²)	Teile- code Part code	B1 ±0.3	D1 ±0.3	H1 ±0.3	B2 ±0.3	D2 ±0.3	H2 ±0.3	L1	Teile Nr. Part no.	Farbe colour	Isolation-Ø insulation-Ø (mm)
Anwendung mit Einzeldichtung/ application with single wire seal ①8														

11-00090-5	-	REV."G" - 15.10.12: Changed note no. 17 was "crossed out part no."		
11-00090-4	-	REV."F" - 13.06.12: Changed: part code 14x1; rework of the compl. table "feature"		
11-00090-1	-	REV."E" - 11.10.11: added: new parts 14x1; column 2 added; added: column L1 changed: no. 019 was 26.0; added: in Note 3 week and year of production		
ECN-NO. ECN-NUMBER	POSITION POSITION	CHANGE DESCRIPTION ÄNDERUNGSBESCHREIBUNG		
PRODUCT SPEC. PROD.-SPEC.	PACKAGING SPEC. VERPACKUNGS-SPEC.	APPLICATION SPEC. ANWENDUNGS-SPEC.	THIS DRAWING AND ALL OTHER INFORMATION CONTAINED THEREIN IS THE PROPERTY OF FCI. Any drawing and/or material, not be copied, reproduced or disclosed to any third party without the express written permission of FCI. © FCI April 1999	
TOLERANCES TOLERANZEN	siehe Tabelle see table	MATERIAL : see table	ÜBERFLÄCHE see table	ISO PROJECTION ISO PROJEKTION
CONVERSION N. UMRECHNUNG N.	---	COLOR : see table	see table	DIMENSION IN MILLIMETERS MESSUNG IN MILLIMETER
DO NOT MEASURE ZEICHNUNG NICHT MESSSEN	DATE DATUM	NAME NAME	TITLE BEZUGSNAME	ECO LVL : STANDARD CODE : GN
CREATED BY GEZEIGT VON	2001-05-16	ST. MAUELEN	PROJECT PROJEKT	95 Boxterminal - DCSI
CHECKED BY GEPRÜFT VON	2001-05-16	Sylvia WEISS	PROJECT PROJEKT	non waterproof / waterproof
APPROVED BY GEBILDET VON	2001-05-16	Franz MAUELEN	PROJECT PROJEKT	non waterproof / waterproof
FILE NAME DOK.-NAME	60070451C			
STATUS STATUS	---			
PART NUMBER TEILENUMMER	---			
See Table				