



Technical drawing of a mechanical part showing dimensions: 2,1 ± 0,2, 5,0, 8,4, and 23,6.



1 Noryl (UL94-VI) Colore Nero (Black Colour).

2 Tolleranza non Cumulativa.
(Non-Cumulative Tolerance.)

3 PA 6.6 15% g.f. masterizzato ROSSO
(PA 6.6 15% g.f. masterized - RED)

4 OBSOLETE PARTS: OBSOLETE CIS
STREAMLINING PER D.RENAUD/D.SINISI

4 OBSOLETE OBSOLETE	4	284072-1	7,62	12,5			3
	2	284071-1	2,54	7,4			
	22	280636	53,34	58,2			
	15	280635	35,56	40,4			
	12	280634	27,94	32,8			
	10	280633	22,86	27,7			
	9	280632	20,32	25,1			
	8	280631	17,78	22,6			
	6	280630	12,70	17,5			
	4	280629	7,62	12,5			
2	280628	2,54	7,4			1	
N ^o Pos.	Part. Number	Dim. "A "	Dim. " B "				Mat.

o (Black Colour).

tiva.

nce.)

izzato Rosso

rized - RED)

OLETE CIS

ENAUD/D.SINISI

				FINITURA / COLORE (FINISH / COLOUR)		MATERIALE (MATERIAL)		NUMERO (PART NUMBER)	
				CUSTOMER DWG. FOR REFERENCE ONLY			DISEGNO PER CLIENTE SOLO PER RIFERIMENTO		
				THIS DRAWING IS UNPUBLISHED		RELEASE FOR PUBLICATION			
				© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA ALL INTERNATIONAL RIGHT RESERVED AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING					
				TOLLERANZE: SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES UNLESS OTHERWISE SPECIFIED)		DIAM. ISOLANTE (INS. DIA. RANGE)		RANGO FILO (WIRE RANGE)	
				$\pm 0,3$				SCALA (SCALE) 5:1	
H3 REVISED PER ECO-10-000445 KK JAN10				ANGOLI (ANGLES) $\pm 2^\circ$		AMP AMP ITALIA S.p.A. Corso F.lli Cervi, 15 COLLEGNO (TORINO)			
H2 RELEASED FOR PRODUCTION P/N 3284071-13 284072-1 ETD-0101				DIS. (DR.)		DESCRIZIONE (DESCRIPTION)			
H1 Appl. P/N 284071-1 284072-1 Appl. P/N 284071-1 284072-1				Bassano 29 th 9-86		AMP MODU II Pin Housing, Single Row, Crimp Snap-In.			
2 Revised note				CONT. (CHK)		LOC. SIZE		NUMERO (DWG NO)	
1 Revised and Redrawn				APP. (APP)		1 A3 C- (Master Dwg.)		REV. H3	
REV. REVISIONI (REV LTR) (REVISION RECORD)				DIS. DATA (DR) (DATE)		1 A3 C- (Master Dwg.)		FOGLIO (SHEET) DI 1 OF 1	