



N-Channel 20-V (D-S) MOSFET

PRODUCT SUMMARY		
V_{DS} (V)	$r_{DS(on)}$ (Ω)	I_D (mA)
20	5 @ $V_{GS} = 4.5$ V	200
	7 @ $V_{GS} = 2.5$ V	175
	9 @ $V_{GS} = 1.8$ V	150
	10 @ $V_{GS} = 1.5$ V	50

TrenchFET®

MOSFETs

1.5-V Rated



**ESD Protected
2000 V**

FEATURES


- Low-Side Switching
- Low On-Resistance: 5 Ω
- Low Threshold: 0.9 V (typ)
- Fast Switching Speed: 35 ns
- 1.8-V Operation
- Gate-Source ESD Protection

BENEFITS

- Ease in Driving Switches
- Low Offset (Error) Voltage
- Low-Voltage Operation
- High-Speed Circuits
- Low Battery Voltage Operation

APPLICATIONS

- Drivers: Relays, Solenoids, Lamps, Hammers, Displays, Memories
- Battery Operated Systems
- Power Supply Converter Circuits
- Load/Power Switching Cell Phones, Pagers



Ordering Information:

SC-75A (SOT-416): Si1032R-T1
 SC-75A (SOT-416): Si1032R-T1—E3 (Lead Free)
 SC-89 (SOT-490): Si1032X-T1
 SC-89 (SOT-490): Si1032X-T1—E3 (Lead Free)

Marking Code: G

ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)

Parameter		Symbol	Si1032R		Si1032X		Unit
			5 secs	Steady State	5 secs	Steady State	
Drain-Source Voltage		V _{DS}	20				V
Gate-Source Voltage		V _{GS}	± 6				
Continuous Drain Current (T _J = 150°C) ^a	T _A = 25°C	I _D	200	140	210	200	mA
	T _A = 85°C		110	100	150	140	
Pulsed Drain Current ^a		I _{DM}	500		600		
Continuous Source Current (diode conduction) ^a		I _S	250	200	300	240	
Maximum Power Dissipation ^a for SC-75	T _A = 25°C	P _D	280	250	340	300	mW
	T _A = 85°C		145	130	170	150	
Operating Junction and Storage Temperature Range		T _J , T _{stg}	-55 to 150				°C
Gate-Source ESD Rating (HBM, Method 3015)		ESD	2000				V

Notes



c. Surface Mounted on FR4 Board.

SPECIFICATIONS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Static						
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}$, $I_D = 250\ \mu\text{A}$	0.40	0.7	1.2	V
Gate-Body Leakage	I_{GSS}	$V_{DS} = 0\ \text{V}$, $V_{GS} = \pm 2.8\ \text{V}$		± 0.5	± 1.0	μA
		$V_{DS} = 0\ \text{V}$, $V_{GS} = \pm 4.5\ \text{V}$		± 1.0	± 3.0	
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = 20\ \text{V}$, $V_{GS} = 0\ \text{V}$			1	
		$V_{DS} = 20\ \text{V}$, $V_{GS} = 0\ \text{V}$, $T_J = 55^\circ\text{C}$			10	
On-State Drain Current ^a	$I_{D(on)}$	$V_{DS} = 5\ \text{V}$, $V_{GS} = 4.5\ \text{V}$	250			mA
Drain-Source On-State Resistance ^a	$r_{DS(on)}$	$V_{GS} = 4.5\ \text{V}$, $I_D = 200\ \text{mA}$			5	Ω
		$V_{GS} = 2.5\ \text{V}$, $I_D = 175\ \text{mA}$			7	
		$V_{GS} = 1.8\ \text{V}$, $I_D = 150\ \text{mA}$			9	
		$V_{DS} = 1.5\ \text{V}$, $I_D = 40\ \text{mA}$			10	
Forward Transconductance ^a	g_{fs}	$V_{DS} = 10\ \text{V}$, $I_D = 200\ \text{mA}$		0.5		S
Diode Forward Voltage ^a	V_{SD}	$I_S = 150\ \text{mA}$, $V_{GS} = 0\ \text{V}$			1.2	V
Dynamic^b						
Total Gate Charge	Q_g	$V_{DS} = 10\ \text{V}$, $V_{GS} = 4.5\ \text{V}$, $I_D = 150\ \text{mA}$		750		pC
Gate-Source Charge	Q_{gs}			75		
Gate-Drain Charge	Q_{gd}			225		
Turn-On Delay Time	$t_{d(on)}$	$V_{DD} = 10\ \text{V}$, $R_L = 47\ \Omega$ $I_D \cong 200\ \text{mA}$, $V_{GEN} = 4.5\ \text{V}$, $R_G = 10\ \Omega$			50	ns
Rise Time	t_r				25	
Turn-Off Delay Time	$t_{d(off)}$				50	
Fall Time	t_f				25	

Notes


- a. Pulse test; pulse width $\leq 300\ \mu\text{s}$, duty cycle $\leq 2\%$.
b. Guaranteed by design, not subject to production testing.

TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ UNLESS NOTED)




TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ UNLESS NOTED)


On-Resistance vs. Drain Current




Capacitance




Gate Charge




On-Resistance vs. Junction Temperature







Source-Drain Diode Forward Voltage



On-Resistance vs. Gate-to-Source Voltage



TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ UNLESS NOTED)





Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[SI1032R-T1](#) [SI1032X-T1](#) [SI1032R-T1-E3](#) [SI1032X-T1-E3](#)