

# DATA SHEET

For a complete data sheet, please also download:

- The IC04 LOCMOS HE4000B Logic Family Specifications HEF, HEC
- The IC04 LOCMOS HE4000B Logic Package Outlines/Information HEF, HEC

## HEF40244B

### buffers

### Octal buffers with 3-state outputs

Product specification  
File under Integrated Circuits, IC04

January 1995

Octal buffers with 3-state outputs



HEF40244B  
buffers

DESCRIPTION

The HEF40244B is an octal non-inverting buffer with 3-state outputs. It features output stages with high current output capability suitable for driving highly capacitive loads.

The 3-state outputs are controlled by the output enable inputs  $\overline{EO}_A$  and  $\overline{EO}_B$ . A HIGH on  $\overline{EO}$  causes the outputs to assume a high impedance OFF-state. The device also features hysteresis on all inputs to improve noise immunity. Schmitt-trigger action in the inputs makes the circuit highly tolerant to slower input rise and fall times.

The HEF40244B is pin and functionally compatible with the TTL '244' device.



HEF40244BP(N): 20-lead DIL; plastic (SOT146-1)  
HEF40244BD(F): 20-lead DIL; ceramic (cerdip) (SOT152)  
HEF40244BT(D): 20-lead SO; plastic (SOT163-1)  
( ): Package Designator North America

PINNING


$I_{A1}$  to  $I_{A4}$  inputs  
 $I_{B1}$  to  $I_{B4}$  inputs  
 $O_{A1}$  to  $O_{A4}$  bus outputs  
 $O_{B1}$  to  $O_{B4}$  bus outputs  
 $\overline{EO}_A$ ,  $\overline{EO}_B$  output enable inputs (active LOW)

FAMILY DATA,  $I_{DD}$  LIMITS category buffers

See Family Specifications

Octal buffers with 3-state outputs

HEF40244B  
buffers



TRUTH TABLE

| INPUTS         |                 | OUTPUT         |
|----------------|-----------------|----------------|
| I <sub>n</sub> | $\overline{EO}$ | O <sub>n</sub> |
| H              | L               | H              |
| L              | L               | L              |
| X              | H               | Z              |

Notes

- 1. H = HIGH state (the more positive voltage)
- L = LOW state (the less positive voltage)
- X = state is immaterial
- Z = high impedance off state

RATINGS

Limiting values in accordance with the Absolute Maximum System (IEC 134).  
See Family Specifications, except for:

|                                             |           |      |        |
|---------------------------------------------|-----------|------|--------|
| D.C. current into any input                 | $\pm I_i$ | max. | 10 mA  |
| D.C. source or sink current into any output | $\pm I_o$ | max. | 25 mA  |
| D.C. current into the supply terminals      | $\pm I$   | max. | 100 mA |



DC CHARACTERISTICS

V<sub>SS</sub> = 0 V

|                                      | V <sub>DD</sub><br>V | V <sub>OH</sub><br>V | V <sub>OL</sub><br>V | SYMBOL           | T <sub>amb</sub> (°C) |      |      |      |      |      |
|--------------------------------------|----------------------|----------------------|----------------------|------------------|-----------------------|------|------|------|------|------|
|                                      |                      |                      |                      |                  | -40                   |      | +25  |      | +85  |      |
|                                      |                      |                      |                      |                  | MIN.                  | TYP. | MIN. | TYP. | MIN. | TYP. |
| Output current<br>HIGH               | 5                    | 4,6                  |                      | -I <sub>OH</sub> | 0,75                  |      | 0,6  | 1,2  | 0,45 | mA   |
|                                      | 10                   | 9,5                  |                      |                  | 1,85                  |      | 1,5  | 3,0  | 1,1  | mA   |
|                                      | 15                   | 13,5                 |                      |                  | 14,5                  |      | 15   | 50   | 15,5 | mA   |
| Output current<br>HIGH               | 5                    | 3,6                  |                      | -I <sub>OH</sub> | 9,3                   |      | 10   | 24   | 10,7 | mA   |
|                                      | 10                   | 8,4                  |                      |                  | 14,4                  |      | 15   | 46   | 15,0 | mA   |
|                                      | 15                   | 13,2                 |                      |                  | 19,5                  |      | 20   | 62   | 19,8 | mA   |
| Output current<br>LOW                | 5                    |                      | 0,4                  | I <sub>OL</sub>  | 2,9                   |      | 2,3  | 5,4  | 1,75 | mA   |
|                                      | 10                   |                      | 0,5                  |                  | 9,5                   |      | 7,6  | 17   | 5,50 | mA   |
|                                      | 15                   |                      | 1,5                  |                  | 30,0                  |      | 25   | 45   | 19,0 | mA   |
| Hysteresis<br>voltage<br>(any input) | 5                    |                      |                      | V <sub>H</sub>   |                       |      | 220  |      |      | mV   |
|                                      | 10                   |                      |                      |                  |                       |      | 250  |      |      | mV   |
|                                      | 15                   |                      |                      |                  |                       |      | 320  |      |      | mV   |

Octal buffers with 3-state outputs

HEF40244B  
buffers



AC CHARACTERISTICS

$V_{SS} = 0\text{ V}$ ;  $T_{amb} = 25\text{ }^{\circ}\text{C}$ ; input transition times  $\leq 20\text{ ns}$

| ALL BUFFERS SWITCHING                     | $V_{DD}$<br>V | TYPICAL FORMULA FOR P ( $\mu\text{W}$ )                                                                                                              |                                                                                                                                                                         |
|-------------------------------------------|---------------|------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Dynamic power dissipation per package (P) | 5<br>10<br>15 | $4\,250\,f_i + \sum (f_o C_L) \times V_{DD}^2$<br>$17\,000\,f_i + \sum (f_o C_L) \times V_{DD}^2$<br>$46\,000\,f_i + \sum (f_o C_L) \times V_{DD}^2$ | where<br>$f_i$ = input freq. (MHz)<br>$f_o$ = output freq. (MHz)<br>$C_L$ = load capacitance (pF)<br>$\sum (f_o C_L)$ = sum of outputs<br>$V_{DD}$ = supply voltage (V) |

## Octal buffers with 3-state outputs

HEF40244B  
buffers

## AC CHARACTERISTICS

 $V_{SS} = 0\text{ V}$ ;  $T_{amb} = 25\text{ }^{\circ}\text{C}$ ;  $C_L = 50\text{ pF}$ ; input transition times  $\leq 20\text{ ns}$ 

|                                         | V <sub>DD</sub><br>V | SYMBOL           | MIN. | TYP. | MAX. | TYPICAL EXTRAPOLATION<br>FORMULA |                                     |
|-----------------------------------------|----------------------|------------------|------|------|------|----------------------------------|-------------------------------------|
| Propagation delays                      |                      |                  |      |      |      |                                  |                                     |
| I <sub>An/Bn</sub> → O <sub>An/Bn</sub> | 5                    | t <sub>PHL</sub> |      | 95   | 190  | ns                               | 83 ns + (0,24 ns/pF) C <sub>L</sub> |
| HIGH to LOW                             | 10                   |                  |      | 40   | 80   | ns                               | 35 ns + (0,10 ns/pF) C <sub>L</sub> |
|                                         | 15                   |                  |      | 30   | 60   | ns                               | 26 ns + (0,07 ns/pF) C <sub>L</sub> |
| I <sub>An/Bn</sub> → O <sub>An/Bn</sub> | 5                    | t <sub>PLH</sub> |      | 85   | 170  | ns                               | 82 ns + (0,06 ns/pF) C <sub>L</sub> |
| LOW to HIGH                             | 10                   |                  |      | 40   | 80   | ns                               | 38 ns + (0,03 ns/pF) C <sub>L</sub> |
|                                         | 15                   |                  |      | 30   | 60   | ns                               | 29 ns + (0,02 ns/pF) C <sub>L</sub> |
| Output transition times                 | 5                    | t <sub>THL</sub> |      | 40   | 80   | ns                               | see Fig.6                           |
| HIGH to LOW                             | 10                   |                  |      | 20   | 40   | ns                               |                                     |
|                                         | 15                   |                  |      | 15   | 30   | ns                               |                                     |
| LOW to HIGH                             | 5                    | t <sub>TLH</sub> |      | 30   | 60   | ns                               |                                     |
|                                         | 10                   |                  |      | 20   | 40   | ns                               |                                     |
|                                         | 15                   |                  |      | 15   | 30   | ns                               |                                     |
| 3-state propagation delays              |                      |                  |      |      |      |                                  |                                     |
| Output disable times                    |                      |                  |      |      |      |                                  |                                     |
| EO̅ → O <sub>An/Bn</sub>                | 5                    | t <sub>PHZ</sub> |      | 70   | 140  | ns                               |                                     |
| HIGH                                    | 10                   |                  |      | 35   | 70   | ns                               |                                     |
|                                         | 15                   |                  |      | 30   | 60   | ns                               |                                     |
| LOW                                     | 5                    | t <sub>PLZ</sub> |      | 75   | 150  | ns                               |                                     |
|                                         | 10                   |                  |      | 40   | 80   | ns                               |                                     |
|                                         | 15                   |                  |      | 30   | 60   | ns                               |                                     |
| Output enable times                     |                      |                  |      |      |      |                                  |                                     |
| EO̅ → O <sub>An/Bn</sub>                | 5                    | t <sub>PZH</sub> |      | 80   | 160  | ns                               |                                     |
| HIGH                                    | 10                   |                  |      | 35   | 70   | ns                               |                                     |
|                                         | 15                   |                  |      | 30   | 60   | ns                               |                                     |
| LOW                                     | 5                    | t <sub>PZL</sub> |      | 90   | 180  | ns                               |                                     |
|                                         | 10                   |                  |      | 40   | 80   | ns                               |                                     |
|                                         | 15                   |                  |      | 30   | 60   | ns                               |                                     |

Octal buffers with 3-state outputs

HEF40244B  
buffers




Fig.6 Output transition times as a function of the load capacitance.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NXP:

[HEF40244BP,652](#) [HEF40244BT,652](#) [HEF40244BT,653](#)