

E-T-A® Thermal Overcurrent Circuit Breaker 1658-...

Description

Very cost effective design to meet international requirements. No exposed metal parts which are, or could become, current-carrying except for terminals. R-type TO CBE to EN 60934.

- Manual reset, cycling trip free mechanism
- Extremely small and lightweight
- UL, CSA, VDE and EN 60934 (IEC 60934) approved

Typical applications

Battery chargers, consumer products, power supplies, motors.

Ordering information

Type No.

1658 single pole thermal circuit breaker

Threadneck design

G21 manual reset type, 3/8"-27 threadneck

G41 manual reset type, 7/16"-28 threadneck

A21 auto reset type, 3/8"-27 threadneck

A41 auto reset type, 7/16"-28 threadneck

A00 auto reset type, without threadneck

F01 snap in

Hardware

00 no hardware

01 one PAL nut, bulk

02 one PAL nut, one knurled nut, bulk

03 one PAL nut mounted

04 one PAL nut, one knurled nut, mounted

05 one PAL nut mounted, one knurled nut, bulk

06 one knurled nut, bulk

07 one hex nut, bulk

08 two hex nuts, bulk

Terminals

P10 blade terminals A6.3-0.8 (QC .250)

P13 blade terminals A6.3-0.8 (QC .250), 90°

S80 straight screw terminals*

S83 90° bent screw terminals*

Current ratings

5...30 A

1658 - G21 - 02 - P10 - 5 A Ordering example

* Screws and lock washers bulk shipped

Standard current ratings and typical voltage drop values

Current rating (A)	Voltage drop (mV)	Current rating (A)	Voltage drop (mV)
5	≤ 250	12	≤ 250
6	≤ 250	15	≤ 250
7	≤ 250	16	≤ 250
8	≤ 250	20	≤ 250
9	≤ 250	25	≤ 250
10	≤ 250	30	≤ 250

Approvals

Authority	Voltage rating	Current ratings
VDE (EN 60934)	AC 240 V; DC 28 V	5...25 A
UL	AC 240 V	5...16 A 1658-G../F..
	AC 120 V	18...30 A 1658-G../F..
	AC 120 V	5...30 A 1658-A...
	DC 32 V	5...30 A 1658-G../F..
	DC 28 V	5...30 A 1658-A..




1658-...

Technical data

For further details please see chapter: Technical Information

Voltage rating		AC 240 V; DC 28 V		
Current ratings		5...30 A		
Typical life	AC + DC	5...16 A	1,000 operations at 2 x I _N , inductive	
		17...25 A	1,000 operations at 2 x I _N , resistive	
Ambient temperature		-20...+60 °C (-4...+140 °F), ≤ 7 A max. +40 °C (+104 °F)		
Insulation co-ordination (IEC 60664 and 60664 A)		rated impulse withstand voltage 2.5 kV reinforced insulation in operating area	pollution degree 2	
Dielectric strength (IEC 60664 and 60664A) operating area		test voltage AC 3,000 V		
Insulation resistance		> 100 MΩ (DC 500 V)		
Interrupting capacity I _{cn}		5...7 A 8...30 A	180 A 200 A	
Interrupting capacity (UL 1077/EN 60934 PC1)		I _N 5...16 A 17...30 A 5...30 A 5...30 A	U _N AC 240 V AC 120 V DC 32 V DC 28 V	2,000 A 2,000 A 2,500 A 2,000 A (1658-A..)
Degree of protection (IEC 60529/DIN 40050)		operating area IP40 terminal area IP00		
Vibration		8 g (57-500 Hz) ± 0.61 mm (10-57 Hz), to IEC 60068-2-6, test Fc, 10 frequency cycles/axis		
Shock		30 g (11 ms) to IEC 60068-2-27, test Ea		
Corrosion		96 hours at 5 % salt mist, to IEC 60068-2-11, test Ka		
Humidity		240 hours at 95 % RH to IEC 60068-2-78, test Cab		
Mass		approx. 16 g		



Dimensions





A00




A21 tightening torque max. 0.8 Nm
3/8-27UNS-2A




G21 tightening torque max. 0.8 Nm
3/8-27UNS-2A





A41



G41



F01




Caution:
Please keep a tight grip on the unit
while removing the female connectors.

See ordering information for mounting hardware.


Terminal design

P10




blade terminals DIN 46244-A6.3-0.8
(QC .250)

S83




terminal screw
6-32 UNC lock washer

P13




blade terminals DIN 46244-A6.3-0.8 (QC .250)
angled 90°

P10-S83



terminal screw
6-32 UNC lock washer


S80



terminal screw
6-32 UNC lock washer


blade terminals
DIN 46244-A6.3-0.8 (QC .250)

Installation drawing




This is a metric design and millimeter dimensions take precedence (mm)
inch

Internal connection diagram



Typical time/current characteristics




The time/current characteristic curve depends on the ambient temperature prevailing. In order to eliminate nuisance tripping, please multiply the circuit breaker current ratings by the derating factor shown below. See also section Technical information.


Ambient temperature °F	-4	+14	+32	+73.4	+104	+122	+140
°C	-20	-10	0	+23	+40	+50	+60
Derating factor							
$I_N > 7A$	0.83	0.85	0.9	1	1.1	1.18	1.25
$I_N \leq 7A$	0.74	0.76	0.82	1	1.23	-	-

Accessories


Mounting nut 3/8", 27-thread
Y 306 671 01




Mounting nut 7/16", 28-thread
Y 303 200 01




Knurled nut 3/8", 27-thread plastic (standard)
Y 307 117 02




Knurled nut 7/16", 28-thread nickel-plated brass
Y 302 294 03




Knurled nut 3/8", 27-thread nickel-plated brass
Y 300 190 03




Hex nut 3/8", 27-thread nickel-plated brass
Y 300 192 01




Hex nut 7/16", 28-thread nickel-plated brass
Y 302 295 01



Press to Reset Plate for 3/8" thread, aluminium
Y 301 059 02



Press to Reset Plate for 7/16" thread, aluminium
Y 302 732 01



This is a metric design and millimeter dimensions take precedence (mm/inch)


Accessories

Reset button seal for 3/8", 27-thread,
short


X 201 285 01

long

X 200 799 01



3/8-27 UNS-2B




3/8-27 UNS-2B

Reset button seal for 7/16", 28-thread,
short


X 222 119 01

long

X 222 119 02



7/16-28 UNS-2B



7/16-28 UNS-2B

All dimensions without tolerances are for reference only. In the interest of improved design, performance and cost effectiveness the right to make changes in these specifications without notice is reserved. Product markings may not be exactly as the ordering codes. Errors and omissions excepted.