









THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	2000
© COPYRIGHT 2000	TE CONNECTIVITY	ALL RIGHTS RESERVED.


LOC IR	DIST -	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	SHIELD RAW MATERIAL CHANGE TO BRASS	08MAR2012	PS	RRP
			C1	ECR-12-014775	21AUG2012	SS	RRP




PACKAGED 190 PIECES IN A TRAY	8 POS. 8 CONT.	OVERALL: Ni 1.27 µm MIN. ALL OVER THE CONTACTS	HOUSING: PBT UL 94 V-0 BLACK	2-5338556-1
		SOLDER ZONE: Sn 2.5 µm MIN. ON THE SOLDER ZONE OF THE CONTACT	CONTACTS: PHOSPHOR BRONZE	
		MATING ZONE: PLATING CONFIRMS TO PRODUCT REQUIREMENTS AS PER SPECIFICATION 108-19064	SHIELD: BRASS PRE-PLATED (BRIGHT TIN)	
PACKAGING	REMARKS	PLATING	MATERIAL	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. Willems 25-Feb-05	 TE Connectivity			
		CHK P. Groels 25-Feb-05				
		APVD J. Broeksteeg 25-Feb-05				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-19064	NAME 8 pos. Modular Jack Side Entry fully shielded with insulation plate -			
	0 PLC ±0.15 1 PLC ±0.15 2 PLC ±0.15 3 PLC ±0.15 4 PLC ±0.15 ANGLES ±0.30°	APPLICATION SPEC 114-19019				
MATERIAL	FINISH	WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=5338556	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 2	REV 1	




D




PANEL CUT-OUT DIMENSIONS



C




B



PRINTED CIRCUIT BOARD LAYOUT.

(VIEW SHOWN IS CIRCUIT (NONCOMPONENT) SIDE OF BOARD.)
PRINTED CIRCUIT BOARD THICKNESS: 1.6 mm NOMINAL.
TOLERANCE UNLESS OTHERWISE SPECIFIED: ± 0.15 mm.

INSULATION PLATE



A

PACKAGED 190 PIECES IN A TRAY	8 POS. 8 CONT.	OVERALL: Ni 1.27 µm MIN. ALL OVER THE CONTACTS SOLDER ZONE: Sn 2.5 µm MIN. ON THE SOLDER ZONE OF THE CONTACT MATING ZONE: PLATING CONFIRMS TO PRODUCT REQUIREMENTS AS PER SPECIFICATION 108-19064	HOUSING: PBT UL 94V-0 BLACK CONTACTS: PHOSPHOR BRONZE SHIELD: BRASS PRE-PLATED BRIGHT TIN	3-5338556-1
PACKAGING	REMARKS	DESCRIPTION	MATERIAL	P/N
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. Willems 25-Feb-05 CHK P. Groels 25-Feb-05 APVD J. Broeksteeg 25-Feb-05	TE Connectivity	
DIMENSIONS: mm		PRODUCT SPEC 108-19064 APPLICATION SPEC 114-19019	NAME 8 pos. Modular Jack Side Entry fully shielded with insulation plate	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		0 PLC ±0.15 1 PLC ±0.15 2 PLC ±0.15 3 PLC ±0.15 4 PLC ±0.15 ANGLES ±0.30° FINISH	SIZE A2	CAGE CODE 00779
MATERIAL -		WEIGHT -	DRAWING NO C-5338556	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 4:1	SHEET 2 OF 2
			REV C1	