

BZH1-2RN62

M

DRAWING
NUMBER

6

ISSUE

6

6

6

6

6

6

6

6

6

6

6

6

6

6

6

6

6

6

6

6

6

6

6

6

6

6

RELEASE NO. DR-365-1

CHECK

WHE

5 MAR 70

5 MAR 70

5 MAR 70

5 MAR 70

5 MAR 70

5 MAR 70

5 MAR 70

5 MAR 70

5 MAR 70

5 MAR 70

5 MAR 70

5 MAR 70

5 MAR 70

5 MAR 70

REVISIONS

A PR-1342

2 JUL 70

B CO28612

11 FEB 71

C CO37675

23 SEP 76

D CO55989

1 NOV 84

E CO72977

6 J W

11 AUG 92

F CO77179-C

12 MAR 94

MAM

12 MAR 94

12 MAR 94

12 MAR 94

12 MAR 94

12 MAR 94

12 MAR 94

12 MAR 94

12 MAR 94

12 MAR 94

12 MAR 94

12 MAR 94

12 MAR 94

12 MAR 94

12 MAR 94


12 MAR 94

12 MAR 94

12 MAR 94

12 MAR 94

12 MAR 94




ELASTOMER PLUNGER SEAL SECURED TO COMPONENTS
BY EXTERNAL BANDING

ALUMINUM LEVER IS SHOWN IN ITS
FREE POSITION AT ONE EXTREME
OF ITS ADJUSTABLE RANGE

LEVER MAY BE LOCKED
IN ANY POSITION THRU 250°

HEX SEAL NUT .938 REF ACROSS FLATS



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE ----- 3-7 OZ	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE ----- 1 OZ MIN	15A-125, 250 OR 480 VAC, 2A-600 VAC 1/8HP-125 VAC; 1/4HP-250 VAC CODE L74 1/2A-125 VDC; 1/4A-250 VDC	UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES TOLERANCES ARE: ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±
PRETRAVEL ----- .718 MAX		WEIGHT
DIFFERENTIAL TRAVEL ----- .229 MAX		
OVERTRAVEL ----- .838 MIN		
SWITCH-BASIC REPLACEMENT --- 8Z-2RN702		

NOTE -

1 - 6-32 UNC X .219 REF BINDING HEAD TERMINAL SCREW AND CUPWASHER (3)

2 - ROD LEVER BRACKET ASSEMBLY MAY BE SET AT ANY
POSITION AROUND AXIS OF PLUNGER