





COIL: @ 25°C
 RESISTANCE 1560 OHMS $\pm$ 10%
 NOMINAL VOLTAGE 26.5 VDC
 MUST OPERATE VOLTAGE 14.2 VDC
 TURN-ON BASE CURRENT 0.13 mADC
 MUST RELEASE 8.0 VDC MAX, 1.37 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: TURN-ON TIME 2.0 MS MAX
 TURN-OFF TIME 7.5 MS MAX
 CONTACT STABILIZATION TIME 2.0 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 8/19/97 EK. JERRY 8/19/97

COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. QPL
 CUST. NO. M28776/1-024M

TYPE 'JMAT' RELAY

JMAPT-26XM