

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1970		Released	JWM	03/01/05	JN	08/12/08	JN	06/12/08



Contents

SPC Type No.	AWG	Description	QTY
1665	20-18	Ring Tongue, #6 Stud	5
1667	20-18	Ring Tongue, #10 Stud	5
1669	16-14	Ring Tongue, #8 Stud	5
1670	16-14	Ring Tongue, #10 Stud	5
3977	16-14	Ring Tongue, 1/4" Stud	5
3979	16-14	Ring Tongue, 3/8" Stud	5
N/A	12-10	Ring Tongue, #8 Stud	5
3980	12-10	Ring Tongue, #10 Stud	5
3981	12-10	Ring Tongue, 1/4" Stud	5
3983	12-10	Ring Tongue, 3/8" Stud	5
1671	20-18	Fork Tongue, #10 Stud	5
1673	16-14	Fork Tongue, #10 Stud	5
N/A	12-10	Fork Tongue, #10 Stud	5
1680	20-18	Butt Wire Splice	10
1681	16-14	Butt Wire Splice	10
1682	12-10	Butt Wire Splice	10
1677	20-18	1/4" Female Fully Nylon Insulated	5
1674	20-18	1/4" Male Fully Nylon Insulated	5
1678	16-14	1/4" Female Fully Nylon Insulated	5
1675	16-14	1/4" Male Fully Nylon Insulated	5

SPC-F004.DWG

TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY:	DATE:	DRAWING TITLE: 115 Piece Crimp and Seal Terminal Kit			
	Jeff McVicker	03/01/05				
	CHECKED BY:	DATE:				
	Jason Nash	06/12/08	SIZE	DWG. NO.		
	APPROVED BY:	DATE:	A	1686	ELECTRONIC FILE	REV
	Jason Nash	06/12/08	SCALE:	NTS	92N3607.dwg	
U.O.M.: INCHES [mm]				SHEET:	1 OF 1	

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY. DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.