



	XCB170	Units
Load Voltage	350	V
Load Current	100	mA
Max R_{ON}	50	Ω

Features

- Small 6 Pin DIP Package
- Low Drive Power Requirements (TTL/CMOS Compatible)
- No Moving Parts
- High Reliability
- Arc-Free With No Snubbing Circuits
- 3750V_{RMS} Input/Output Isolation
- No EMI/RFI Generation
- Machine Insertable, Wave Solderable
- Surface Mount and Tape & Reel Versions Available

Applications

- Telecommunications
 - Telecom Switching
 - Tip/Ring Circuits
 - Modem Switching (Laptop, Notebook, Pocket Size)
 - Hookswitch
 - Dial Pulsing
 - Ground Start
 - Ringer Injection
- Instrumentation
 - Multiplexers
 - Data Acquisition
 - Electronic Switching
 - I/O Subsystems
 - Meters (Watt-Hour, Water, Gas)
- Medical Equipment-Patient/Equipment Isolation
- Security
- Aerospace
- Industrial Controls

Description

The XCB170 is a 1-Form-B relay which uses optically coupled MOSFET technology to provide 3750V of input to output isolation. The efficient MOSFET switches and photovoltaic die use Clare's patented OptoMOS® architecture. A highly efficient GaAlAs infrared LED controls the optically coupled input. The device is available in small 6-pin dual in line package in standard through hole and surface mount lead bend.

Approvals

- UL Recognized: File Number E76270
- CSA Certified: File Number LR 43639-10
- BSI Certified to:
 - BS EN 60950:1992 (BS7002:1992)
Certificate #: 7344
 - BS EN 41003:1993
Certificate #: 7344


Ordering Information

Part #	Description
XCB170	6 Pin DIP (50/Tube)
XCB170S	6 Pin Surface Mount (50/Tube)
XCB170STR	6 Pin Surface Mount (1000/Reel)

Pin Configuration


XCB170 Pinout

AC/DC Configuration




XCB170 Pinout

DC Only Configuration



Switching Characteristics of Normally Closed (Form B) Devices



**Absolute Maximum Ratings (@ 25° C)**

Parameter	Min	Typ	Max	Units
Input Power Dissipation	-	-	150 ¹	mW
Input Control Current	-	-	50	mA
Peak (10ms)	-	-	1	A
Reverse Input Voltage	-	-	5	V
Total Power Dissipation	-	-	800 ²	mW
Isolation Voltage Input to Output	3750	-	-	V _{RMS}
Operational Temperature	-40	-	+85	°C
Storage Temperature	-40	-	+125	°C
Soldering Temperature DIP Package	-	-	+260	°C
Surface Mount Package (10 Seconds Max.)	-	-	+220	°C

¹ Derate Linearly 1.33 mW/°C² Derate Linearly 6.67 mW/°C


Absolute Maximum Ratings are stress ratings. Stresses in excess of these ratings can cause permanent damage to the device. Functional operation of the device at these or any other conditions beyond those indicated in the operational sections of this data sheet is not implied. Exposure of the device to the absolute maximum ratings for an extended period may degrade the device and effect its reliability.

Electrical Characteristics


Parameter	Conditions	Symbol	Min	Typ	Max	Units
Output Characteristics @ 25°C						
Load Voltage (Peak)	-	V _L	-	-	350	V
Load Current (Continuous) AC/DC Configuration	-	I _L	-	-	100	mA
DC Configuration	-	I _L	-	-	180	mA
Peak Load Current	10ms	I _{LPK}	-	-	350	mA
On-Resistance AC/DC Configuration	I _L =120mA	R _{ON}	-	31	50	Ω
DC Configuration	I _L =200mA	R _{ON}	-	10	15	Ω
Off-State Leakage Current	V _L =350V	I _{LEAK}	-	-	1	μA
Switching Speeds Turn-On	I _F =5mA, V _L =10V	T _{ON}	-	-	5	ms
Turn-Off	I _F =5mA, V _L =10V	T _{OFF}	-	-	5	ms
Output Capacitance	50V; f=1MHz	C _{OUT}	-	25	-	pF
Capacitance Input to Output	-	-	-	3	-	pF
Input Characteristics @ 25°C						
Input Control Current	I _L =120mA	I _F	5	-	50	mA
Input Dropout Current	-	I _F	0.4	0.7	-	mA
Input Voltage Drop	I _F =5mA	V _F	0.9	1.2	1.4	V
Reverse Input Voltage	-	V _R	-	-	5	V
Reverse Input Current	V _R =5V	I _R	-	-	10	μA
Input to Output Capacitance	-	C _{I/O}	-	3	-	pF

PERFORMANCE DATA*


XCB170
Typical LED Forward Voltage Drop
 (N=50 Ambient Temperature = 25°C)
 $I_F = 5\text{mADC}$




XCB170
Typical On-Resistance Distribution
 (N=50 Ambient Temperature = 25°C)
 (Load Current = 100mADC)




XCB170
Typical Blocking Voltage Distribution
 (N=50 Ambient Temperature = 25°C)




XCB170
Typical I_F for Switch Operation
 (N=50 Ambient Temperature = 25°C)
 (Load Current = 100mADC)




XCB170
Typical I_F for Switch Dropout
 (N=50 Ambient Temperature = 25°C)
 (Load Current = 100mADC)




XCB170
Typical Turn-Off Time
 (N=50 Ambient Temperature = 25°C)
 (Load Current = 100mADC)




XCB170
Typical Turn-On Time
 (N=50 Ambient Temperature = 25°C)
 (Load Current = 100mADC)




XCB170
Typical Load Current vs. Temperature




XCB170
Typical Leakage vs. Temperature
 (Measured across Pins 4 & 6)




XCB170
Typical Blocking Voltage vs. Temperature



XCB170
Typical Turn-Off vs. Temperature
 (Load Current = 100mADC)











XCB170
Typical Turn-On vs. Temperature
 (Load Current = 100mADC)



* The Performance data shown in the graphs above is typical of device performance. For guaranteed parameters not indicated in the written specifications, please contact our application department.




PERFORMANCE DATA*




* The Performance data shown in the graphs above is typical of device performance. For guaranteed parameters not indicated in the written specifications, please contact our application department.

6Pin DIP Through Hole (Standard)



Technical drawing of a mechanical part with dimensions:

- Top dimension: $7.620 \pm .254$ ($.300 \pm .010$)
- Left side dimension: $3.302 \pm .051$ ($.130 \pm .002$)
- Bottom left dimension: $.254 \pm .0127$ ($.010 \pm .0005$)
- Bottom right dimension: $.635 \pm .127$ ($.025 \pm .005$)
- Right side dimension: $4.445 \pm .127$ ($.175 \pm .005$)



Top view drawing of a square plate. The dimensions and tolerances are as follows:

- Overall width: $6.800 \pm .127$ DIA. ($.031$ DIA.)
- Overall height: $7.620 \pm .127$ ($.300 \pm .005$)
- Inner square width: $5.080 \pm .127$ ($.200 \pm .005$)
- Inner square height: $6.350 \pm .127$ ($.250 \pm .005$)
- Four circular holes are located at the corners of the inner square.

(Top View)

Diagram illustrating the top view of a 2x3 grid of squares. The dimensions and tolerances are as follows:

- Horizontal spacing between columns: $2.540 \pm .127$ ($.100 \pm .005$)
- Vertical spacing between rows: $1.905 \pm .127$ ($.075 \pm .005$)
- Horizontal spacing between columns (bottom): $1.499 \pm .127$ ($.059 \pm .005$)
- Vertical spacing between rows (right): $8.305 \pm .127$ ($.327 \pm .005$)

Technical drawing of a 35mm film strip showing dimensions and components. The drawing includes a perspective view of the film strip on the left and a detailed cross-sectional view on the right. Key dimensions and components are labeled:

- 35mm DIA. (13.00)**: Diameter of the film reel.
- Top Cover Tape Thickness .102 MAX. (.004)**: Thickness of the top cover tape.
- Embossed Carrier**: The carrier part of the film strip.
- Embossment**: The raised part of the film strip.
- 6.731 MAX. (.265)**: Maximum width of the film strip.
- .406 MAX. (.016)**: Maximum thickness of the film strip.
- 12.090 (.476)**: Length of the film strip.
- 4.877 (.192)**: Thickness of the top cover tape.
- Top Cover Tape**: The tape covering the top of the film strip.
- .050R TYP.**: Typical radius of the film strip.
- 2.007 ± .102 (.079 ± .004)**, **1.498 ± .102 (.059 ± .004)**, **3.987 ± .102 (.157 ± .004)**: Dimensions of the film strip segments.
- 7.493 ± .102 (.295 ± .004)**: Dimension of the film strip segment.
- 16.002 ± .305 (.630 ± .012)**: Dimension of the film strip segment.
- 10.300 (.405)**: Dimension of the film strip segment.
- 11.989 ± .102 (.472 ± .004)**: Dimension of the film strip segment.
- 10.300 ± .102 (.405 ± .004)**: Dimension of the film strip segment.
- 1.549 ± .102 (.061 ± .004)**: Dimension of the film strip segment.
- User Direction of Feed**: Arrow indicating the direction of feed.

5



CLARE

For additional information please visit our website at: www.clare.com

Clare, Inc. makes no representations or warranties with respect to the accuracy or completeness of the contents of this publication and reserves the right to make changes to specifications and product descriptions at any time without notice. Neither circuit patent licenses nor indemnity are expressed or implied. Except as set forth in Clare's Standard Terms and Conditions of Sale, Clare, Inc. assumes no liability whatsoever, and disclaims any express or implied warranty, relating to its products including, but not limited to, the implied warranty of merchantability, fitness for a particular purpose, or infringement of any intellectual property right.

The products described in this document are not designed, intended, authorized or warranted for use as components in systems intended for surgical implant into the body, or in other applications intended to support or sustain life, or where malfunction of Clare's product may result in direct physical harm, injury, or death to a person or severe property or environmental damage. Clare, Inc. reserves the right to discontinue or make changes to its products at any time without notice.

Specification: DS-XCB170-R2.0
©Copyright 2001, Clare, Inc.
OptoMOS® is a registered trademark of Clare, Inc.
All rights reserved. Printed in USA.
9/26/01