

- +

LCDs
- +

Lighting
- +

Optoelectronics
- +

Power Devices
- Document Library

Home » LCDs » 5 - 9 inch / 13 - 25 cm LCDs



Active Area (W x H):	130.56 x 97.92 mm
Backlight System:	LED
Brightness:	350 nits
Contrast Ratio:	350:1
Description:	True Industrial Module features 50,000-hr rated backlight, extended temperature range for both storage and operation, shock and vibration resistance; its light weight and slim profile are made possible by COG (Chip-on-Glass) technology; also contains onboard backlight driver.
Diagonal Size:	6.4 inch (16.32 cm)
Display Mode:	Normally White
Family:	LQ064V3DG06
Interface:	18-bit digital (6 bits/color)
Operating Temperature Range:	-30°C to +80°C
Outline Dimensions (W x H x D):	161.3 x 117.0 x 12.0 mm
Pixel Format:	640 x 480
Response Time:	60 ms
RoHS:	Yes
Status:	New
Storage Temperature Range:	-30°C to +80°C
Type:	VGA
Viewing Angle - 12 o clock:	40 °
Viewing Angle - 6 o clock:	70 °
Viewing Angle - side to side:	140 °

Documentation

There are no matching documents for this product or criteria.