




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		B	REVISION PER ECO-07-003727	23FEB07	KW	DB
			B1	REVISED PER ECO-09-023313	13OCT09	KK	AEG



MATERIAL: CONNECTOR-NYLON UL94V-0 (BLACK).
CONTACTS-0.30 [.012] THICK COPPER ALLOY
BRIGHT TIN-LEAD 0.00203 [.000080] MIN THICK FOR CONTACTS
644579-2 THRU 1-644579-5
MATTE WHISKER MITIGATED TIN PLATE 0.00203 [.000080] MIN THICK
OVER 0.00076 [.000030] MIN THICK NICKEL FOR CONTACTS
3-644579-2 THRU 4-644579-5

2. CONTACTS ACCEPT 24 AWG WIRE WITH 1.52 [.060] MAX INSULATION DIAMETER.

3. CONTACTS MUST ACCEPT 0.64±0.03 [.025±.001] SQUARE POST AND REMAIN LOCKED IN POSITION.

4. IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY NOT APPEAR ON ALL ASSEMBLIES.

5. DIMENSIONS IN BRACKETS ARE IN INCHES.

6. HOUSING FEATURES ARE: FEED THRU WITH LOCKING RAMP AND WITH POLARIZING TAB.

7. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

LEAD	38.10	[1.500]	15	4-644579-5
	35.56	[1.400]	14	4-644579-4
	33.02	[1.300]	13	4-644579-3
	30.48	[1.200]	12	4-644579-2
	27.94	[1.100]	11	4-644579-1
	25.40	[1.000]	10	4-644579-0
	22.86	[.900]	9	3-644579-9
	20.32	[.800]	8	3-644579-8
	17.78	[.700]	7	3-644579-7
	15.24	[.600]	6	3-644579-6
	12.70	[.500]	5	3-644579-5
	10.16	[.400]	4	3-644579-4

LEAD	38.10	[1.500]	15	4-644579-5
	35.56	[1.400]	14	4-644579-4
	33.02	[1.300]	13	4-644579-3
	30.48	[1.200]	12	4-644579-2
	27.94	[1.100]	11	4-644579-1
	25.40	[1.000]	10	4-644579-0
	22.86	[.900]	9	4-644579-9
	20.32	[.800]	8	4-644579-8
	17.78	[.700]	7	4-644579-7
	15.24	[.600]	6	4-644579-6
	12.70	[.500]	5	4-644579-5
	10.16	[.400]	4	4-644579-4

DIM A	NO.OF POSN	ASSEMBLY
-------	------------	----------

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOVER 03-DEC-2004	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]		CHK D. BOSSI 03-DEC-2004		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. BOSSI 03-DEC-2004	NAME	
0 PLC ± 1 PLC ± 2 PLC ± 0.13 [.005] 3 PLC ± 4 PLC ±		PRODUCT SPEC 108-1050	MTA .100 CONNECTOR ASSEMBLY 24 AWG, UL94V-0, SPECIAL	
MATERIAL		APPLICATION SPEC 114-1019	SIZE A2	CAGE CODE 00779
FINISH		WEIGHT	DRAWING NO C=644579	RESTRICTED TO
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1	REV B1