





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		R6	REVISED PER ECO-12-014997	22AUG12	KH	SM



- 1 PARTS COMPLY WITH AMP SOLDERABILITY SPEC 109-11-3.
- 2 0.00508 [.000200] MIN BRIGHT TIN-LEAD.
- 3 PARTS COMPLY WITH AMP SOLDERABILITY SPEC 109-11-1.
- 4 0.00305 [.000120] MIN BRIGHT TIN-LEAD OVER 0.00102 [.000040] MIN NICKEL.
- 5 FOR FOREIGN PRODUCTION ONLY.
- 6 CARRIER STRIP TO HAVE 1.52 [.060] DIA PILOT HOLE
- 7 0.00305 [.000120] MIN TIN OVER 0.00102 [.000040] MIN NICKEL.
- 8 WIRE RANGE: 0.3 – 0.9 mm² (22 – 18 AWG).
- 9 INSULATION RANGE: 1.52 – 2.79 [.060 – .110] DIA.
- 10 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 11 0.00508 [.000200] MIN BRIGHT TIN.
- 12 HOLE DIAMETER TO BE 1.83±0.08 FOR WIRE 0.3–0.6mm² (20–22 AWG) OR 1.96±0.08 FOR WIRE 0.8–0.9mm² (18 AWG).

OBSOLETE SUPERSEDED BY 3-640311-1	1	11	0.20[.008] PH BRZ	3-640311-1
	3 5 6	7	0.20[.008] BRASS	640311-5
	3 5	4	0.20[.008] BRASS	640311-3
	1	2	0.20[.008] PH BRZ	640311-1
NOTES		FINISH	MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CARPENTER 21AUG2003	TE Connectivity		
DIMENSIONS: INCHES		CHK J. ELLIS 21AUG2003			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. ELLIS 21AUG2003	NAME MINI AMP-IN™		
	0 PLC ±	PRODUCT SPEC			
	1 PLC ±	APPLICATION SPEC	SIZE A2		
MATERIAL SEE TABLE	2 PLC ± 0.13 [.005]	114-1016			
	3 PLC ±	WEIGHT	CAGE CODE 00779		
FINISH SEE TABLE	4 PLC ±	CUSTOMER DRAWING			
	ANGLES ±	SCALE 1:1	DRAWING NO C=640311		
		SHEET 1 of 1			
		REV R6			

METRIC