






A



B



PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



C

TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24A.PV00
15	39.14	33.32	25.18	24.54	19.18	D15S24A.PV00
25	53.03	47.04	39.12	38.25	33.12	D25S24A.PV00
37	69.32	63.50	55.68	54.71	49.68	D37S24A.PV00

Plating: 4 --> flash AU
Plating: 6 --> 0.76μ AU

D

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24A.PV00LF
15	39.14	33.32	25.18	24.54	19.18	D15S24A.PV00LF
25	53.03	47.04	39.12	38.25	33.12	D25S24A.PV00LF
37	69.32	63.50	55.68	54.71	49.68	D37S24A.PV00LF

Plating: 4 --> flash AU
Plating: 6 --> 0.76μ AU

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0000

European Views

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	JOUBERT	1996/09/10	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 2		
Eng	PESSON	1996/09/10			0.XX	±0.1				
Chr	LEGARE	1996/09/10			0.XX' ±2°	0.XXX				
Appr	LEGARE	1996/09/10	Product family				D-SUB	Spec ref -		
			FEMALE CONNECTOR STD EURO				dwg no C01-8646-0493		Rev. D	
title straight solder type for										
catalog no -										
							CUSTOMER		sheet 1 of 1	

rev	ecn no	dr	date
A	-	JOU	1996/09/10
B	L505-001	MPE	2005/03/14
C	L505-0056	MPE	2005/06/27
D	L506-0097	LGO	2006/07/28
-	-	-	-
-	-	-	-
-	-	-	-