

PRODUCT NO.	POSITIONS LOADED	CONTACT PLATING	MOUNTING EARS
90598-001-001LF	ALL	5u" Au + high performance lubricant	Y
-002-002LF	2,3,4,5,6,7	5u" Au + high performance lubricant	Y
-003-003LF	ALL	5u" Au + high performance lubricant	Y
-004-004LF	ALL	50u" / 1.27u GXT	Y
-005-005LF	1,2,7,8	5u" Au + high performance lubricant	Y
-006-006LF	ALL	5u" Au + high performance lubricant	N
-007-007LF	ALL	50u" / 1.27u GXT	N
-008-008LF	ALL	5u" Au + high performance lubricant	N
-009-009LF	2-7	5u" Au + high performance lubricant	N
-010-010LF	2-7	5u" Au + high performance lubricant	N
-011-011LF	3,4,5,6	50u" / 1.27u GXT	N
-012-012LF	ALL	15u" / 0.37u GXT	N
-013-013LF	ALL	6u" / 0.15u GXT	Y
-014-014LF	ALL	15u" / 0.37u GXT	Y
-015-015LF	ALL	30u" / 0.76u GXT	Y


PRODUCT NO.	POSITIONS LOADED	CONTACT PLATING	MOUNTING EARS
90598-101-101LF	ALL	5u" Au + high performance lubricant	Y
-102-102LF	2,3,4,5,6,7	5u" Au + high performance lubricant	Y
-103-103LF	ALL	5u" Au + high performance lubricant	Y
-104-104LF	ALL	50u" / 1.27u Au	Y
-105-105LF	1,2,7,8	5u" Au + high performance lubricant	Y
-106-106LF	ALL	5u" Au + high performance lubricant	N

LEAD FREE PRODUCT NO.

NOTES :


- 1 P/NO WITH DASH 0XX -NOMIAL WAVE SOLDERING APPLICATION.
P/NO WITH DASH 1XX -1R REFLOW APPLICATION.
PACKAGING SPEC. BUS-14-164.
- 2 SCRATCH MARKS ACCEPTABLE ON THESE SURFACES.
JACK IS FOR 1,57/062 THICK PCB.
- 3 SHOULD THE JACK NEED TO BE DISMOUNTED FROM THE PCB, PLS REMOVE JACK AS PER RECOMMENDED METHOD HEREIN. (DETAIL A)
NIPPING THE LEGS OF THE PEG TOGETHER IS DISALLOWED,
OTHERWISE LEG BREAKAGE MAY OCCUR.
THESE DIMENSIONS ARE TAKEN FROM THE TOP OF THE PEG.
- 4 MOUNTING EARS OPTIONAL. REFER TO TABLE
- 5 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
- 6 MOUNTING EARS OPTIONAL. REFER TO TABLE
- 7 THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.57mm MINIMUM THICK CIRCUIT BOARD
- 8 IF LF P/N PACKAGING MEETS GS-14-920 SPECIFICATION
- 9 EQUIVALENT THICKNESS Au AND GXT PLATING HAVE SAME FUNCTION AND THEY ARE ALTERNATIVE BY THE CUSTOEMR .

DIRECTION OF DISMOUNT



JACK DISMOUNT METHOD

DETAIL A
NOTE 5



mat'l. code	surface	tolerance	projection	product family
ISD1302	ISD1001	ISD406	ISD1001	MOD JACK
tolerances unless otherwise specified	tolerances unless otherwise specified	tolerances unless otherwise specified	tolerances unless otherwise specified	tolerances unless otherwise specified
M T00202	07/04/00	0.0X±0.3	mm	8 POS VERT. SNAP PEG
N N04-0102	11/23/04	0.0X±0.15	mm	P.C.B. III MOD JACK ASSY
P N06-0039	03/10/06	0.0XX±0.05	scale 2.0	awg no sheet 2 of 2 size
R N08-0097	09/25/08	C L FENG	01/08/97	90598
S ELX-N-01080	03/14/12	engr TONY CHIEN	01/08/97	A4
T ELX-N-15908	09/23/13	chr TONY CHIEN	01/08/97	Product Customer Drawing
sheet index	revision	appd JENN TSAO	01/08/97	