




DUAL-IN-LINE SOCKETS

SERIES 115...003 • ULTRA LOW PROFILE • OPEN FRAME



- Our lowest profile DIP socket with an above PCB height of only .095"
- Special short Hi-Rel, 4-finger BeCu #12 contact is rated at 3 amps. See page 252 for details
- Series 115 uses MM #1534 pins. See page 161 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations
- For Electrical, Mechanical and Environmental Data, see page 264 for details



Total number of pins				Quantity per tube	ORDERING INFORMATION						
	A	B	C								
6	0.3	0.3	0.4	68	115-XX-306-41-003000 115-XX-308-41-003000 115-XX-314-41-003000 115-XX-316-41-003000 115-XX-318-41-003000 115-XX-320-41-003000 115-XX-322-41-003000 115-XX-324-41-003000 115-XX-328-41-003000						
8	0.4	0.3	0.4	50							
14	0.7	0.3	0.4	28							
16	0.8	0.3	0.4	25							
18	0.9	0.3	0.4	22							
20	1.0	0.3	0.4	20							
22	1.1	0.3	0.4	18							
24	1.2	0.3	0.4	16							
28	1.4	0.3	0.4	14							
20	1.0	0.4	0.5	20					115-XX-420-41-003000 115-XX-422-41-003000 115-XX-424-41-003000 115-XX-428-41-003000		
22	1.1	0.4	0.5	18							
24	1.2	0.4	0.5	16							
28	1.4	0.4	0.5	14							
24	1.2	0.6	0.7	16	115-XX-624-41-003000 115-XX-628-41-003000 115-XX-632-41-003000 115-XX-636-41-003000 115-XX-640-41-003000 115-XX-648-41-003000 115-XX-650-41-003000						
28	1.4	0.6	0.7	14							
32	1.6	0.6	0.7	12							
36	1.8	0.6	0.7	11							
40	2.0	0.6	0.7	10							
48	2.4	0.6	0.7	8							
50	2.5	0.6	0.7	8							
XX=Plating Code See Below RoHS-2 2011/65/EU											
SPECIFY PLATING CODE XX =										91	93
Sleeve (Pin) 						200 μ" Sn/Pb	200 μ" Sn/Pb		200 μ" Sn	200 μ" Sn	200 μ" Sn
Contact (Clip) 						10 μ" Au	30 μ" Au		10 μ" Au	30 μ" Au	100 μ" Sn