




		95.10 [3.744]	24	2-640604-4
		91.14 [3.588]	23	2-640604-3
		87.17 [3.432]	22	2-640604-2
		83.21 [3.276]	21	2-640604-1
	SUPERSEDED	79.25 [3.120]	20	2-640604-0
		75.29 [2.964]	19	1-640604-9
		71.32 [2.808]	18	1-640604-8
		67.36 [2.652]	17	1-640604-7
		63.40 [2.496]	16	1-640604-6
		59.44 [2.340]	15	1-640604-5
		55.47 [2.184]	14	1-640604-4
	SUPERSEDED	51.51 [2.028]	13	1-640604-3
	SUPERSEDED	47.55 [1.872]	12	1-640604-2
	SUPERSEDED	43.59 [1.716]	11	1-640604-1
	SUPERSEDED	39.62 [1.560]	10	1-640604-0
		35.66 [1.404]	9	1-640604-9
	SUPERSEDED	31.70 [1.248]	8	1-640604-8
	OBSOLETE	27.74 [1.092]	7	1-640604-7
	SUPERSEDED	23.77 [.936]	6	1-640604-6
	SUPERSEDED	19.81 [.780]	5	1-640604-5
	SUPERSEDED	15.85 [.624]	4	1-640604-4
	SUPERSEDED	11.89 [.468]	3	1-640604-3
	SUPERSEDED	7.92 [.312]	2	1-640604-2
		DIM A	NO OF CIRCUITS	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. LEWIS	12FEB91	 TE Connectivity			
		CHK R. SWING	12FEB91				
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. CLARK	19FEB91	NAME	MTA-156 CONNECTOR ASSEMBLY, 18 AWG, STANDARD		
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13 [0.005] 4 PLC ± - ANGLES ± -	PRODUCT SPEC 108-1051					
		APPLICATION SPEC 114-1020	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL	FINISH	WEIGHT	A2	00779	G-640604	-	
		CUSTOMER DRAWING		SCALE	4:1	SHEET 1 of 1	REV U2