



ELECTRONICS, INC.  
44 FARRAND STREET  
BLOOMFIELD, NJ 07003  
(973) 748-5089  
<http://www.nteinc.com>



## NTE429 Hardware Socket for 28-Lead DIP Type Package .100" (2.54mm) Lead Spacing

### Features:

- Dual Contacts Open Frame Structure
- Stackable End-to-End and Side-to-Side
- Polarization mark

### Specifications:

|                                                    |                                                             |
|----------------------------------------------------|-------------------------------------------------------------|
| Insulator .....                                    | Thermoplastic                                               |
| Contact .....                                      | Phosphor Bronze, 150u" Tin Plating over 30u" to 50u" Nickel |
| Maximum Contact Resistance (Initial) .....         | 20mΩ                                                        |
| Minimum Insulation Resistance .....                | 1000MΩ                                                      |
| Dielectric Withstanding Voltage (Per Minute) ..... | 500V AC                                                     |
| Operating Temperature Range .....                  | -65° to +150°C                                              |
| Storage Temperature Range .....                    | -20° to +80°C                                               |

