




Technical drawing of a rectangular component with dimensions and labels:

- Dimensions:**
 - Overall width: (1.02) REF.
 - Overall height: (1.14) REF.
 - Internal width: (2.54) REF.
 - Internal height: (7.11) REF.
 - Internal width (typical): (2.54) TYP.
 - Internal height (typical): (2.29) REF. TYP.
 - Internal width (typical): (2.54) REF.
 - Internal height (typical): (1.55) REF. TYP.
- Labels:**
 - A REF.
 - B
 - C
 - J
- Other:**
 - Reference dimensions: (1.02) REF., (1.14) REF., (2.29) REF. TYP., (1.55) REF. TYP.
 - Typical dimensions: (2.54) TYP., (2.54) REF., (1.55) REF. TYP.



NOTES:

- 1- 20 CIRCUIT SIZE SHOWN FOR ILLUSTRATION PURPOSES.
- 2- PIN PUSHOUT FORCE:(17.79 N)/4 LBS.
- 3- PINS MUST MEET SOLDERABILITY SPEC. MIL-STD-202 METHOD 208B.
- 4- WINDOW NOT AVAILABLE ON 6 AND 8 CIRCUIT SIZE.
- 5- FOR CHARTED DIMENSIONS AND ASSEMBLY NO.S NOT SHOWN ON THIS SHEET - SEE SHEET 2.
- 6- ROW TO ROW PIN HEIGHT VARIATION MUST NOT EXCEED (0.131/.005 IN.
- 7- PRODUCT CONFORMS TO PS-8723.

[illegible]

MATERIAL:

SHROUDED WAFER: GLASS FILLED POLYESTER, 94V-0; COLOR: BLACK.
PINS: PHOSPHOR BRONZE,
SEE SHEET 2 FOR FINISHES.

ASSEMBLY STYLE "A" AND "B"

DIMENSIONS SHOWN METRIC INCH				MFG. SQA. REV. I.T.R.		REVISIONS	
$\nabla = 0$				REVISE ONLY ON CAD SYSTEM			
TITLE				SALES ASSEMBLY			
1. NAME INCH METRIC 2. NAME $\pm .01$ $\pm .013$ 3. NAME $\pm .01$ $\pm .025$				WAFER - STRAIGHT MT. FULLY SHROUDED .100 GRID FOOTPRINT .050 SQ. PINS WITH .066 END WALLS			
MOLEX INCORPORATED				SHEET NO.		DATE	
PART  69532				104		92/07/17	
SEE CALL				SDA-1873*****			
FILE NAME 58723X1				THIS DRAWING CANNOT BE REPRODUCED OR REPRODUCED TO MOLD AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
SPEC. BY RB		ENGR.		DATE		DTD.	
APPR. BY		SCALE 4:1		DATE		DTD.	

