


## SMD Power Inductors (NR series S type)

## NRS6010T100MMGF



## ■ Features

- Item Summary  
10  $\mu$ H( $\pm 20\%$ ), 1000mA, 1100mA
- Lifecycle Stage  
Mass Production
- Standard packaging quantity (minimum)  
Taping 1000pcs

## ■ Products characteristics table

CaseSize (EIA/JIS)	-/6010
Inductance	10 $\mu$ H( $\pm 20\%$ )
Inductance Measuring Frequency	100kHz
Rated Current -Saturation Current	1000mA
Rated Current -Temperature Rise Current	1100mA
DC Resistance (max)	0.324 $\Omega$
Avg. of DC.Resistance	0.27 $\Omega$
Temperature Range	-25°C to 125°C
Self-resonant Frequency (min)	25MHz
RoHS Compliance	Yes
Halogen Free	Yes
Soldering Method	Reflow


## ■ External Dimensions

L	6mm $\pm 0.2$
W	6mm $\pm 0.2$
H	1mm max

## ■ Recommended Land Patterns

【推奨シダーリダーリング】
実装上の注意
・実装状態を確認の上ご使用くださいますようお願いいたします。
・本製品のみで付けたリフローはんだ工法に限ります。

【Recommended Land Patterns】
Surface Mounting
・Mounting and soldering conditions should be checked beforehand.
・Applicable soldering process to these products is reflow soldering only.



SMD Power Inductors (NR series/NR series H type/S type /V type)	A	B	C
NR6010, NR6012, NR6014, NR6020, NR6022, NR6028, NR6045, NR6048	1.6	4.7	5.7
			unit:mm

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.  
TAIYO YUDEN reserves the right to make change to the Date at any time without notice.  
Before making final selection, please check product specification.

2014.06.06