






REV.	DATE	ECR NO.	DESCRIPTION
A	01/24/06	—	ADD 50ohm TO DESCRIPTION/ UPDATE DRAWING FORMAT
B	12/03/08	100062	REVISE CABLE STRIPPING TO 4.5/ CONTACT PIN TO 13.75



RECOMMENDED
CABLE STRIPPING DIM'S



						UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex					
8							DRAWN	GRS	12/03/08							
7							CHECKED									
6							ISSUED				PART DESCRIPTION TNC PANEL DIRECT SOLDER JACK (FOR .141” SEMI RIGID CABLE)					
5	SOLDER NUT	BRASS	GOLD	1			SHEET		1 OF 1							
4	INSULATOR	PTFE	NATURAL	1						PART NO. 122419						
3	CONTACT PIN	PHOS. BRONZE	GOLD	1												
2	INSULATOR	PTFE	NATURAL	1						DWG. NO. 122419.DWG						
1	BODY/HOUSING	BRASS	NICKEL	1												
DESCRIPTION		MATERIAL	FINISH	QTY			CAD FILE		C:/122/122419.DWG		REV.	B	SIZE	A	SCALE	NA