



Standard Recovery Diodes, 165 A to 230 A (INT-A-PAK Power Modules)



INT-A-PAK


RoHS
COMPLIANT

FEATURES

- High voltage
- Electrically isolated by DBC ceramic (Al_2O_3)
- 3500 V_{RMS} isolating voltage
- Industrial standard package
- High surge capability
- Glass passivated chips
- Modules uses high voltage power diodes in four basic configurations
- Simple mounting
- UL approved file E78996 
- Designed and qualified for multiple level
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

APPLICATIONS

- DC motor control and drives
- Battery chargers
- Welders
- Power converters

PRIMARY CHARACTERISTICS	
$I_{\text{F(AV)}}$	165 A to 230 A
Type	Modules - diode, high voltage
Package	INT-A-PAK
Circuit configuration	Single diode, two diodes common anode, two diodes common cathode, two diodes doubler circuit

MAJOR RATINGS AND CHARACTERISTICS					
SYMBOL	CHARACTERISTICS	VSK.166..	VSK.196..	VSK.236..	UNITS
$I_{\text{F(AV)}}$		165	195	230	A
	T_{C}	100	100	100	$^{\circ}\text{C}$
$I_{\text{F(RMS)}}$		260	305	360	A
I_{FSM}	50 Hz	4000	4750	5500	
	60 Hz	4200	4980	5765	
I^2t	50 Hz	80	113	151	kA^2s
	60 Hz	73	103	138	
$I^2\sqrt{t}$		798	1130	1516	$\text{kA}^2\sqrt{\text{s}}$
V_{RRM}		400 to 1600			V
T_{J}	Range	-40 to +150			$^{\circ}\text{C}$

ELECTRICAL SPECIFICATIONS

VOLTAGE RATINGS				
TYPE NUMBER	VOLTAGE CODE	V_{RRM} , MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE V	V_{RSM} , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	I_{RRM} AT 150 $^{\circ}\text{C}$ mA
VS-VSK.166 VS-VSK.196 VS-VSK.236	04	400	500	20
	08	800	900	
	12	1200	1300	
	14	1400	1500	
	16	1600	1700	



FORWARD CONDUCTION								
PARAMETER	SYMBOL	TEST CONDITIONS			VALUES			UNITS
					VSK.166	VSK.196	VSK.236	
Maximum average on-state current at case temperature	I _{F(AV)}	180° conduction, half sine wave			165	195	230	A
					100	100	100	°C
Maximum RMS on-state current	I _{F(RMS)}				260	305	360	
Maximum peak, one-cycle on-state, non-repetitive surge current	I _{FSM}	t = 10 ms	No voltage reapplied	Sine half wave, initial T _J = T _J maximum	4000	4750	5500	A
		t = 8.3 ms			4200	4980	5765	
		t = 10 ms	100 % V _{RRM} reapplied		3350	4000	4630	
		t = 8.3 ms			3500	4200	4850	
Maximum I ² t for fusing	I ² t	t = 10 ms	No voltage reapplied		80	113	151	kA ² s
		t = 8.3 ms			73	103	138	
		t = 10 ms	100 % V _{RRM} reapplied		56	80	107	
		t = 8.3 ms			52	73	98	
Maximum I ² √t for fusing	I ² √t	t = 0.1 ms to 10 ms, no voltage reapplied			798	1130	1516	kA ² √s
Low level value of threshold voltage	V _{F(TO)1}	(16.7 % × π × I _{F(AV)} < I < π × I _{F(AV)}), T _J maximum			0.73	0.69	0.7	V
High level value of threshold voltage	V _{F(TO)2}	(I > π × I _{F(AV)}), T _J maximum			0.88	0.78	0.83	
Low level value on-state slope resistance	r _{t1}	(16.7 % × π × I _{F(AV)} < I < π × I _{F(AV)}), T _J maximum			1.5	1.3	1.2	mΩ
High level value on-state	r _{t2}	(I > π × I _{F(AV)}), T _J maximum			1.26	1.2	1.07	
Maximum forward voltage drop	V _{FM}	I _{FM} = π × I _{F(AV)} , T _J = 25 °C, 180° conduction Average power = V _{F(TO)} × I _{F(AV)} + r _f × (I _{F(RMS)}) ²			1.43	1.38	1.46	V

BLOCKING						
PARAMETER	SYMBOL	TEST CONDITIONS	VSK.166	VSK.196	VSK.236	UNITS
Maximum peak reverse and off-state leakage current	I_{RRM}	$T_J = 150\text{ °C}$	20			mA
RMS insulation voltage	V_{INS}	50 Hz, circuit to base, all terminals shorted, $t = 1\text{ s}$	3500			V

THERMAL AND MECHANICAL SPECIFICATIONS						
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES			UNITS
			VSK.166	VSK.196	VSK.236	
Maximum junction operating and storage temperature range	T _J , T _{Stg}		-40 to +150			°C
Maximum thermal resistance, junction to case per junction	R _{thJC}	DC operation	0.2	0.16	0.14	K/W
Maximum thermal resistance, case to heatsink per module	R _{thCS}	Mounting surface smooth, flat and greased	0.05			
Mounting torque ± 10 %	IAP to heatsink busbar to IAP	A mounting compound is recommended and the torque should be rechecked after a period of 3 hours to allow for the spread of the compound. Lubricated threads.	4 to 6			Nm
Approximate weight			200			g
			7.1			oz.
Case style			INT-A-PAK			



ΔR CONDUCTION PER JUNCTION

DEVICES	SINUSOIDAL CONDUCTION AT T _J MAXIMUM					RECTANGULAR CONDUCTION AT T _J MAXIMUM					UNITS
	180°	120°	90°	60°	30°	180°	120°	90°	60°	30°	
VSK.166	0.025	0.03	0.038	0.055	0.089	0.018	0.031	0.041	0.057	0.089	K/W
VSK.196	0.016	0.019	0.024	0.034	0.053	0.012	0.02	0.026	0.035	0.054	
VSK.236	0.009	0.010	0.014	0.018	0.025	0.008	0.012	0.015	0.019	0.025	

Note

- Table shows the increment of thermal resistance R_{thJC} when devices operate at different conduction angles than DC




Fig. 1 - Current Ratings Characteristics




Fig. 3 - On-State Power Loss Characteristics




Fig. 2 - Current Ratings Characteristics




Fig. 4 - On-State Power Loss Characteristics




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 6 - Maximum Non-Repetitive Surge Current




Fig. 7 - On-State Power Loss Characteristics






Fig. 8 - On-State Power Loss Characteristics







Fig. 9 - On-State Power Loss Characteristics




Fig. 10 - Current Ratings Characteristics




Fig. 12 - On-State Power Loss Characteristics




Fig. 11 - Current Ratings Characteristics




Fig. 13 - On-State Power Loss Characteristics




Fig. 14 - Maximum Non-Repetitive Surge Current




Fig. 15 - Maximum Non-Repetitive Surge Current





Fig. 16 - On-State Power Loss Characteristics





Fig. 17 - On-State Power Loss Characteristics





Fig. 18 - On-State Power Loss Characteristics




Fig. 19 - Current Ratings Characteristics




Fig. 21 - On-State Power Loss Characteristics




Fig. 20 - Current Ratings Characteristics




Fig. 22 - On-State Power Loss Characteristics




Fig. 23 - Maximum Non-Repetitive Surge Current




Fig. 24 - Maximum Non-Repetitive Surge Current




Fig. 25 - On-State Power Loss Characteristics






Fig. 26 - On-State Power Loss Characteristics







Fig. 27 - On-State Power Loss Characteristics




Fig. 28 - On-State Voltage Drop Characteristics




Fig. 30 - On-State Voltage Drop Characteristics




Fig. 29 - On-State Voltage Drop Characteristics




Fig. 31 - Thermal Impedance $Z_{\theta JC}$ Characteristics




Fig. 32 - Thermal Impedance Z_{thJC} Characteristics




Fig. 33 - Thermal Impedance Z_{thJC} Characteristics

ORDERING INFORMATION TABLE

Device code

VS-VS	KD	236	16	PbF
-------	----	-----	----	-----

①

②

③

④

⑤

1

- Vishay Semiconductors product

2

- Circuit configuration

3

- Current rating: $I_{F(AV)}$

4

- Voltage code x 100 = V_{RRM}





5

- PbF = Lead (Pb)-free

Note

- To order the optional hardware go to www.vishay.com/doc?95172




CIRCUIT CONFIGURATION		
CIRCUIT DESCRIPTION	CIRCUIT CONFIGURATION CODE	CIRCUIT DRAWING
Two diodes doubler circuit	D	VSKD... 
Two diodes common cathode	C	VSKC... 
Two diodes common anode	J	VSKJ... 
Single diode	E	VSKE... 

LINKS TO RELATED DOCUMENTS	
Dimensions	www.vishay.com/doc?95254

INT-A-PAK DBC

DIMENSIONS in millimeters (inches)





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[VS-VSKC166/08PBF](#) [VS-VSKC196/12PBF](#) [VS-VSKC236/12PBF](#) [VS-VSKD166/04PBF](#) [VS-VSKC196/04PBF](#) [VS-](#)
[VSKC236/04PBF](#) [VS-VSKC236/16PBF](#) [VS-VSKD236/12PBF](#) [VS-VSKE196/08PBF](#) [VS-VSKD236/16PBF](#) [VS-](#)
[VSKD196/12PBF](#) [VS-VSKD196/04PBF](#) [VS-VSKE166/04PBF](#) [VS-VSKD196/16PBF](#) [VS-VSKE166/12PBF](#) [VS-](#)
[VSKE166/08PBF](#) [VS-VSKE236/12PBF](#) [VS-VSKJ236/16PBF](#) [VS-VSKJ166/16PBF](#) [VS-VSKJ236/04PBF](#) [VS-](#)
[VSKC166/04PBF](#) [VS-VSKD236/04PBF](#) [VS-VSKJ236/12PBF](#) [VS-VSKE166/16PBF](#) [VS-VSKD166/14PBF](#) [VS-](#)
[VSKD236/08PBF](#) [VS-VSKE236/16PBF](#) [VS-VSKD166/16PBF](#) [VS-VSKD166/08PBF](#) [VS-VSKJ166/04PBF](#) [VS-](#)
[VSKE166/14PBF](#) [VS-VSKD166/12PBF](#) [VS-VSKC196/08PBF](#) [VS-VSKD196/08PBF](#) [VS-VSKE196/12PBF](#) [VS-](#)
[VSKC166/16PBF](#) [VS-VSKC166/12PBF](#) [VS-VSKE196/16PBF](#) [VS-VSKE236/04PBF](#) [VS-VSKE196/04PBF](#)