


Standard Power Integrated Module with PFC and Shunts

flow PIM® 1 + P; 600V, 20A

V23990-P305-_10-PM



Maximum Ratings / Höchstzulässige Werte

at T_J=25°C, unless otherwise specified

Parameter	Condition		Symbol	Value	Unit
Input Rectifier Bridge Gleichrichter					
Repetitive peak reverse voltage Periodische Rückw. Spitzensperrspannung			VRRM	1200	V
Forward average current Dauergrenzstrom	sine d=0.5	TC=25°C TC=80°C	IFAV	29	A
Surge forward current Stoßstrom Grenzwert	tp=10ms	TJ=25°C	IFSM	250	A
I2t-value Grenzlastintegral	tp=10ms	TJ=25°C	I²t	310	A²s
Power dissipation per Diode Verlustleistung pro Diode	Tj=150°C	TC=25°C TC=80°C	Ptot	53	W
Transistor Inverter Transistor Wechselrichter					
Collector-emitter break down voltage Kollektor-Emitter-Sperrspannung			VCE	600	V
DC collector current Kollektor-Dauergleichstrom	Tj=150°C	TC=25°C TC=80°C	IC	20	A
Repetitive peak collector current Periodischer Kollektorspitzenstrom	Tj=150°C tp=1ms	TC=25°C TC=80°C	Icpuls	40	A
Power dissipation per IGBT Verlustleistung pro IGBT	Tj=150°C	TC=25°C TC=80°C	Ptot	45	W
Gate-emitter peak voltage Gate-Emitter-Spitzenspannung			VGE	±20	V
Diode Inverter Diode Wechselrichter					
DC forward current Dauergleichstrom	Tj=150°C	TC=25°C TC=80°C	IF	17	A
Repetitive peak forward current Periodischer Spitzenstrom	Tj=150°C tp=1ms	TC=25°C TC=80°C	IFRM	34	A
Power dissipation per Diode Verlustleistung pro Diode	Tj=150°C	TC=25°C TC=80°C	Ptot	25	W
PFC Transistor					
Drain to source breakdown voltage Drai-Source Sperrspannung			Vbr	500	V
DC drain current Drain-Dauergleichstrom	Tj=150°C	TC=25°C TC=80°C	Id	30 21	A
Pulsed drain current Periodischer Drainstrom	Tj=150°C tp=1ms	TC=25°C TC=80°C	Idpuls	60 42	A
Power dissipation Verlustleistung	Tj=150°C	TC=25°C TC=80°C	Ptot	210 115	W
Gate-source peak voltage Gate-Source-Spitzenspannung			Vgs	±20	V

PFC Diode					
DC forward current Dauergleichstrom	Tj=150°C	TC=25°C	IF	20	A
		TC=80°C			
Repetitive peak forward current Periodischer Spitzenstrom	Tj=150°C	TC=25°C	IFRM	40	A
	tp=1ms	TC=80°C			
Power dissipation per Diode Verlustleistung pro Diode	Tj=150°C	TC=25°C	Ptot	23	W
		TC=80°C			
Thermal properties					
Thermische Eigenschaften					
max. Chip temperature max. Chiptemperatur			Tjmax	150	°C
Storage temperature Lagertemperatur			Tstg	-40...+125	°C
Operation temperature Betriebstemperatur			Top	-40...+125	°C
Thermal resistance, chip to case Wärmewiderstand Chip-Bodenplatte per chip	Diode Rectifier		RthJC	1,30	K/W
	Transistor Inverter		RthJC	1,60	K/W
	Diode Inverter		RthJC	2,80	K/W
	Transistor PFC		RthJC	0,60	K/W
	Diode PFC		RthJC	1,20	K/W
Insulation properties					
Modulisation					
Insulation test voltage Isolationsspannung	t=1min		Vis	4000	Vdc
Creepage distance Kriechstrecke				12,7	mm
Clearance Luftstrecke				12,7	mm

Standard Power Integrated Module with PFC and Shunts

flow PIM® 1 + P; 600V, 20A

V23990-P305-_10-PM

→ B: with PFC/ mit PFC
→ D: w/o PFC/ ohne PFC

Characteristic values / Charakteristische Werte
at T_J=25°C, unless otherwise specified

Parameter	Symbol	Condition:	T	RG	VGE	VCE	IF	IC	Value			Unit
FET Parameter			(°C)	RG	VGS	VDS		Id	min.	typ.	max.	
Input Rectifier Bridge Gleichrichter												
Forward voltage Durchlaßspannung	V _F		T _J =25°C				20			1,17		V
Threshold voltage (for pwr. loss calc. only) Schleusenspannung	V _{to}		T _J =25°C				20			0,92		V
Slope resistance (for power loss calc. only) Ersatzwiderstand	r _t		T _J =25°C				20			12,5		mΩ
Reverse current Sperrstrom	I _r	V _R =V _{Rmax}	T _J =25°C								0,02	mA
Transistor Inverter, inductive load Transistor Wechselrichter												
Gate emitter threshold voltage Gate-Schwellenspannung	V _{GE(th)}	V _{ge} =V _{ce}	T _J =25°C					500μ	4,5	5,5	6,5	V
Collector-emitter saturation voltage Kollektor-Emitter Sättigungsspannung	V _{CE(sat)}		T _C =25°C		15			20,0	1,7	2	2,5	V
Collector-emitter cut-off current incl. FRED Kollektor-Emitter Reststrom inkl. FRED	I _{CES}		T _C =25°C		0	600					70	μA
Gate-emitter leakage current Gate-Emitter Reststrom	I _{GES}		T _J =25°C		30	0					120	nA
Turn-on delay time Einschaltverzögerungszeit	t _{d(on)}	R _{g(on)} =R _{g(off)}	T _J =25°C T _J =125°C	62	15	400		20,0		22 20	50 42	ns
Rise time Anstiegszeit	t _r	R _{g(on)} =R _{g(off)}	T _J =25°C T _J =125°C	62	15	400		20,0		12 14	30 30	ns
Turn-off delay time Abschaltverzögerungszeit	t _{d(off)}	R _{g(on)} =R _{g(off)}	T _J =25°C T _J =125°C	62	15	400		20,0		143 156	300 330	ns
Fall time Fallzeit	t _f	R _{g(on)} =R _{g(off)}	T _J =25°C T _J =125°C	62	15	400		20,0		19 24	50 58	ns
Turn-on energy loss per pulse Einschaltverlustenergie pro Puls	E _{on}	R _{g(on)} =R _{g(off)}	T _J =125°C		15	400		20,0		645		mWs
Turn-off energy loss per pulse Abschaltverlustenergie pro Puls	E _{off}	R _{g(on)} =R _{g(off)}	T _J =125°C		25	400		20,0		862		mWs
SC withstand time Kurzschlußverhalten	t _{SC}	@ 10*I _c (max)	T _J =125°C								10	μs
Input capacitance Eingangskapazität	C _{ies}	f=1MHz	T _J =25°C		0	25				1,1		nF
Output capacitance Ausgangskapazität	C _{oss}	f=1MHz	T _J =25°C									nF
Diode Inverter Diode Wechselrichter												
Diode forward voltage Durchlaßspannung	V _F		T _J =25°C				20			2		V
Peak reverse recovery current Rückstromspitze	I _{RM}	dI _F /dt= -200A/μs	T _J =25°C T _J =125°C			400	20			6,4		A
Reverse recovery time Sperrverzögerungszeit	t _{rr}	dI _F /dt= -200A/μs	T _J =125°C			400	20			74		ns
Reverse recovered charge Sperrverzögerungsladung	Q _{rr}	dI _F /dt= -200A/μs	T _J =125°C			400	20			0,35		μC

Transistor PFC													
Static drain to source ON resistance Statische drain-source Widerstand	Rds(on)	TJ=25°C	10					22,0			0,15	Ω	
Gate threshold voltage Gate Spitzenspannung	V(GS)th	VDS=VGS TJ=25°C						2			4	V	
Drain to Source breakdown voltage Drain source Leckstrom	V(BR)DSS	ID=350μA TJ=25°C		0				500				V	
Drain to Source Leakage Current Drain source Leckstrom	Igss	TJ=25°C		30							100	nA	
Turn On Delay Time Einschaltverzögerung	td(ON)	VDD=350V TJ=25°C	2,2					36,0		23		ns	
Rise Time Anstiegszeit	tr	VDD=350V TJ=25°C	2,2					36,0		98		ns	
Turn off delay time Abschaltverzögerung	td(OFF)	VDD=350V TJ=25°C	2,2					36,0		52		ns	
Fall time Abstiegszeit	tf	VDD=350V TJ=25°C	2,2					36,0		80		ns	
Total gate charge Gate Ladung	Qg	VDD=350V TJ=25°C		10	400			36,0			180	nC	
Gate to source charge Gate source Ladung	Qgs	TJ=25°C		10	400			36,0			46	nC	
Input capacitance Eingangskapazität	Ciss	f=1MHz TJ=25°C		0	25					5579		pF	
Output capacitance Ausgangskapazität	Coss	f=1MHz TJ=25°C		0	400					221		pF	
Diode PFC													
Forward voltage Durchlaßspannung	VF	TJ=25°C TJ=25°C TJ=125°C						25 50 25			1,3 1,5 1,3	1,7 2 1,7	V V V
Breakdown voltage Sperrspannung	Vr	Ir=100μA									600		V
Reverse leakage current Leckstrom	Irm	Vr=Vr rated Vr=0.8*Vr rated TJ=25°C TJ=125°C								1,5 600	20 2000	μA	
Reverse recovery time Sperrverzögerungszeit	trr	Vr=200V dif/dt=-200A/μs TJ=25°C TJ=125°C					25			50 105	75 160	ns	
Peak recovery current Rückstromspitze	Irrm	Vr=200V dif/dt=-200A/μs TJ=25°C TJ=125°C					25			4,5 8	10 15	A	
Reverse recovery charge Sperrverzögerungsladung	Qrr	Vr=200V dif/dt=-200A/μs TJ=25°C TJ=125°C					25			112 420	375 1200	nC	
Peak rate of fall of recovery current Sitzenteilheit von Rückstrom	di(rec)max /dt	Vr=200V dif/dt=-200A/μs TJ=25°C TJ=125°C					25			250 160		A/μs	
NTC-Thermistor NTC-Widerstand													
Rated resistance Nennwiderstand	R25	Tol. ±5% Tc=25°C								22		kΩ	
Deviation of R100 Abweichung von R100	DR/R	R100=1503W Tc=100°C								1486		%/K	
Power dissipation Verlustleistung	P	Tc=25°C									210	mW	
B-value B-Wert	B(25/100)	Tol. ±3%								4000		K	
Shunt resistors Shuntwiderstände													
R1 value R1 Wert	R	Tol. 1% Tc=25°C								15		mΩ	
Power dissipation Verlustleistung	P	Tc=25°C									5	W	
R2 value R2 Wert	R	Tol. 1% Tc=25°C								22		mΩ	
Power dissipation Verlustleistung	P	Tc=25°C									3	W	
R3 value R3 Wert	R	Tol. 1% Tc=25°C								22		mΩ	
Power dissipation Verlustleistung	P	Tc=25°C									3	W	


Output inverter

Typ. output characteristics

Output inverter IGBT

$$I_C = f(V_{CE})$$

parameter: $t_p = 250 \mu s$, $T_j = 25^\circ C$




Typ. output characteristics

Output inverter IGBT

$$I_C = f(V_{CE})$$

parameter: $t_p = 250 \mu s$, $T_j = 125^\circ C$




Typ. transfer characteristics

Output inverter IGBT

$$I_C = f(V_{GE})$$

parameter: $t_p = 250 \mu s$, $V_{CE} = 10 V$




Typ. diode characteristics

Output inverter FRED

$$I_F = f(V_F)$$

parameter: $t_p = 250 \mu s$




Output inverter

Typ. Switching losses

Output inverter IGBT

$E = f(I_C)$, inductive load, $T_j = 25^\circ\text{C}$

par.: $V_{CE} = 400\text{ V}$, $V_{GE} = 15\text{ V}$, $R_G = 18\ \Omega$, $R_{Gon} = R_{Goff}$




Typ. Switching losses

Output inverter IGBT

$E = f(R_G)$, inductive load, $T_j = 25^\circ\text{C}$

par.: $V_{CE} = 400\text{ V}$, $V_{GE} = 15\text{ V}$, $I_C = 20\text{ A}$, $R_{Gon} = R_{Goff}$




Typ. Switching time

Output inverter IGBT

$t = f(I_C)$, inductive load, $T_j = 25^\circ\text{C}$

par.: $V_{CE} = 400\text{ V}$, $V_{GE} = 15\text{ V}$, $R_G = 18\ \Omega$, $R_{Gon} = R_{Goff}$




Typ. Switching time

Output inverter IGBT

$t = f(R_G)$, inductive load, $T_j = 25^\circ\text{C}$

par.: $V_{CE} = 400\text{ V}$, $V_{GE} = 20\text{ V}$, $I_C = 15\text{ A}$, $R_{Gon} = R_{Goff}$




Output inverter

Typ. Switching losses

Output inverter IGBT

$E = f(I_C)$, inductive load, $T_j = 125^\circ\text{C}$

par.: $V_{CE} = 400\text{ V}$, $V_{GE} = 15\text{ V}$, $R_G = 18\ \Omega$, $R_{Gon} = R_{Goff}$




Typ. Switching losses

Output inverter IGBT

$E = f(R_G)$, inductive load, $T_j = 125^\circ\text{C}$

par.: $V_{CE} = 400\text{ V}$, $V_{GE} = 15\text{ V}$, $I_C = 20\text{ A}$, $R_{Gon} = R_{Goff}$




Typ. Switching time

Output inverter IGBT

$t = f(I_C)$, inductive load, $T_j = 125^\circ\text{C}$

par.: $V_{CE} = 400\text{ V}$, $V_{GE} = 15\text{ V}$, $R_G = 18\ \Omega$, $R_{Gon} = R_{Goff}$




Typ. Switching time

Output inverter IGBT

$t = f(R_G)$, inductive load, $T_j = 125^\circ\text{C}$

par.: $V_{CE} = 400\text{ V}$, $V_{GE} = 15\text{ V}$, $I_C = 20\text{ A}$, $R_{Gon} = R_{Goff}$




FRED diode

Typ. Reverse recovery time

Output inverter FRED diode

$$t_{rr} = f(di_f / dt)$$

par.: $V_R = 400 \text{ V}$, $T_J = 125^\circ \text{C}$




Typ. Reverse recovery current

Output inverter FRED diode

$$I_{rr} = f(di_f / dt)$$

par.: $V_R = 400 \text{ V}$, $T_J = 125^\circ \text{C}$




Typ. Reverse stored charge

Output inverter FRED diode

$$Q_{rr} = f(di_f / dt)$$

par.: $V_R = 400 \text{ V}$, $T_J = 125^\circ \text{C}$




Typ. di_{rec} / dt





Output inverter FRED diode

$$I_{rr} = f(di_f / dt)$$

par.: $V_R = 400 \text{ V}$, $T_J = 125^\circ \text{C}$



Output inverter




Output inverter

Power dissipation

Output inverter FRED

$$P_{tot} = f(T_C)$$

parameter: $T_j = 125^\circ\text{C}$




Forward current

Output inverter FRED

$$I_F = f(T_C)$$

parameter: $T_j = 125^\circ\text{C}$




Short circuit safe operating area





Output inverter IGBT

$$I_{CSC} = f(V_{CE}), T_j = 125^\circ\text{C}$$





parameter: $V_{GE} \leq 15\text{ V}$, $t_{SC} \leq 10\text{ }\mu\text{s}$, $L < 50\text{ nH}$





PFC




PFC



PFC



Thermistor




Input rectifier bridge

Typ. diode characteristics

Input rectifier Bridge

$$I_F = f(V_F)$$

parameter: $t_p = 250 \mu s$




Transient thermal impedance

Input Rectifier Bridge

$$Z_{thJC} = f(t_p)$$

Parameter: $D = t_p / T$




Power dissipation

Rectifier

$$P_{tot} = f(T_c)$$

parameter: $T_j = 125 \text{ °C}$



Forward current

Rectifier

$$I_F = f(T_c)$$

parameter: $T_j = 125 \text{ °C}$

