

UG1212-A-R1



☐ Latching action

Actuator remains in the low position when "ON".

☐ Illuminated or non-illuminated

☐ Compact

Behind-panel depth less than 20 mm (.787)

☐ Flat round actuator for optional marking

☐ Sealed to IP67

ENVIRONMENTAL SPECIFICATIONS

- Front panel sealing : IP67 according to IEC 60529
- Shock resistance : 100 g according to IEC 512-4, test 6c
- Vibration resistance : 10-500Hz - 10 g according to IEC 512-4, test 6d
- Salt spray : IEC 512-6, test 11f
- Robustness (non-illuminated) : IK06 according to EN 50102 (1 joule)
- Operating temperature : -40°C to +85°C

ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load :
 - 4A 12VDC, 200.000 cycles
 - 1A 48VDC, 200.000 cycles
 - 2A 48VDC, 100.000 cycles
 - 3A 48VDC, 75.000 cycles
 - 1A 72VDC, 15.000 cycles
- Initial contact resistance : 100 mΩ max.
- Insulation resistance : 1 GΩ min. at 500VDC
- Dielectric strength : 1.500 Vrms between terminals
1.000 VAC rms between terminals and frame

For W terminals, current has to be limited to 400mA.

LED COMPONENT SPECIFICATIONS

LED colour	Forward current	Typ. forward voltage	Max. forward voltage
Super red (LOS)	20mA	1,95V	1,95V
Yellow (LOY)	20mA	2V	2,05V
Green (LOG)	20mA	2,1V	2,5V
Blue (LOB)	20mA	3,2V	4V

A resistor must be series-connected by the user.
Resistor value = $\frac{\text{supply voltage} - \text{LED forward voltage}}{\text{LED forward current}}$

GENERAL SPECIFICATIONS


- Panel thickness : 1,5 mm (.059) min.
5,5 mm (.217) max.
- Total travel : 2,5 mm (.098) +/- 0,3 mm
- Typical operating force : 5 N +/- 2N
- Low level/mech. life : 200.000 cycles
- Torque : 1,5 Nm max. applied to nut
- Soldering : 320°C max. for 3 sec.

MATERIALS


- Case : thermoplastic, UL 94-V0
- Actuator : polyamide 6/6
- Bushing/bezel : zinc die-cast (zamak), black painted
- Contacts : silver, gold plated
- Output wires (flying lead terminals) :
 - F version : AWG20, section 0,6 mm²
 - W version : AWG24, section 0,23 mm²
- LED wires :
 - F version : AWG26, section 0,12 mm²
 - W version : AWG24, section 0,23 mm²
- Lens : polycarbonate
- Terminal seal : epoxy

MOUNTING


Panel cut-out



Matrix mounting




Back of panel space requirement



IP series

Pushbutton switches for harsh environments - bushing Ø 12 mm - latching

Overview



ABOUT THIS SERIES

On the following pages, you will find successively :
model structure of switches and options in the same order as in above chart

Dimensions : first dimensions are in mm while inches are shown as bracketed numbers.



NOTICE : please note that not all combinations of above numbers are available.
Refer to the following pages for further information.



A sealing boot is available to protect the switches against frost and sand (P/N U5125).
It is presented after the IA series and in section H.



Mounting accessories : Standard hardware supplied : 1 hex nut 14 mm (.551) across flats and 1 O-Ring.




Packaging unit : 25 pieces


IP series

Pushbutton switches for harsh environments - bushing Ø 12 mm - latching


Square or round - illuminated



- Four LED colours
- Tin plated LED terminals



MODEL
STRUCTURE



Shown with standard flying lead terminals.


Square models



Solder lug terminals
IPC1SAD OFF - ON

Flying lead terminals
IPC1FAD OFF - ON

For THIN flying leads, replace F with W.



Also available with straight PC : **IPC1PAD** or quick-connect terminals : **IPC1Z1AD**


Round models



Solder lug terminals
IPR1SAD OFF - ON


Flying lead terminals
IPR1FAD OFF - ON

For THIN flying leads, replace F with W.




Also available with straight PC : **IPR1PAD** or quick-connect terminals : **IPR1Z1AD**

ACTUATOR COLOURS




1 : blue - B : dark blue - 2 : black - 3 : green - 4 : grey
5 : yellow - 6 : red - 7/1 : white - 8 : bright chrome
9 : orange - A : satin chrome

LED COLOURS



LOS : super red - LOY : yellow - LOG : green - LOB : blue

OPTIONS




100 : Satin chrome bezel
101 : Bright chrome bezel

IP series

Pushbutton switches for harsh environments - bushing Ø 12 mm - latching

Square or round - non-illuminated

MODEL STRUCTURE



Shown with standard flying lead terminals.

Actuator marking available on IPP models (symbol 10 mm max.). On request.

Square models



Solder lug terminals
IPC1SAD


OFF - ON

Flying lead terminals
IPC1FAD

OFF - ON

For THIN flying leads, replace F with W.

→ Flat



Also available with straight PC : **IPC1PAD** or quick-connect terminals : **IPC1Z1AD**

Round models



CURVED ACTUATOR

Solder lug terminals
IPR1SAD

OFF - ON

Flying lead terminals
IPR1FAD

OFF - ON

FLAT ACTUATOR


Solder lug terminals
IPP1SAD

OFF - ON

Flying lead terminals
IPP1FAD

OFF - ON


→ Flat



Also available with straight PC : **IP•1PAD** or quick-connect terminals : **IP•1Z1AD**


For THIN flying leads, replace F with W.

ACTUATOR COLOURS




1 : blue - B : dark blue - 2 : black - 3 : green - 4 : grey - 5 : yellow - 6 : red - 7/1 : white - 8 : bright chrome
9 : orange - A : satin chrome

OPTIONS



100 : Satin chrome bezel
101 : Bright chrome bezel
104 : High actuator (for round model only)



104 IPR

104 IPP