

# CONTROL PRODUCTS

PCB  
TERMINAL  
BLOCKS

INTER-  
CONNECTION

FUSES &  
FUSE-  
HOLDERS

LEDS &  
INDICATORS

MINIATURE  
SWITCHES

LIMIT &  
SAFETY  
SWITCHES

CONTROL  
PRODUCTS

INTERFACE  
MODULES &  
SUPPORTS

RELAY  
BASES

ENCLOSURES

BATTERIES

TRANS-  
FORMERS

## Heavy Duty Footswitch

- Industrial die-cast footswitch
- Heavy duty IP65 applications
- Snap action and slow action contact blocks  
1 NO + 1 NC
- Rising saddle-washer terminal connections
- Single or double double-pole contact blocks
- Positive opening operation
- Silver contacts
- Anti Slip foot pedal
- Non-slip rubber feet
- Supplied with IP65 cable gland
- CE approved



PART NO.	DESCRIPTION
CFSHC1	Guarded 1 snap action contact block
CFSHC2	Guarded 1 slow action contact block
CFSHC1C1	Guarded 2 snap action contact blocks
CFSHC2C2	Guarded 2 slow action contact blocks
CFSHC1C2	Guarded 1 snap and 1 slow action contact blocks

### SPECIFICATIONS

Contact Block Rated	10A		
Insulation voltage (Ui)	500VAC 600VDC		
Protection against short circuits	fuse 10A 500V type aM		
Alternate current: AC15 (50-60Hz)			
Ui (V)	250	400	500
Ie (A)	6	4	1
Direct current: DC13			
Ue (V)	24	125	250
Ie (A)	6	1.1	0.4
Connectors flexible wire sizes	min max	1 x 0.5 mm <sup>2</sup> (1 x AWG 20) 2 x 2.5mm <sup>2</sup> (2 x AWG 14)	
Actuating force			
		single snap action	10N
		single slow action	12N
		double snap action	13N
		double slow action	15N
Ambient temperature			
Weight guarded		from -25°C to +80°C	
		1.4 kg	

