



Home: Crimp Housings &gt;

**Part Number: 98686-0001**

MOX Receptacle Kit, 4 Rows, Key 1, Black, 40 Circuits



Series image - Reference only

Status: Planned for Obsolescence

Series: 98686  
Category: Crimp HousingsGo to [Part Detail](#) ▾ [CHECK DISTRIBUTOR INVENTORY](#) [Add to My Parts](#)  
 [Email this page](#)Mates With Part(s):  
98184 Series (Header)Use With Part(s):  
[98658](#) Crimp Terminals, [98194](#) Crimp Terminals**Application Tooling****FAQ**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application Tooling**[Check our list of old tooling that used to be available for this part](#)**Product Environmental Compliance**[EU ELV](#): Product not active

EU RoHS Certificate of Compliance (PDF)

[EU RoHS](#): Product not active

Multiple Part Product Compliance Statements

[EU RoHS Phthalates](#): Product not active

EU RoHS, REACH SVHC, &amp; Low-Halogen

[China RoHS](#):

Multiple Part Industry Compliance Documents

[REACH SVHC](#): Product not active

\*IPC 1752A Class C

[Low-Halogen Status](#): Product not active

\*IPC 1752A Class D

\*Molex Product Compliance Declaration

Questions on Product Environmental Compliance? Email [ProductCompliance@molex.com](mailto:ProductCompliance@molex.com)Request Molex's CMRT from [conflictminerals@molex.com](mailto:conflictminerals@molex.com)**Part Detail****COLLAPSE ALL****General**

Status	Planned for Obsolescence
Category	Crimp Housings
Series	<a href="#">98686</a>
Application	Power
Comments	will be delivered as kit containing housing, lever and carrier
Product Name	MOX
UPC	756054713495

**Physical**

Circuits (maximum)	40
Color - Resin	Black, Natural
Gender	Receptacle
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	10.830/g
Number of Rows	4
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-25°C to +105°C

**Electrical**

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	5.0A
-------------------------------	------

**Solder Process Data****Solderability Shelf Life Statement**

Lead-free Process Capability	N/A
------------------------------	-----

**PRODUCTS****QUICK LINKS****RESOURCES****STAY CONNECTED**Antennas  
Application Tooling  
Cable Assemblies  
Connected Lighting  
Connectors  
Copper Flex  
Electrical Products  
Industrial Automation  
Membrane Switches  
Optical Solutions  
Printed Electronic SolutionsCompany Information  
Contact Molex  
Cross-Reference  
Koch Industries  
Industries  
Investor Relations  
Literature  
Molex Racing  
Press Room / Press Releases  
Product Index  
Sitemap  
Terms & ConditionsSupply Chain Transparency  
Business Continuity  
Compliance  
ecocare  
Feedback | Help  
Jobs  
Legal | Trademarks  
Mobile Site  
Supplier Portal  
Privacy Policy  
Tradeshows