




D


C

B


A



P/N 284392-2 AS SHOWN



RECOMMENDED PC BOARD LAYOUT



1. MATERIALS AND FINISH
HOUSING : PA 6.6, UL 94-V0, COLOR GREEN.
CLAMP : BRASS, NICKEL PLATED
TERMINAL : BRASS, TIN PLATED
CLAMPING SCREW : M3, BRASS, NICKEL PLATED
2. SUITABLE FOR 1.6-2.4 mm. PC BOARD THICKNESS.
3. END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING
4. WIRE SIZE RANGE
14 - 30 AWG
5. NOT CUMULATIVE TOLERANCE

95.25	25	2-284392-5
91.44	24	2-284392-4
87.63	23	2-284392-3
83.82	22	2-284392-2
80.01	21	2-284392-1
76.20	20	2-284392-0
72.39	19	1-284392-9
68.58	18	1-284392-8
64.77	17	1-284392-7
60.96	16	1-284392-6
57.15	15	1-284392-5
53.34	14	1-284392-4
49.53	13	1-284392-3
45.72	12	1-284392-2
41.91	11	1-284392-1
38.10	10	1-284392-0
34.29	9	284392-9
30.48	8	284392-8
26.67	7	284392-7
22.86	6	284392-6
19.05	5	284392-5
15.24	4	284392-4
11.43	3	284392-3
7.62	2	284392-2
DIM "A"	NO. OF POS	PART NUMBER

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN 01FEB2002 E. ZANOLINI	
mm		0 PLC ±.3 1 PLC ±.3 2 PLC ±.25 3 PLC ±.25 4 PLC ±.25 ANGLES ±.25		CHK 01FEB2002 E. ZANOLINI	
MATERIAL		FINISH		APVD 01FEB2002 D. BIEVENOUR	
CUSTOMER DRAWING		PRODUCT SPEC		108-20166	
		APPLICATION SPEC		114-20079	
		WEIGHT		-	

TE TE Connectivity

NAME				
TERMINAL BLOCK, PCB MOUNT, STRAIGHT SIDE ENTRY WIRE, STACKING W/ INTERLOCK, 3.81mm PITCH				
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
A3	00779	C=284392	-	
		SCALE	SHEET	OF
		4:1	1	1
			REV	B1