MIC94070/71/72/73



High Side Power Switches

General Description

The MIC94070-73 are high-side load switches designed for operation between 1.7V to 5.5V. The devices contain a low on-resistance P-channel MOSFET that supports 1.2A of continuous current. The MIC94071 and MIC94073 feature an active load discharge circuit which insures capacitive loads retain no charge when the main switch is in an OFF state.

MIC94070-71 feature rapid turn on while MIC94072-73 provide a slew rate controlled Soft-Start turn-on of 800µs (typical) to prevent in-rush current from glitching supply rails.

An active pull-down on the enable input keeps MIC94070-73 in a default OFF state until the EN pin is pulled to a high level. Built-in level shift circuitry allows low voltage logic signals to switch higher supply voltages, or vice versa; high level logic signals can control low level voltages.

MIC94070-73's operating voltage range makes them suitable for 1-cell Lithium ion and 2- to 3-cell NiMH/NiCad/Alkaline powered systems, as well as all 5V applications. Their low operating current of 2μ A and low shutdown current of 4μ A maximize battery life.

Data sheets and support documentation can be found on Micrel's web site at: www.micrel.com.


Features

- 1.7V to 5.5V input voltage range
- 1.2A continuous operating current
- 3A pulse current
- 120mΩ R_{DSON} (typical)
- Built-in level shift for control logic; can be operated by 1.5V logic.
- Low 2µA quiescent current
- Soft-Start: MIC94072/73
- Micro-power shutdown <1µA
- Load discharge circuit: MIC94071, MIC94073
- Space saving 1.2mm × 1.6mm Thin MLF® package


Applications

- Load switch in portable applications:
 - Cellular phones
 - PDAs
 - MP3 players
 - Digital Cameras
 - Portable instrumentation
- Battery switch-over circuits
- Level translator

Typical Application



MIC94070, 72 Load Switch Application



MIC94071, 73
Load Switch with Capacitive Load Discharge

MLF and MicroLeadFrame are registered trademarks of Amkor Technologies, Inc.

Micrel Inc. • 2180 Fortune Drive • San Jose, CA 95131 • USA • tel +1 (408) 944-0800 • fax + 1 (408) 474-1000 • http://www.micrel.com

September 2007 M9999-090507

Ordering Information

Part Number		Part Marking ⁽¹⁾		Fast	Soft-	Load	Pankaga	
Standard	Pb-Free	Standard	Pb-Free	Turn On	Start	Discharge	Package	
_	MIC94070YC6	_	70P	•			SC-70-6	
_	MIC94071YC6	_	71P	•		•	SC-70-6	
_	MIC94072YC6	_	72P		•		SC-70-6	
_	MIC94073YC6	_	73P		•	•	SC-70-6	
_	MIC94070YMT	_	P70	•			1.2mm x 1.6mm Thin MLF®	
_	MIC94071YMT	_	P71	•		•	1.2mm x 1.6mm Thin MLF®	
_	MIC94072YMT	_	P72		•		1.2mm x 1.6mm Thin MLF®	
_	MIC94073YMT	_	P73		•	•	1.2mm x 1.6mm Thin MLF®	

Notes

Pin Configuration



Pin Description

Pin Number		Pin Name	Pin Function				
SC-70	MLF	riii Naiile					
1	1	V_{OUT}	Drain of P-channel MOSFET.				
2,5	2	GND	Ground and the backside pad (MLF only) should both be connected to electrical ground.				
4	3	V_{IN}	Source of P-channel MOSFET.				
3	4	EN	Enable (Input): Active-high CMOS compatible control input for switch A. Do not leave floating.				
6		NIC	No Internal Connection. A signal or voltage applied to this pin will have no effect on device operation.				

^{1.} Under-bar symbol on SC-70 Pb-free packages may not be to scale.

Absolute Maximum Ratings (1)

Input Voltage (V _{IN})	+6V
Enable Voltage (V _{EN})	
Continuous Drain Current (I _D) (3)	
$T_A = 25^{\circ}C \text{ (MLF}^{\oplus}) \dots$	±1.2A
$T_A = 25^{\circ}C (SC-70)$	±1.2A
Pulsed Drain Current (I _{DP}) (4)	±3.0A
Continuous Diode Current (I _S) (4)	–50mA
Storage Temperature (T _s) ESD Rating – HBM ⁽⁶⁾	4KV

Operating Ratings (2)

Input Voltage (V _{IN}))	+1.7 to +5.5V
Junction Tempera	ture (T _J)	40°C to +125°C
Package Thermal	Resistance	
SC-70-6 (θ_{JA})		240°C/W
1.2mm × 1.6m	nm MLF $^{ ext{@}}$ ($ heta_{ ext{JA}}$)	172°C/W
1.2mm × 1.6m	nm MLF $^{ ext{@}}$ ($ heta_{ ext{JC}}$) $^{(3)}$	134°C/W

Electrical Characteristics

 T_A = 25°C, bold values indicate -40°C $\leq T_A \leq +85$ °C, unless noted.

Symbol	Parameter	Condition	Min	Тур	Max	Units
V _{EN_TH}	Enable Threshold Voltage	$V_{IN} = 1.8V \text{ to } 4.5V, I_D = -250\mu\text{A}$	0.5		1.2	V
		$V_{IN} = 1.7V \text{ to } 4.5V, I_D = -250\mu\text{A}$	0.4		1.2	V
IQ	Supply Current	$V_{IN} = V_{EN} = 5.5V$, $I_D = OPEN$		50nA	5	μΑ
		Measured on the V _{IN} pin (7)				
I _{EN}	Enable Input Current	$V_{IN} = V_{EN} = 5.5V$, $I_D = OPEN$		2	4	μΑ
I _{SHUT-Q}	Shutdown Current	$V_{IN} = +5.5V, V_{EN} = 0V, I_D = OPEN$		25nA	1	μΑ
		Measured on the V _{IN} pin (7)				
I _{SHUT-SWITCH}	OFF State Leakage Current	$V_{IN} = +5.5V$, $V_{EN} = 0V$, $I_D = SHORT$		50nA	1	μΑ
		Measured on V _{OUT} (7)				
R _{DS(ON)}	P-Channel Drain to Source	$V_{IN} = +5.0V, I_D = -100mA, V_{EN} = 1.5V$		120	170	mΩ
	ON Resistance	$V_{IN} = +4.5V, I_D = -100mA, V_{EN} = 1.5V$		130	185	mΩ
	SC-70 Package	$V_{IN} = +3.6V, I_D = -100mA, V_{EN} = 1.5V$		145	210	mΩ
		$V_{IN} = +2.5V, I_D = -100mA, V_{EN} = 1.5V$		165	225	mΩ
		$V_{IN} = +1.8V, I_D = -100mA, V_{EN} = 1.5V$		200	260	mΩ
		$V_{IN} = +1.7V, I_D = -100mA, V_{EN} = 1.5V$		210	285	mΩ
R _{DS(ON)}	P-Channel Drain to Source	$V_{IN} = +5.0V, I_D = -100mA, V_{EN} = 1.5V$		100	160	mΩ
	ON Resistance MLF Package	$V_{IN} = +4.5V, I_D = -100mA, V_{EN} = 1.5V$		110	165	mΩ
		$V_{IN} = +3.6V, I_D = -100mA, V_{EN} = 1.5V$		125	180	mΩ
		$V_{IN} = +2.5V, I_D = -100mA, V_{EN} = 1.5V$		145	200	mΩ
		$V_{IN} = +1.8V, I_D = -100mA, V_{EN} = 1.5V$		180	240	mΩ
		$V_{IN} = +1.7V, I_D = -100mA, V_{EN} = 1.5V$		190	265	mΩ
R _{SHUTDOWN}	Turn-Off Resistance	$V_{IN} = +3.6V$, $I_{TEST} = 1mA$, $V_{EN} = 0V$		200	400	Ω
		MIC94071, 73				

Electrical Characteristics (Dynamic)

 V_{IN} = 5V; T_A = 25°C, bold values indicate -40°C $\leq T_A \leq +85$ °C, unless noted.


Symbol	Parameter	Condition	Min	Тур	Max	Units
t _{ON_DLY}	Turn-On Delay Time	$V_{IN} = +3.6V$, $ID = -100$ mA, $V_{EN} = 1.5V$		0.85	1.5	μs
		MIC94070, 71				
		$V_{IN} = +3.6V$, $ID = -100$ mA, $V_{EN} = 1.5V$		700	1200	μs
		MIC94072, 73				
t _{ON_RISE}	Turn-On Rise Time	$V_{IN} = +3.6V$, $ID = -100$ mA, $V_{EN} = 1.5V$	0.5	1	5	μs
		MIC94070, 71				
		$V_{IN} = +3.6V$, $ID = -100$ mA, $V_{EN} = 1.5V$	500	800	1500	μs
		MIC94072, 73				


t _{OFF_DLY}	Turn-Off Delay Time	$V_{IN} = +3.6V$, $ID = -100$ mA, $V_{EN} = 1.5V$	100	200	ns
		MIC94070, 71			
		$V_{IN} = +3.6V$, $ID = -100$ mA, $V_{EN} = 1.5V$	60	200	ns
		MIC94072, 73			
t _{OFF_FALL}	Turn-Off Fall Time	$V_{IN} = +3.6V$, $ID = -100$ mA, $V_{EN} = 1.5V$	60	100	ns
		MIC94070, 71			
		$V_{IN} = +3.6V$, $ID = -100$ mA, $V_{EN} = 1.5V$	60	100	ns
		MIC94072, 73			


Notes:


- 1. Exceeding the absolute maximum rating may damage the device.
- 2. The device is not guaranteed to function outside its operating rating.
- 3. With backside thermal contact to PCB.
- 4. Pulse width <300µs with < 2% duty cycle.
- 5. Continuous body diode current conduction (reverse conduction, i.e. V_{OUT} to V_{IN}) is not recommended.
- 6. Devices are ESD sensitive. Handling precautions recommended. HBM (Human body model), 1.5k in series with 100pF.
- 7. Measured on the MIC94070YMT, for other part numbers, please contact Micrel.


Typical Characteristics





































Functional Characteristics MIC94070



















MIC94071


















MIC94072













MIC94073












Package Information



6-Pin SC-70 (C6)



Recommended Land Pattern for MLF 1.2x1.6 4 Lead



Optional for maximum thermal performance. Heatsink should be connected to GND plane of PCB for maximum thermal performance.

Disclaimer: This is only a recommendation based on information available to Micrel from its suppliers. Actual land pattern may have to be significantly different due to various materials and processes used in PCB assembly. Micrel makes no representation or warranty of performance based on the recommended land pattern."

MICREL, INC. 2180 FORTUNE DRIVE SAN JOSE, CA 95131 USA

TEL +1 (408) 944-0800 FAX +1 (408) 474-1000 WEB http://www.micrel.com

The information furnished by Micrel in this data sheet is believed to be accurate and reliable. However, no responsibility is assumed by Micrel for its use. Micrel reserves the right to change circuitry and specifications at any time without notification to the customer.

Micrel Products are not designed or authorized for use as components in life support appliances, devices or systems where malfunction of a product can reasonably be expected to result in personal injury. Life support devices or systems are devices or systems that (a) are intended for surgical implant into the body or (b) support or sustain life, and whose failure to perform can be reasonably expected to result in a significant injury to the user. A Purchaser's use or sale of Micrel Products for use in life support appliances, devices or systems is a Purchaser's own risk and Purchaser agrees to fully indemnify Micrel for any damages resulting from such use or sale.

© 2007 Micrel, Incorporated.