


VDE SCREWDRIVER

VDE 42

VDE HEXAGON ALLEN KEY for in-hex screws

- Acc. to DIN ISO 2936
- Particularly suitable for cable branch clamping rings
- Oil-hardened
- GEDORE vanadium special steel
- VDE insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004



1000 V

Code	No.	mm	L ₁	L ₂			£
2324849	VDE 42 3	3	130	23.5	20	1	
2324857	VDE 42 4	4	120	40.0	25	1	
2324865	VDE 42 5	5	140	48.0	45	1	
2324873	VDE 42 6	6	140	48.0	60	1	
2324881	VDE 42 8	8	150	51.0	110	1	
2324903	VDE 42 10	10	220	51.0	230	1	
2324911	VDE 42 12	12	260	61.5	350	1	

VDE 42 T

VDE HEXAGON ALLEN KEY WITH T-HANDLE for in-hex screws

- Insulated acc. to IEC 60900:2004
- With Check-Tool insulation
- GEDORE chrome-vanadium steel 59CrV4



1000 V

Code	No.	mm	(+mm)			£
2661225	VDE 42 T 4	4	160	145	1	
2661233	VDE 42 T 5	5	160	250	1	
2661241	VDE 42 T 6	6	160	250	1	
2661268	VDE 42 T 8	8	160	260	1	
2661276	VDE 42 T 10	10	200	390	1	
2661284	VDE 42 T 11	11	200	400	1	
2661292	VDE 42 T 12	12	200	420	1	

VDE 2170

VDE SCREWDRIVER for slotted head screws

- VDE insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, fully insulated blade
- Blade tip to DIN ISO 2380-1 form A
- With impact resistant handle
- Blade in chrome-vanadium steel, with black tip



1000 V

Code	No.	mm	mm				£
1612220	VDE 2170 2,5	0.4	2.5	75	155	29	10
1612239	VDE 2170 3	0.5	3.0	100	180	33	10
1612247	VDE 2170 3,5	0.6	3.5	100	190	46	10
1612255	VDE 2170 4	0.8	4.0	100	190	49	10
1612271	VDE 2170 5,5	1.0	5.5	125	225	81	10
1612298	VDE 2170 6,5	1.2	6.5	150	260	116	10
1612301	VDE 2170 8	1.2	8.0	175	195	158	10
1612336	VDE 2170 10	1.6	10.0	200	320	188	10

VDE 2160 PH

VDE SCREWDRIVER for cross-slotted head screws PH

- VDE insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, fully insulated blade
- Blade tip to DIN ISO 8764-1 PH
- With impact-resistant handle
- Blade in chrome-vanadium steel, with black tip



1000 V

Code	No.	PH	mm	mm			£
1612107	VDE 2160 PH 0	0	M1,6 - M2	60	140	30	10
1612115	VDE 2160 PH 1	1	M2 - M3	80	180	68	10
1612123	VDE 2160 PH 2	2	M3,5 - M5	100	210	101	10
1612131	VDE 2160 PH 3	3	M5,5 - M7	150	270	168	10
1612158	VDE 2160 PH 4	4	M8 - M10	200	320	249	10

VDE 2160 PZ

VDE SCREWDRIVER for cross-slotted head screws PZ

- VDE insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, fully insulated blade
- Blade tip to DIN ISO 8764-1 PZ
- With impact-resistant handle
- Blade in chrome-vanadium steel, with black tip



1000 V

Code	No.	PZ	mm	mm			£
1612166	VDE 2160 PZ 0	0	M1,6 - M2	60	140	29	10
1612182	VDE 2160 PZ 1	1	M2 - M3	80	180	68	10
1612190	VDE 2160 PZ 2	2	M3,5 - M5	100	210	102	10
1612204	VDE 2160 PZ 3	3	M5,5 - M7	150	270	168	10
1612212	VDE 2160 PZ 4	4	M8 - M10	200	320	250	10

VDE 2170-2160 PH-077

VDE SCREWDRIVER SET 7 pieces

- Packed in environmentally-friendly cardboard box
- For slotted and cross-slotted head screws PH
- VDE insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, fully insulated blade
- With impact-resistant handle




1000 V

Code	No.	Contents			£
1616048	VDE 2170-2160 PH-077	PH 2,5 4 5,5 6,5 PH 0 1 2	575	1	

VDE 8098
VDE STRIPPING PLIERS with VDE dipped insulation


- Opening stop, spring and brass adjusting screw for wires 0.8 - 6.0 mm²
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation



Code	No.	L	L ₃	W ₃	T ₁	mm ²			£
6708980	VDE 8098-160	160	43.5	18.5	8.5	0,8-6	217	1	

VDE 8098 H
VDE STRIPPING PLIERS with VDE insulating sleeves

- Opening stop, spring and brass adjusting screw for wires 0.8 - 6.0 mm²
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004



Code	No.	L	L ₃	W ₃	T ₁	mm ²			£
1552074	VDE 8098-160 H	160	43.5	18.5	8.5	0,8-6	204	1	

VDE 8099
VDE STRIPPING PLIERS STRIP-FIX with VDE dipped insulation

- Self-adjusting, for wires 0.5 - 5.0 mm²
- GEDORE special hardened and tempered steel, oil-hardened, chrome-plated
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation
- E-8099 = Pair of spare knives



Code	No.	mm	inch	mm ²			£
6709600	VDE 8099-160	160	6.1/2	0,5-5	226	1	
5709580	E-8099			12	1		

VDE 8099 H
VDE STRIPPING PLIERS STRIP-FIX with VDE insulating sleeves

- Self-adjusting, for wires 0.5 - 5.0 mm²
- V-shaped cutting jaws for stripping the plastic insulation of single and multi-strand conductors
- GEDORE special hardened and tempered steel, oil-hardened, chrome-plated
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004



Code	No.	mm	inch	mm ²			£
1552082	VDE 8099-160 H	160	6.1/2	0,5-5	211	1	

VDE 146
VDE UNIVERSAL PLIERS 7 settings


- Gripping pliers with safety box joint and finger protection
- GEDORE special chrome-vanadium steel
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation



Code	No.	mm	mm			£
6120140	VDE 146 10	250	31	485	1	

VDE 8250
VDE HEAVY DUTY COMBINATION PLIERS with VDE dipped insulation

- For heavy continuous use
- Good lever action for easy cutting
- Induction-hardened precision cutting edges, hardness 62 - 64 HRC
- For flat and round material
- To cut all wire types including piano wire, 1.6 mm
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation





Code	No.	L	L ₃	W ₃	W ₄	T ₁			£
1429582	VDE 8250-160	160	35.0	22.8	5.8	10.4	236	1	
6720090	VDE 8250-180	180	38.5	25.6	6.5	11.0	312	1	
6720250	VDE 8250-200	200	39.5	27.0	6.5	12.4	365	1	
6720330	VDE 8250-225	225	42.2	27.7	6.5	13.0	485	1	

VDE 8250 H

VDE HEAVY DUTY COMBINATION PLIERS with VDE insulating sleeves

- For heavy continuous use
- Good lever action for easy cutting
- Induction-hardened precision cutting edges, hardness 62 - 64 HRC
- For flat and round material
- To cut all wire types including piano wire, 1.6 mm
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004




Code	No.	L	L ₃	W ₃	W ₄	T ₁	mm ²	Ø	£
1550942	VDE 8250-160 H	160	35.0	22.8	5.8	10.4	228	1	
1550950	VDE 8250-180 H	180	38.5	25.6	6.5	11.0	288	1	
1550969	VDE 8250-200 H	200	39.5	27.0	6.5	12.4	369	1	

VDE 8314

VDE SIDE CUTTER with VDE dipped insulation

- With slender head - ideal for confined spaces
- Induction-hardened precision cutting edges, hardness 63 - 65 HRC
- For medium-hard wire, 1.6 mm
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation




Code	No.	L	L ₃	W ₃	T ₁	Ø	mm ²	Ø	£
6743540	VDE 8314-140	140	18.5	18.5	9.5	1.6	199	1	
6743620	VDE 8314-160	160	19.0	22.0	10.0	1.6	253	1	

VDE 8314 H

VDE SIDE CUTTER with VDE insulating sleeves

- With slender head - ideal for confined spaces
- Induction-hardened precision cutting edges, hardness 63 - 65 HRC
- For medium-hard wire, 1.6 mm
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004




Code	No.	L	L ₃	W ₃	T ₁	Ø	mm ²	Ø	£
1552155	VDE 8314-140 H	140	18.5	18.5	9.5	1.6	177	1	
1552163	VDE 8314-160 H	160	19.0	22.0	10.0	1.6	231	1	

VDE 8315 H

VDE ELECTRICIANS' SIDE CUTTER with VDE insulating sleeves

- Double-function electricians' side cutters for cutting and wire stripping
- Stripping holes for single or multi-strand conductors 1.5 and 2.5 mm²
- Induction-hardened precision cutting edges
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004




Code	No.	L	L ₃	W ₃	T ₁	mm ²	Ø	mm ²	£
1742582	VDE 8315-160 H	160	19	22	10	1,5 / 2,5	1,6	231	1


VDE 8316

VDE POWER SIDE CUTTER with VDE dipped insulation

- Good lever action for easy cutting
- Induction-hardened precision cutting edges, hardness 63 - 65 HRC
- For hard wire/piano wire - values see table
- Max. cutting capacity Ø 1.8 - 2.0 mm
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation





Code	No.	L	L ₃	W ₃	T ₁	Ø	mm ²	£
1429590	VDE 8316-180	180	22.6	26	11	1,8	285	1
6742570	VDE 8316-200	200	22.0	28	11	2,0	341	1



VDE 8316 H
VDE POWER SIDE CUTTER with VDE insulating sleeves


- Good lever action for easy cutting
- Induction-hardened precision cutting edges, hardness 63 - 65 HRC
- For hard wire/piano wire - values see table
- Max. cutting capacity Ø 1.8 - 2.0 mm
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004



Code	No.	L	L ₃	W ₃	T ₁	Ø	W ₄	T ₁	W ₅	£
1550993	VDE 8316-180 H	180	22.6	26	11	1,8	267	1		
1551000	VDE 8316-200 H	200	22.0	28	11	2,0	344	1		

VDE 8367
VDE HEAVY DUTY END CUTTING NIPPERS



- Good lever action for easy cutting
- Induction-hardened precision cutting edges, hardness 63 - 65 HRC
- For hard wire/piano wire 1.6 mm
- GEDORE special hardened and tempered steel, drop-forged, oil-hardened and annealed
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation



Code	No.	L	L ₃	W ₃	T ₁	Ø	W ₄	T ₁	W ₅	£
2324830	VDE 8367-160	160	6.9	27	23.5	1,6	220	1		

VDE 8120
VDE FLAT NOSE PLIERS with VDE dipped insulation



- Long, flat jaws and serrated gripping surfaces
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation



Code	No.	L	L ₃	W ₃	W ₄	T ₁	W ₅	T ₁	W ₆	£
6715330	VDE 8120-160	160	51	16.5	3.4	9	185	1		

VDE 8120 H
VDE FLAT NOSE PLIERS with VDE insulating sleeves


- Long, flat jaws and serrated gripping surfaces
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004



Code	No.	L	L ₃	W ₃	W ₄	T ₁	W ₅	T ₁	W ₆	£
1552090	VDE 8120-160 H	160	51	16.5	3.4	9	175	1		

VDE 8122
VDE ROUND NOSE PLIERS with VDE dipped insulation


- Long, round jaws and serrated gripping surfaces
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation



Code	No.	L	L ₃	W ₃	D ₁	T ₁	W ₅	T ₁	W ₆	£
6717110	VDE 8122-160	160	48	16.5	2.5	8.7	170	1		

VDE 8122 H
VDE ROUND NOSE PLIERS with VDE insulating sleeves

- Long, round jaws and serrated gripping surfaces
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004




Code	No.	L	L ₃	W ₃	D ₁	T ₁	W ₅	T ₁	W ₆	£
1552104	VDE 8122-160 H	160	48	16.5	2.5	8.7	154	1		

VDE 8132

VDE TELEPHONE PLIERS with VDE dipped insulation, straight pattern

- Long, flat-round jaws, straight gripping faces, serrated
- Induction-hardened precision cutting edges, hardness 61 - 63 HRC
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation




Code	No.	L	L ₃	W ₃	W ₄	T ₁	T ₂	↔	↔	£
6721570	VDE 8132-160	160	50.0	16.5	3.2	9.0	2.5	193	1	
6721650	VDE 8132-200	200	75.7	18.5	3.7	9.5	2.8	248	1	



VDE 8132 H

VDE TELEPHONE PLIERS with VDE insulating sleeves, straight pattern

- Long, flat-round jaws, straight gripping faces, serrated
- Induction-hardened precision cutting edges, hardness 61 - 63 HRC
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004




Code	No.	L	L ₃	W ₃	W ₄	T ₁	T ₂	↔	↔	£
1552112	VDE 8132-160 H	160	50.0	16.5	3.2	9.0	2.5	164	1	
1552120	VDE 8132-200 H	200	75.7	18.5	3.7	9.5	2.8	235	1	



VDE 8132 AB

VDE BENT NOSE TELEPHONE PLIERS with VDE dipped insulation, angled pattern

- Long, flat-round jaws, angled gripping surfaces, serrated
- Induction-hardened precision cutting edges, hardness 61 - 63 HRC
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation




Code	No.	L	L ₃	W ₃	W ₄	T ₁	T ₂	↔	↔	£
6721730	VDE 8132 AB-160	160	46.0	16.5	3.2	9.0	2.5	177	1	
6721810	VDE 8132 AB-200	200	70.5	18.5	3.7	9.5	2.8	252	1	

VDE 8132 AB H

VDE BENT NOSE TELEPHONE PLIERS with VDE insulating sleeves, angled pattern

- Long, flat-round jaws, angled gripping surfaces, serrated
- Induction-hardened precision cutting edges, hardness 61 - 63 HRC
- GEDORE special hardened and tempered steel, chrome-plated
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004



Code	No.	L	L ₃	W ₃	W ₄	T ₁	T ₂	↔	↔	£
1552139	VDE 8132 AB-160 H	160	46.0	16.5	3.2	9.0	2.5	173	1	
1552147	VDE 8132 AB-200 H	200	70.5	18.5	3.7	9.5	2.8	235	1	

VDE S 8003

VDE PLIERS SET WITH VDE DIPPED INSULATION 3 pieces

- ✓ Packed in environmentally-friendly cardboard box
- ✓ Handles with VDE dipped insulation up to 1000 V, acc. to EN 60900/IEC 60900:2004, two-ply Check-Tool insulation



1000 V

Code	No.	Contents	Weight	Unit	£
6708120	VDE S 8003	VDE 8132-160 VDE 8250-180 VDE 8314-160	760	1	

VDE S 8003 H

VDE PLIERS SET WITH VDE INSULATING SLEEVES 3 pieces

- ✓ Packed in environmentally-friendly cardboard box
- ✓ Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004



1000 V

Code	No.	Contents	Weight	Unit	£
1550594	VDE S 8003 H	VDE 8132-160 H VDE 8250-180 H VDE 8314-160 H	747	1	

RZB2-11

VDE PLIERS SET 3 pieces

- ✓ In rugged plastic case
- ✓ Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004



1000 V

Code	No.	Contents	Weight	Unit	£
1692291	RZB2-11	VDE 8132-160 H VDE 8250-180 H VDE 8314-160 H	865	1	

RZB2-5

VDE PLIERS SET 3 pieces

- ✓ In rugged plastic case
- ✓ Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900:2004



1000 V

Code	No.	Contents	Weight	Unit	£
1708244	RZB2-5	VDE 8098-160 H VDE 8250-180 H VDE 8314-160 H	835	1	

RZB1-17

VDE TOOL SET 8 pieces

- ✓ In rugged plastic case



1000 V

Code	No.	Contents	Weight	Unit	£
1828045	RZB1-17	VDE 8132-200 H VDE 8250-180 H VDE 8314-160 H VDE 2170 4 5,5 VDE 2160 PH 1 2 4615 3	1700	1	

Contents

	VDE 8132 -200 H
	VDE 8250 -180 H
	VDE 8314 -160 H
	VDE 2170 4 5,5
	VDE 2160 PH 1 2
	4615 3

VDE ASSORTMENTS

S 1023

TOOL ASSORTMENT FOR MECHANICAL ENGINEERS 120 pieces

- Practical entry-level toolset
- The range includes mechanical and electrical engineering tools
- Recommended hook assortment 1500 HS-1023 (53 pieces)
- Also available in tool trolley or on tool boards

Code	No.	Contents	€	£
1999060	S 1023	118 tools in metric sizes	13.0	876.17
2657619	1023-1450-2	Tool set S 1023 + 2x tool panel 1450 L + hook assortment 1500 HS-1023	27.3	1,114.05
2657627	1023-1578	Tool set S 1023 + tool trolley 1578	56.5	1,272.64



Contents	
1 B 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22	
D 20 4 5 6 7 8 9 10 11 12 13	
680 4 5,5 6,5	
685 3 4 5 6	
685 X 5 6 8	
687 TX T10 T15 T20 T25 T27 T30 T40	
690 1 2	
690 PZD 1 2 3	
620	
676	
699	
2090 -4	
2093 U -20	
1993 U -10 T	
19 8 9 10 11 12 13 14 15 16 17 19 22 24 27 30 32	
1987	

Contents	
1990 -5 -10	
1995	
VDE 8132 -200 H	
VDE 8250 -180 H	
VDE 8314 -160 H	
VDE 2170 4 5,5	
VDE 2160 PH 1 2	
V 4614 PLUS	
4615 3	
171 IS 1,2 1,5 2	
165 PH 00 0	
8305 -2	
8306 -5	
42 1,3 1,5 2 (5/64AF) 2,5 3 4 5 6 8 10	
97 -150	

Contents	
100 -10	
119 -3 -5	
600 H -500	
248 ST -30	
8701 2-8	
8719 2-8	
8722 2-8	
403	
4528	
710	
745	
4534 -3	
298 -04	
8354 -1	
8139 -220 TL	

S 1093

VDE TOOL ASSORTMENT 26 pieces

- Particularly suited as the initial outfit for electrical specialists
- The GEDORE tool case or tool trolley are suited for mobile assignments
- Recommended hook assortment 1500 HS-1093 (26 pieces)
- Also available with case or on tool board

Code	No.	Contents	€	£
2319942	S 1093	26 tools in metric sizes	4.8	289.39
2657317	1093	Tool set S 1093 + tool case WK 1091 L	9.0	389.41
2657309	1093-1450	Tool set S 1093 + tool panel 1450 L + hook assortment 1500 HS-1093	11.1	375.67



Contents	
142 10 C	
VDE 8250 -180 H	
VDE 8132 -160 H	
VDE 8314 -160 H	
VDE 2170 4 5,5 6,5 8	
VDE 2160 PZ 1 2	

Contents	
V 4614 PLUS	
42 2 (5/64AF) 2,5 3 4 5 6 8 10	
4533 -2	
4528	

Contents	
8097	
600 H -500	
112 A -250	
110 HS -318	
0175 -06	

1090
TOOL CASE ELECTRICIAN 90 pieces

- ✓ The perfect tool set for the electrician or property manager
- ✓ A thoughtful assortment for the work to be done
- ✓ Packed in a strong plastic case with aluminium frame
- ✓ Three steel hinges, screwed handle, fitted with built in locks
- ✓ May be used wherever the right tools have to be always at hand
- ✓ GEDORE vanadium tools, chrome-plated
- ✓ Dimensions: W 460 x D 380 x H 200 mm



Code	No.	Contents		£
6601590	1090	Tool set S 1090 + tool case WK 1090 L	13.2	708.94

	Contents
	401
	401 A [10x]
	6 14x17 18x19 21x23 22x24
	8 4 4,5 5 5,5 6 7 8 9 10 11 12 13
	20 4 4,5 5 5,5 6 7 8 9 10 11 13
	2087
	2095
	2098
	2090 -4
	2093 U -3
	42 2 (5/64AF) 2,5 3 4 5 6 7 8 10
	60 CP 10
	156 S

	Contents
	2153 5,5
	2161 PH 1
	2160 PZ 1 2
	VDE 2160 PH 1 2
	VDE 2170 3,5 4 5,5 6,5
	4615 3,5
	173 5,5 8
	174 1
	745
	4522
	4534 -3
	145 10 JC
	8096 -140

	Contents
	VDE 8098 -160
	VDE 8120 -160
	VDE 8250 -180
	VDE 8132 AB -160
	VDE 8316 -200
	95 -175
	99 10-2 10-4
	101
	112 A -250
	112 S
	600 H -300
	72 H -100
	E-1090 LK LZ LF LS

1091
ELECTRICIANS TOOL CASE 18 pieces

- ✓ Robust tool case with 18-piece basic assortment
- ✓ **Particularly suitable for beginners in electronic professions**
- ✓ From eco-friendly tanned cowhide
- ✓ Carefully processed with strong industrial seams
- ✓ Base insert from zinc-plated sheet steel
- ✓ Edges reinforced with aluminium angle brackets, metal parts durable riveted
- ✓ With feet to protect sensitive surfaces
- ✓ Front part can be lowered for quick access to the tools, with two key locks to prevent inadvertent opening
- ✓ Removable carrying strap with shoulder protector and sturdy carrying handle
- ✓ Anti-theft protection due to two lockable notches, delivery includes two keys
- ✓ Document partition
- ✓ Interior measurements 430 x 200 x 290 mm



Code	No.	Contents		£
1953710	1091	Tool set S 1091 + tool case WK 1091 L	8.3	364.05

	Contents
	VDE 2133 7 8 10
	VDE 2160 PH 1 2 3
	VDE 2170 3 4 5,5
	4528
	4533 -2

	Contents
	V 4614 PLUS
	4629
	8097

	Contents
	VDE 8132 -160 H
	VDE 8250 -180 H
	VDE 8316 -180 H
	E-1091 ST

VDE 1001

VDE TOOL SET 14 pieces

- With practical foam insert in sturdy PVC case
- Dimensions: 380 x 285 x 70 mm
- Cranked allen socket screwdriver no. 42 is for locking the adjusting screw of extension VDE 1990, not VDE insulated



12,5
1/2
1000V

1000 V

Code	No.	Contents	Weight	Qty	£
6602560	VDE 1001	VDE 19 10 12 13 14 17 19 22 24 VDE 1993 U VDE 1990-5 -10 VDE 1989 T VDE 2170 5,5 42 2,5	3.5	1	700.39

Contents	
	VDE 19 10 12 13 14 17 19 22 24
	VDE 1993 U
	VDE 1990 -5 -10

Contents	
	VDE 1989 T
	VDE 2170 5,5
	42 2,5

VDE 1030

VDE TOOL CABINET 108 pieces

- Complete with a selection of VDE tools
- Dimensions: 190 x 500 x 750 mm



1000 V

Code	No.	Contents	Weight	Qty	£
6602130	VDE 1030	108 tools in cabinet	46.0	1	2,698.85
5600730	VDE 1030 L	Cabinet, empty	20.0	1	836.93

Contents	
	VDE 2133 5 6 7 8 9 10 11 12 13
	VDE 19 10 11 12 13 14 15 17 19 22 24 27 30 32
	VDE IN 19 5 6 8
	VDE 1990 -5 -10
	VDE 1993 U
	VDE 2170 2,5 4 5,5 6,5
	VDE 2160 PH 0 1 2
	VDE 894 10 11 12 13 14 15 16 17 19
	VDE 8098 -160 H
	VDE 8132 -160 H

Contents	
	VDE 8250 -160 H
	VDE 8314 -160 H
	VDE 4507 -4
	647
	171 IS 1,2 1,5 2
	165 PH 00 0
	8305 -2
	8306 -5
	4 K -500
	1500 H 1-50 [6x] 2-13 [17x] 3 [27x]

VDE ACCESSORIES

VDE 910

VDE RUBBER COVER SHEET

- ✓ VDE protective equipment acc. to VDE 0680, Part 1
- ✓ Thickness: 1.6 mm



Code	No.	L	W	mm	kg	£
1826816	VDE 910 13	130	130	40	1	9.17
1826832	VDE 910 25	250	350	210	1	33.04
1827030	VDE 910 50	500	500	430	1	91.22
1828193	VDE 910 60	600	600	700	1	123.23
1828207	VDE 910 100	1000	1000	1800	1	282.06
1828215	VDE 910 120	1200	1200	2950	1	410.42

VDE 911

VDE INSULATION MAT

- ✓ VDE protective equipment acc. to VDE 0303
- ✓ Thickness: 4.5 mm



Code	No.	L	W	mm	kg	£
1828258	VDE 911 100	1000	1000	6.0	1	158.67
1828266	VDE 911 1000	10000	1000	60.0	1	1,386.22

VDE 912

VDE ELECTRICIANS' SAFETY GLOVES

- ✓ Acc. to DIN EN 60903
- ✓ Made of natural latex

△ 1000 V



Code	No.	mm	kg	£
1828274	VDE 912 9	215	1	110.02
1828282	VDE 912 10	215	1	110.02

VDE 912

UNDER-GLOVES for VDE 912



Code	No.	mm	kg	£
1828290	VDE 912 50	50	1	9.75

V 915

NH-FUSE INSERTION GLOVE WITH SLEEVE

- ✓ To work on NH fuse inserts sizes 00 to 3
- ✓ To insert and remove low-tension high-performance fuses (NH fuse inserts)
- ✓ Can also be used for other devices applied instead of the fuse inserts, e.g. earthing and short-circuiting devices, inserting or removing blind fuse elements
- ✓ With contact blades to DIN 43620 Part 1, sizes 00 - 3 for nominal voltage to 600 V alternating voltage



△ 1000 V

Code	No.	mm	kg	£
2661314	V 915	460	1	122.35

V 916

PROTECTIVE BOOTS (PU)

- ✓ From polyurethane (PU) with steel cap
- ✓ To CE-EN 345-1



△ 1000 V

Code	No.	Size	mm	kg	£
2661322	V 916 39-40	39-40 / 6-6.1/2	3000	1	213.50
2661330	V 916 41	41 / 7.1/2	3000	1	213.50
2661349	V 916 42	42 / 8	3000	1	213.50
2661357	V 916 43	43 / 9	3000	1	213.50
2661365	V 916 44-45	44-45 / 9.1/2-10.1/2	3000	1	213.50
2661373	V 916 46	46 / 11	3000	1	213.50
2661381	V 916 47	47 / 12	3000	1	213.50

VDE 913

VDE PLASTIC CLAMP

- ✓ VDE protective equipment acc. to VDE 0680, Part 1



VDE 913 80



VDE 913 160

Code	No.	mm	mm	kg	£
1828304	VDE 913 80	80	30	1	17.49
1828312	VDE 913 160	160	70	1	17.86



- More VDE tools on request!
- Haven't you found the right tool?
- Ask us about custom-orders.
- Your problems are our assignments.