





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ANDERSON POWER PRODUCTS. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF ANDERSON POWER PRODUCTS IS PROHIBITED.

Copyright 2010

ANDERSON POWER PRODUCTS RESERVES THE RIGHT TO ALTER PRODUCT TYPES, THEIR TECHNICAL DATA, DIMENSION, STYLE AND ACCESSORIES WITHOUT PRIOR NOTIFICATION.



ITEM	QTY	DESCRIPTION	MATERIAL
1	1	CABLE SEALING NUT	NYLON, BLACK, UL94 V-2
2	1	CLAW	NYLON, BLACK, UL94 V-2
3	1	WIRE SEAL	EPDM, BLACK
4	1	PG GLAND BODY	NYLON, BLACK, UL94 V-2
5	1	GASKET	EPDM, BLACK

SEE SHEET 2 FOR LIST OF PART NUMBERS AND WIRE SEAL ARRANGEMENTS

NOTES:

- GLANDS FOR USE ON HIGH POWER SPEC PAK™ ONLY
- ALL MATERIALS ROHS COMPLIANT
- REFER TO ASSEMBLY INSTRUCTION 1S6554

DIMENSIONS ARE IN:		MM [INCH]		APPROVALS		 ANDERSON POWER PRODUCTS					
UNLESS OTHERWISE STATED				DRAWN							
TOLERANCES:				CMS		TITLE PG-36 CABLE SEALING GLANDS FOR SPEC PAK™					
DECIMALS (INCH)		DECIMALS (MM)		CHECKED							
.XX ± .02		.X ± .5		LLD							
ANGLES		±2°		MFG APPRV							
SURFACE FINISH:				CHB		SIZE A		DWG NO. 115054S1		REV. 0	
MACHINED		128 [3.2]✓		QC APPRV							
MOLDED		64 [1.6]✓		UFN							
MATERIAL:				ENG APPRV							
FINISH:				BD		SCALE		CADFILE		SHEET	
						NONE		03361		1 OF 2	
				-CAD GENERATED DRAWING- DO NOT MANUALLY UPDATE DO NOT SCALE							
3rd ANGLE PROJECTION											


REV.	DESCRIPTION	APPRV	DATE
REVISIONS			

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ANDERSON POWER PRODUCTS. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF ANDERSON POWER PRODUCTS IS PROHIBITED.


Copyright 2010

ANDERSON POWER PRODUCTS RESERVES THE RIGHT TO ALTER PRODUCT TYPES, THEIR TECHNICAL DATA, DIMENSION, STYLE AND ACCESSORIES WITHOUT PRIOR NOTIFICATION.


PS1P36-26X




PS1P36-32X




PS2P36-13X




PS2P36-9X




PS3P36-7X




PS3P36-10X



PS4P36-12X



PS5P36-8X



WIRE SEALING RANGE

GLAND P/N	SPEC PAK CODE	mm		INCHES	
		MIN	MAX	MIN	MAX
PS1P36-26X	PS03	21.0	26.5	0.83	1.04
PS1P36-32X	PS04	24.0	32.0	0.94	1.26
PS2P36-13X	PM21	11.0	13.0	0.43	0.51
PS2P36-9X	PM22	7.0	9.0	0.28	0.35
PS3P36-7X	PM31	6.5	7.8	0.26	0.31
PS3P36-10X	PM32	7.7	10.0	0.30	0.39
PS4P36-12X	PM41	10.0	12.0	0.39	0.47
PS5P36-8X	PM51	6.5	8.3	0.26	0.33

DIMENSIONS ARE IN:		MM [INCH]		APPROVALS		ANDERSON POWER PRODUCTS TITLE PG-36 CABLE SEALING GLANDS FOR SPEC PAK™	
UNLESS OTHERWISE STATED		TOLERANCES:		DRAWN	12/21/2010		
DECIMALS (INCH)	DECIMALS (MM)	ANGLES		CHECKED	12/21/2010	SIZE A	
.XX ± .02	.X ± .5	±2°		LLD	12/21/2010		
SURFACE FINISH:				MFG APPRV	12/21/2010		
MACHINED	128 [3.2]			CHB	12/21/2010		
MOLDED	64 [1.6]			QC APPRV	12/21/2010	DWG NO. 115054S1	
MATERIAL:				UFN	12/21/2010		
FINISH:				ENG APPRV	12/21/2010	REV. 0	
				BD	12/21/2010		
3rd ANGLE PROJECTION		-CAD GENERATED DRAWING- DO NOT MANUALLY UPDATE DO NOT SCALE			SCALE NONE		CADFILE 03361
					SHEET 2 OF 2		