

## Features

## Unregulated Converter

- Industry Standard Pinout
- 1kVDC or 2kVDC Isolation
- UL94V-0 Package Material
- Optional Continuous Short Circuit Protected
- Fully Encapsulated
- Custom Solutions Available
- Efficiency to 85 %

### Description

The RO DC/DC converters are typically used in general purpose power isolation and voltage matching applications, and feature a full industrial operating temperature range of -40°C to +85°C without derating.

### Selection Guide

| Part Number<br>SIP 4 | (2kV) | Input Voltage<br>(VDC) | Output Voltage<br>(VDC) | Output Current<br>(mA) | Efficiency<br>(%) | Max. Capacitive Load <sup>(1)</sup> |
|----------------------|-------|------------------------|-------------------------|------------------------|-------------------|-------------------------------------|
| RO-xx3.3S            | (H)   | 3.3, 5, 12, 15, 24     | 3.3                     | 303                    | 75                | 2200µF                              |
| RO-xx05S             | (H)   | 3.3, 5, 12, 15, 24     | 5                       | 200                    | 78-80             | 1000µF                              |
| RO-xx09S             | (H)   | 3.3, 5, 12, 15, 24     | 9                       | 111                    | 78-80             | 1000µF                              |
| RO-xx12S             | (H)   | 3.3, 5, 12, 15, 24     | 12                      | 83                     | 80-84             | 470µF                               |
| RO-xx15S             | (H)   | 3.3, 5, 12, 15, 24     | 15                      | 66                     | 80-84             | 470µF                               |
| RO-xx24S             | (H)   | 3.3, 5, 12, 15, 24     | 24                      | 42                     | 78-85             | 220µF                               |

xx = Input Voltage (other input and output voltage combinations available on request)

\* add Suffix "P" for Continuous Short Circuit Protection, e.g. RO-0505S/P, RO-0505S/HP

### Specifications (measured at $T_A = 25^\circ\text{C}$ , nominal input voltage, full load and after warm-up)

|                                                   |                                                           |                                                 |
|---------------------------------------------------|-----------------------------------------------------------|-------------------------------------------------|
| Input Voltage Range                               | $\pm 10\%$                                                |                                                 |
| Output Voltage Accuracy                           | $\pm 5\%$                                                 |                                                 |
| Line Voltage Regulation                           | 1.2%/1% of $V_{in}$ typ.                                  |                                                 |
| Load Voltage Regulation                           | 3.3V output type                                          | 20% max.                                        |
| (10% to 100% full load)                           | 5V output type                                            | 15% max.                                        |
|                                                   | 9V, 12V, 15V, 24V output types                            | 10% max.                                        |
| Output Ripple and Noise (20MHz limited)           | 100mVp-p max.                                             |                                                 |
| Operating Frequency                               | 50kHz min. / 100kHz typ. / 105kHz max.                    |                                                 |
| Efficiency at Full Load                           | 70% min. / 80% typ.                                       |                                                 |
| Minimum Load = 0%                                 | Specifications valid for 10% minimum load only.           |                                                 |
| Isolation Voltage                                 | (tested for 1 second)                                     | 1000VDC                                         |
|                                                   | (rated for 1 minute**)                                    | 500VAC / 60Hz                                   |
| Isolation Voltage                                 | H-Suffix (tested for 1 second)                            | 2000VDC                                         |
|                                                   | H-Suffix (rated for 1 minute**)                           | 1000VAC / 60Hz                                  |
| Isolation Capacitance                             | 20pF min. / 75pF max.                                     |                                                 |
| Isolation Resistance                              | 10 GΩ min.                                                |                                                 |
| Short Circuit Protection                          | 1 Second                                                  |                                                 |
| P-Suffix                                          | Continuous                                                |                                                 |
| Operating Temperature Range (free air convection) | -40°C to +85°C (see Graph)                                |                                                 |
| Storage Temperature Range                         | -55°C to +125°C                                           |                                                 |
| Relative Humidity                                 | 95% RH                                                    |                                                 |
| Package Weight                                    | 1.4g                                                      |                                                 |
| Packing Quantity                                  | 42 pcs per Tube                                           |                                                 |
| MTBF (+25°C)                                      | Detailed Information see Application Notes chapter "MTBF" | using MIL-HDBK 217F 985 x 10 <sup>3</sup> hours |
| (+85°C)                                           |                                                           | using MIL-HDBK 217F 200 x 10 <sup>3</sup> hours |

continued on next page

\*\*Any data referred to in this datasheet are of indicative nature and based on our practical experience only. For further details, please refer to our Application Notes.

## ECONOLINE

## DC/DC-Converter


with 3 year Warranty

# RECOM

## 1 Watt

## SIP4

## Single Output




**E-358085**

**EN-60950-1 Certified**  
**UL-60950-1 Certified**  
**EN-60601-1 Certified\***  
 (\* /H suffix)

# RO

## Derating-Graph (Ambient Temperature)



Refer to Application Notes

### Specifications (measured at $T_A = 25^\circ\text{C}$ , nominal input voltage, full load and after warm-up)

#### Certifications

CB Test Report Report: US/15348/UL

IEC 60950-1:2005 2nd Ed.

UL General Safety Report: E358085

UL 60950-1 2nd Ed.

EN General Safety Report: SPCLVD1109103

EN60950-1:2006 + A12:2011

EN Medical Safety Report: MDD1112018 + RM1112018



IEC/EN 60601-1 3rd Edition Medical Report + ISO14971 Risk Assessment

#### Notes



Note 1 Maximum capacitive load is defined as the capacitive load that will allow start up in under 1 second without damage to the converter.

### Typical Characteristics



#### RO-xx05S



#### RO-xx12S





#### RO-xx15S





### Package Style and Pinning (mm)

#### 4 PIN SIP Package



#### Recommended Footprint Details



#### RO Pin Connections

| Pin # | Single |
|-------|--------|
| 1     | -Vin   |
| 2     | +Vin   |
| 3     | -Vout  |
| 4     | +Vout  |

XX.X ± 0.5 mm  
XX.XX ± 0.25 mm

The product information and specifications are subject to change without prior notice. All products are designed for non-safety critical commercial and industrial applications. The Buyer agrees to implement safeguards that anticipate the consequences of any failures that might cause harm, loss of life and/or damage property.